

PRODUCT SUMMARY

SKY77759-51 Multimode Multiband Power Amplifier Module for Penta-Band (I, II, IV, V, VIII) WCDMA / HSDPA / HSUPA / HSPA+ / LTE Bands 1, 2, 4, 5, 8, 26, 27, 34, 39

Applications

- Multiband 3G handsets
- WCDMA/ HSDPA/ HSUPA/ LTE-modulated handsets for Bands I, II, IV, V, VIII

Features

- 50 ohm input and output impedances, integrated DC blocking on all ports
- CMOS-compatible, two-wire MIPI® logic inputs (SCLK, SDATA)
- VCC stages can attach to battery or buck DC/DC
- Small, low profile package:
5.3 mm x 4.3 mm x 0.75 mm (Max.)
32-pad configuration

3G FEATURES:

WCDMA mode supports output power, bandwidth for bands I, II, IV, V, VIII (and sub-bands IX, X, XVIII, IXX, XXVI) through an integrated band-select switch
Digital bias optimization through RFFE interface for best efficiency / linearity tradeoff

4G FEATURES:

Optimized for Average Power Tracking system
LTE supports output power bandwidth bands 1, 2, 4, 5, 8, 26, 27, 34, 39 (and sub-bands 9, 10, 18, 19, 26)

Description

The SKY77759-51, a multimode multiband (MMMB) Power Amplifier Module (PAM), supports 3G/4G handsets and operates efficiently in WCDMA and LTE modes. The PAM includes separate WCDMA blocks operating in low and high bands, a logic control block for multiple power control levels, and band enable functions in both cellular and UMTS. RF I/O ports are internally matched to 50 Ω to minimize external components. Extremely low leakage current maximizes handset standby time. The InGaP/GaAs die and passive components are mounted on a multi-layer laminate substrate and the assembly encapsulated in plastic overmold.

WCDMA: The SKY77759-51 enhanced architecture supports WCDMA, High-Speed Downlink Packet Access (HSDPA), High-Speed Uplink Packet Access (HSUPA) and LTE modulations; it covers multiple bands for 3GPP including bands I, II, IV, V, VIII, and operates at different power modes. The module is fully controllable via MIPI interface.

LTE: The SKY77759-51 meets spectral linearity requirements of LTE modulation with QPSK/16QAM up to 20 MHz bandwidth, including various resource block allocations, with good power-added efficiency.



Skyworks Green™ products are compliant with all applicable legislation and are halogen-free. For additional information, refer to Skyworks *Definition of Green™*, document number SQ04-0074.

Ordering Information

Product Name	Order Number	Evaluation Board Part Number
SKY77759-51 Multimode Multiband Power Amplifier Module	SKY77759-51	EN40-D875-001

Copyright © 2016, Skyworks Solutions Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions Inc. ("Skyworks") products or services. These materials including the information contained herein are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation products services specifications or product descriptions at any time without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts incompatibilities or other difficulties arising from any future changes.

No license whether express implied by estoppel or otherwise is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials products or information provided hereunder including the sale distribution reproduction or use of Skyworks products information or materials except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND WHETHER EXPRESS IMPLIED STATUTORY OR OTHERWISE INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE MERCHANTABILITY PERFORMANCE QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION TEXT GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES INCLUDING BUT NOT LIMITED TO ANY SPECIAL INDIRECT INCIDENTAL STATUTORY OR CONSEQUENTIAL DAMAGES INCLUDING WITHOUT LIMITATION LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical lifesaving or life-sustaining applications or other equipment in which the failure of the Skyworks products could lead to personal injury death physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products which may deviate from published specifications as a result of design defects errors or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance customer product design or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions Inc. in the United States and other countries. Third-party brands and names are for identification purposes only and are the property of their respective owners. Additional information including relevant terms and conditions posted at www.skyworksinc.com are incorporated by reference.