

DATA SHEET

SMV1405 to SMV1413 Series: Silicon Abrupt Junction Varactor Bondable Chips

Applications

- VCO applications up to 18 GHz
- Voltage tuned filters
- Voltage variable phase shifters


Features

- High Q
- · Low series resistance for low phase noise





Skyworks GreenTM products are compliant with all applicable legislation and are halogen-free. For additional information, refer to *Skyworks Definition of Green*TM, document number SQ04-0074.



Description

The SMV1405 to SMV1413 group of silicon abrupt junction varactor diodes is designed for use in Voltage Controlled Oscillators (VCOs) requiring tight capacitance tolerances. The low resistance of these varactors makes them appropriate for high-Q resonators in wireless system VCOs to frequencies up to 18 GHz. This family of varactors is characterized for capacitance over temperature.

Electrical and Mechanical Specifications

The absolute maximum ratings of the SMV1405 to SMV1413 varactors are provided in Table 1. Electrical specifications are provided in Table 2. Typical capacitance values are listed in

Table 3. Typical performance characteristics of the SMV1405 to SMV1413 varactors are illustrated in Figures 1 and 2.

The SPICE model for the SMV1405 to SMV1413 varactors is shown in Figure 3 and the associated model parameters are provided in Table 4.

Table 1. SMV1405 to SMV1413 Series Absolute Maximum Ratings (Note 1)

Parameter	Symbol	Minimum	Typical	Maximum	Units
Reverse voltage	VR			30	V
Forward current	l _F			20	mA
Power dissipation	Po			250	mW
Operating temperature	Тор	- 55		+125	°C
Storage temperature	Тѕтс	- 55		+150	°C
Electrostatic discharge:	ESD				
Human Body Model (HBM), Class 0				<250	V

Note 1: Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to device with only one parameter set at the limit and all other parameters set at or below their nominal value. Exceeding any of the limits listed here may result in permanent damage to the device.

CAUTION: Although these devices are designed to be as robust as possible, electrostatic discharge (ESD) can damage them. These devices must be protected at all times from ESD. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD precautions should be used at all times.

Table 2. SMV1405 to SMV1413 Series Electrical Specifications (Note 1) (Top = 25 °C, Unless Otherwise Noted)

Part Number	Min. VB, IR @ 10 μA (V)	Ст @ 4 V (pF)	Міп. <u>Ст @ 0 V</u> Ст @ 30 V (Ratio)	Max. Rs @ 4 V, 500 MHz (Ω)	Typ. Q @ 4 V, 50 MHz	Die Drawing
SMV1405-000	30	1.08 to 1.32	4.1	0.80	3200	150-813
SMV1408-000	30	1.62 to 1.98	4.1	0.60	2900	150-813
SMV1413-000	30	3.59 to 4.29	4.2	0.35	2400	150-813

Note 1: Performance is guaranteed only under the conditions listed in this table.

Package and Handling Information

Instructions on the shipping container label regarding exposure to moisture after the container seal is broken must be followed. Otherwise, problems related to moisture absorption may occur when the part is subjected to high temperature during solder assembly.

Additional bonding and handling methods are contained in the Skyworks Application Notes, *Waffle Pack Chip Carrier Handling/Opening Procedure* (document #200146) and *Diode Chips, Beam-Lead Diodes, Capacitors: Bonding Methods and Packaging* (document #200532).

Package dimensions are shown in Figure 4. The SMV1405 to SMV1413 series of varactors are not delivered on carrier tapes.

Table 4. Capacitance vs Reverse Voltage

VR (V)	Ст (рF)					
	SMV1405	SMV1408	SMV1413			
0	2.67	4.08	9.24			
0.5	2.12	3.36	7.39			
1.0	1.84	2.94	6.37			
1.5	1.70	2.60	5.71			
2.0	1.55	2.38	5.22			
2.5	1.44	2.24	4.85			
3.0	1.34	2.08	4.55			
4.0	1.25	1.88	4.10			
5.0	1.17	1.72	3.77			
10.0	0.95	1.28	2.85			
20.0	0.77	1.01	2.12			
30.0	0.63	0.95	1.77			

Typical Performance Characteristics




Figure 1. Capacitance vs Reverse Voltage




Figure 2. Relative Capacitance Change vs Temperature




Figure 3. SPICE Model

Table 5. SPICE Model Parameters (Note 1)

Part Number	CJO (pF)	(A) An	М	C _P (pF)	Rs (Ω)
SMV1405	2.37	0.77	0.5	0.29	0.80
SMV1408	3.89	0.92	0.5	0.21	0.60
SMV1413	8.92	0.87	0.5	0.30	0.35

Note 1: Values extracted from measured performance.

For more details, refer to the Skyworks Application Note, Varactor SPICE Models for RF VCO Applications, document #200315.




Figure 4. 150-813 Die Dimensions

Copyright © 2002-2011, 2014 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.