

#### **FINAL DATA SHEET**

# **APD Series: Silicon PIN Diode Bondable Chips**

### **Applications**


- Switches
- Attenuators

#### **Features**

- Established Skyworks PIN diode process
- Low capacitance designs to 0.05 pF
- Voltage ratings to 200 V
- Chip size < 15 mils square
- . Tight control of I layer base width
- Mesa and planar chip designs



Skyworks Green<sup>™</sup> products are compliant with all applicable legislation and are halogen-free. For additional information, refer to *Skyworks Definition of Green*<sup>™</sup>, document number SQ04-0074.



## **Description**

Skyworks APD series of silicon PIN diodes are designed for use as switch and attenuator devices in high-performance RF and microwave circuits. The PIN diode designs are useful over a wide range of frequencies from below 100 MHz to beyond 30 GHz. These devices use Skyworks well-established silicon technology resulting in PIN diodes with tightly controlled I-region characteristics.

The low capacitance and low resistance of the APD0505 through APD1520 diodes are ideal for switch applications that require insertion loss and fast switching speed. For switch or attenuator applications requiring high power and low distortion, the thick I-region and high reverse breakdown voltage of the APD2220 is ideal.

The absolute maximum ratings of the APD diode series are provided in Table 1. Electrical specifications are provided in Table 2. Table 3 identifies the die part numbers with their corresponding top contact diameters and die outline drawings. Typical performance characteristics are provided in Figures 1 through 5.

**Table 1. APD Series Absolute Maximum Ratings** 

Parameter	Symbol	Minimum	Maximum	Units
Power dissipation	Pois		$\frac{\textit{Maximum } T_J - \textit{Case Temp}}{\textit{Thermal Re sis tance}_{junction-to-case}}$	W
Reverse voltage	VR		See Voltage Rating column in Table 2	V
Forward current	lF		200	mA
Operating temperature	Тор	-65	+175	°C
Storage temperature	Тѕтс	-65	+200	°C

**ESD HANDLING**: Although this device is designed to be as robust as possible, electrostatic discharge (ESD) can damage this device.

This device must be protected at all times from ESD when handling or transporting. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection.

Industry-standard ESD handling precautions should be used at all times.

Table 2. APD Series Electrical Specifications<sup>1</sup> (Top = +25 °C, Unless Otherwise Noted)

Parameter	Junction Capacitance (CJ) VR = 50 V, 1 MHz (pF) Maximum	Junction Capacitance (CJ) VR = 0 V, 1 MHz (pF)	Series Resistance (Rs), I = 10 mA, 500 MHz (Ω)  Maximum	Forward Voltage (V <sub>F</sub> ) I <sub>F</sub> = 10 mA (V) Typical	Minority Carrier Lifetime (TL) I = 10 mA (ns)	Voltage Rating <sup>2</sup> (V) Maximum	I-Region Thickness (μm) Nominal	Thermal Resistance (θυc) (°C/W)
	Switching Applications							- maximum
APD0505-000	0.05	0.05	2.5	0.93	70	50	5	118
APD0510-000	0.10	0.10	1.5	0.90	90	50	5	76
APD0520-000	0.20	0.18	1.0	0.88	120	50	5	55
APD0805-000	0.05	0.10	2.0	0.89	100	100	8	87
APD0810-000	0.10	0.15	1.5	0.88	160	100	8	60
APD1505-000	0.06 @ 10 V	0.12	2.5	0.88	350	200	15	60
APD1510-000	0.10	0.20	2.0	0.86	300	200	15	56
APD1520-000	0.20	0.25	1.2	0.84	900	200	15	44
Attenuator Applications								
APD2220-000	0.20	0.25	4.0	0.79	700	200	50	18

Performance is guaranteed only under the conditions listed in this table.

 $<sup>^2</sup>$  Reverse current is specified at 10  $\mu$ A maximum at the voltage rating noted. Do not exceed this voltage.

### FINAL DATA SHEET • APD Series: Silicon PIN Diode Bondable Chips

**Table 3. APD Series Parts** 

Part Number	Top Contact Diameter (±0.5 mils)	Die Drawing			
Switching Applications					
APD0505-000	1.50	150-806			
APD0510-000	2.30	150-801			
APD0520-000	3.05	150-801			
APD0805-000	2.25	150-801			
APD0810-000	3.05	150-801			
APD1505-000	2.75	150-806			
APD1510-000	3.50	150-813			
APD1520-000	5.00	150-802			
Attenuator Applications					
APD2220-000	8.50	149-815			

## **Typical Performance Characteristics at 25 °C**




Figure 1. Resistance vs Forward Current @ 500 MHz




Figure 3. Capacitance vs Reverse Voltage





Figure 2. Resistance vs Forward Current @ 500 MHz



**Figure 4. Forward Current vs Forward Voltage** 




Figure 5. Maximum CW Input Power vs Case Temperature

### **Package Outline Drawings**

Package outline die drawings for the APD diode series are shown in Figures 6 and 7. Additional bonding and handling methods are contained in the Skyworks Application Notes, *Waffle Pack Chip Carrier Handling/Opening Procedure* (document #200146) and

Diode Chips, Beam-Lead Diodes, Capacitors: Bonding Methods and Packaging (document #200532).

#### **Die Packages**




Figure 6. 149-815 Die




Figure 7. 150 Series Die



Copyright © 2002-2010, 2012-2014, 2020 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.