

DATA SHEET

PIN Diode Chips Supplied on Film Frame

Applications

- Switches
- Attenuators

Features

- Preferred device for module applications
- PIN diodes supplied are 100% tested, saw cut, and mounted on film frame
- Low cost



u

Skyworks GreenTM products are compliant with all applicable legislation and are halogen-free. For additional information, refer to *Skyworks Definition of Green*TM, document number SQ04-0074.



Description

The PIN diodes that comprise this family of diodes supplied on film frames are designed for high-volume applications from 10 MHz to over 3 GHz. This family contains three groups of PIN diodes:

- 1. Low-capacitance, low-resistance PIN diodes designed primarily for RF switching applications:
 - SMP1320-099
 - SMP1321-099
 - SMP1322-099
 - SMP1340-099
- PIN diodes with mid-range I-layers and resistance designed for either RF switching or attenuator applications:
 - SMP1302-099
- SMP1331-099
- SMP1353-099
- 3. PIN diodes with thick I-layers designed for low-distortion RF variable attenuator applications:
 - SMP1304-099
 - SMP1307-099

These PIN diodes are provided as 100 percent tested, diced wafers mounted on film frames for optimal compatibility with high-volume pick-and-place assembly techniques.

Absolute maximum ratings are provided in Table 1. Electrical specifications are provided in Table 2. Chip dimensions are shown in Table 3. Typical performance characteristics are illustrated in Figures 1 through 5. Figure 6 describes the wafer film frame.

Table 1. PIN Diode Chips Absolute Maximum Ratings¹

Parameter	Symbol	Minimum	Maximum	Units
Reverse voltage	VR		Voltage rating	V
Maximum junction temperature	TJ		+175	°C
Operating temperature	Тор	-65	+150	°C
Storage temperature	TSTG	-65	+150	°C
Electrostatic discharge:	ESD			
Human Body Model (HBM), Class 1C			1000	V

¹ Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to device with only one parameter set at the limit and all other parameters set at or below their nominal value.

ESD HANDLING: Although this device is designed to be as robust as possible, electrostatic discharge (ESD) can damage this device.

This device must be protected at all times from ESD when handling or transporting. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection.

Industry-standard ESD handling precautions should be used at all times.

Table 2. PIN Diode Chips Electrical Specifications 1 (Top = 25 $^{\circ}$ C)

Part Number	l Region (μm) Nominal	Voltage Rating (V)	CJ (pF) VR = 30 V, f = 1 MHz	Typ VF (mV) @ IF = 10 mA	Max Rs (Ω) IF = 1 mA, f = 100 MHz	Max Rs (Ω) IF = 10 mA, f = 100 MHz	Typ TL (ns) IF = 10 mA	Application
SMP1302-099	50	200	0.12 typ 0.15 max	800	13.5 min 17 typ 21.5 max	3	700	Switch and attenuator
SMP1304-099	100	200	0.07 typ 0.15 max	800	30 min 37 typ 50 max	7	1000	Attenuator
SMP1307-099	175	200	0.08 typ 0.20 max	850	60 min 75 typ 100 max	15	1500	Attenuator
SMP1320-099	7	50	0.12 typ 0.175 max	850	2 typ	0.9	400	Switch
SMP1321-099	12	100	0.07 typ 0.15 max	860	3 typ	2.0	400	Switch
SMP1322-099	7	50	0.66 typ 0.85 max	825	1.5	0.45 typ	400	Switch
SMP1331-099	30	200	0.13 typ 0.16 max	800	14.5	1.7 typ	600	Switch and attenuator
SMP1340-099	5	50	0.10 typ @ 10 V 0.15 max @ 10 V	880	1.7 typ	1.2	100	Switch
SMP1353-099	50	200	0.08 typ@ 20 V 0.13 max @ 20 V	850	15	2.8	2000	Switch and attenuator

Performance is guaranteed only under the conditions listed in this table.

Reverse current is specified @ 10 μ A maximum at the voltage rating. This voltage should not be exceeded.

The PIN diodes listed here are processed on 100 mm silicon wafers, 100% DC tested, saw cut, and shipped on 6-inch film frame hoops.

Electrical rejects are identified with black ink on the film frame.

Attenuators are 100% series resistance tested @ 1 mA/100 MHz.

Table 3. PIN Diode Chip Dimensions

	Quantity of Good	Diodes Per Wafer	Chip Size	Chip Height	Anode Contact (In)
Part Number	Minimum	Nominal	(In)	(In)	
SMP1302-099	40000	46000	0.0135 ± 0.001	0.005 ± 0.001	0.0085 ± 0.0005
SMP1304-099	40000	46000	0.0135 ± 0.001	0.009 ± 0.001	0.0085 ± 0.0005
SMP1307-099	20000	25000	0.0185 ± 0.001	0.009 ± 0.001	0.0110 ± 0.0005
SMP1320-099	40000	46000	0.0135 ± 0.001	0.005 ± 0.001	0.0030 ± 0.0003
SMP1321-099	40000	46000	0.0135 ± 0.001	0.005 ± 0.001	0.0030 ± 0.0003
SMP1322-099	40000	46000	0.0135 ± 0.001	0.005 ± 0.001	0.0075 ± 0.0005
SMP1331-099	40000	46000	0.0135 ± 0.001	0.005 ± 0.001	0.0075 ± 0.0005
SMP1340-099	65000	72000	0.0105 ± 0.001	0.005 ± 0.001	0.0029 ± 0.0003
SMP1353-099	65000	72000	0.0105 ± 0.001	0.005 ± 0.001	0.0070 ± 0.0005

Typical Performance Characteristics (ToP = 25 °C)




Figure 1. Series Resistance vs Forward Current @ 1 MHz




Figure 3. Capacitance vs Reverse Voltage @ 1 MHz




Figure 5. Capacitance vs Reverse Voltage @ 1 MHz




Figure 2. Series Resistance vs Forward Current @ 100 MHz





Figure 4. Capacitance vs Reverse Voltage @ 1 MHz



- Wafer on nitto tape
 Color: light blue
 Thickness: 2.2 to 3.0 mils
 Tensile strength: 6.6 lbs (in width)
 Ring material: plastic

Figure 6. Wafer Film Frame Description

DATA SHEET • PIN DIODE CHIPS SUPPLIED ON FILM FRAME

Copyright © 2002-2008, 2011-2013, 2015-2016 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.