

DATA SHEET

SKY65249-11: WLAN 802.11b, g, n Intera™ Front-End Module

Features

- 2.4 to 2.5 GHz operation
- Cardbus, mini PC1, PCle and AP applications
- P_{OUT} @ 2.5% EVM (OFDM54): 18 dBm
- Gain: 25 dB
- Integrated PA, filters, directional detector and diversity switch
- Single supply voltage: 3.0 to 3.6 V
- Dual antennas
- Small, ultra thin package 4 x 4 x 0.9 mm
- Lead (Pb)-free and RoHS-compliant

Description


The SKY65249-11 Intera FEM contains one complete 2.4 GHz transmit/receive chain in a compact RF front-end module optimized for single band 2.4–2.5 GHz operation. The SKY65249-11 includes a PA with integrated input filtering for 3.2–3.3 GHz rejection, and temperature-compensated directional power detector with 20 dB dynamic range. Also included are low loss, high rejection harmonic filters and a diversity switch which provide high linearity in transmit and low loss in receive paths.

The SKY65249-11 is packaged in a lead (Pb)-free, RoHS-compliant laminate package, which measures 16 mm².



Skyworks offers lead (Pb)-free, RoHS (Restriction of Hazardous Substances)-compliant packaging.

Functional Block Diagram



Absolute Maximum Ratings

| Parameter | Symbol | Condition | Min. | Тур. | Max. | Unit |
|-----------------------------|--------------------|-----------|------|------|------|------|
| V _{CC} | V _{CC} | | -0.3 | | 5.5 | V |
| V _{REF} G | V _{REF} G | | -0.3 | | 5.5 | V |
| Tx In | Tx IN | | | | 10 | dBm |
| Junction temperature | T _J | | | | 150 | °C |
| Dissipated power | P _D | | | 0.6 | 1.0 | W |
| Thermal resistence | Θ _{JC} | | | | 55 | °C/W |
| Moisture sensitivity level | MSL-3 | | | | 250 | °C |
| Operating temperature range | T _{OP} | | -20 | | 85 | °C |
| Storage temperature range | T _{STO} | | -65 | | 150 | °C |

Performance is guaranteed only under the conditions listed in the specifications table and is not guaranteed under the full range(s) described by the Absolute Maximum specifications. Exceeding any of the absolute maximum/minimum specifications may result in permanent damage to the device and will void the warranty.

Recommended Operating Conditions

| Parameter | Symbol | Condition | Min. | Тур. | Max. | Unit |
|-----------------------|--------------------|-----------|------|------|------|------|
| Supply voltage | V _{CC} | | 3 | 3.3 | 3.6 | V |
| Reference voltage | V _{REF} G | | 2.8 | 2.9 | 3.0 | V |
| Operating temperature | T _{OP} | | 0 | 25 | 85 | °C |

DC Characteristics

Conditions: V_{CC} = 3.3 V, T_{OP} = 25 °C. Measurements made on Skyworks EVB with all losses de-embedded. All unused ports terminated into 50 Ω unless otherwise specified.

| Parameter | Symbol | Condition | Min. | Тур. | Max. | Unit |
|------------------------------------|--------------------|---|------|------|------|------|
| Total 802.11g Tx supply current | I _{CC} -g | $P_{OUT} = 18 \text{ dBm}, 54 \text{ Mbps OFDM},$ $V_{REF}G = 2.9 \text{ V}$ | | 180 | | mA |
| Total 802.11g Tx quiescent current | I _{CQ} -g | No RF | | 95 | | mA |
| Total 802.11b Tx supply current | I _{CC} -b | $P_{OUT} = 20 \text{ dBm}, 11 \text{ Mbps CCK}$ $V_{REF}G = 2.9 \text{ V}$ | | 210 | | mA |

PA Logic Characteristics

Conditions: $V_{CC}=3.3$ V, $T_{OP}=25$ °C. Measurements made on Skyworks EVB with all losses de-embedded. All unused ports terminated into 50 Ω unless otherwise specified.

| Parameter | Symbol | Condition | Min. | Тур. | Max. | Unit |
|------------------------|----------------------|-----------|------|------|------|------|
| Reference voltage high | V _{REF} G–H | | 2.8 | 2.9 | 3.0 | V |
| Reference voltage low | V _{REF} G–L | | 0 | | 0.3 | V |
| Reference current high | I _{REF} G–H | | | 4 | | mA |
| Reference current low | I _{REF} G-L | | | 20 | | μΑ |

Switch Characteristics

Conditions: V_{CC} = 3.3 V, T_{OP} = 25 °C. Measurements made on Skyworks EVB with all losses de-embedded. All unused ports terminated into 50 Ω unless otherwise specified.

| Parameter | Symbol | Condition | Min. | Тур. | Max. | Unit |
|-----------------------------|----------------------|-----------|------|------|------|------|
| Control voltage - ON state | V _{CTL} on | | 3 | 3.3 | 3.6 | V |
| Control voltage - OFF state | V _{CTL} off | | 0 | | 0.2 | V |
| Control current - ON state | I _{CTL} on | RF ON | | 10 | 75 | uA |
| Control current - ON state | I _{CTL} on | RF OFF | | 2 | 20 | uA |

Truth Table

| MODE | RxA0 (V) | RxA1 (V) | TxA0 (V) | TxA1 (V) | V _{CC} (V) | V _{REF} G (V) |
|-----------|----------|----------|----------|----------|---------------------|------------------------|
| Rx-ANT0 | 3.3 | 0 | 0 | 0 | 3.3 | 0 |
| Rx-ANT1 | 0 | 3.3 | 0 | 0 | 3.3 | 0 |
| Tx-ANT0 | 0 | 0 | 3.3 | 0 | 3.3 | 2.9 |
| Tx-ANT1 | 0 | 0 | 0 | 3.3 | 3.3 | 2.9 |
| TxRx-ANT0 | 3.3 | 0 | 3.3 | 0 | 3.3 | 2.9 |

All other conditions not recommended.

CAUTION: Although this device is designed to be as robust as possible, Electrostatic Discharge (ESD) can damage this device. This device must be protected at all times from ESD. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD precautions should be employed at all times.

802.11b,g Transmit Specifications

Conditions: $V_{CC}=3.3$ V, $V_{REF}G=2.9$ V, $T_{OP}=25$ °C. PA enables and control voltages set according to Truth Table. Measurements made on Skyworks EVB with all losses de-embedded. All unused ports terminated into 50 Ω unless otherwise specified.

| Parameter | Symbol | Condition | Min. | Тур. | Max. | Unit |
|---|--------------------------|---|---|------|------|---------|
| Frequency range | F | | 2.4 | | 2.5 | GHz |
| Linear output power - g | Plin_g | 54 Mbps OFDM, 64 QAM, EVM = 2.5 % | | 18 | | dBm |
| Compliant output power - b | P _{OUT} _b | 11 Mbps CCK | | 21 | | dBm |
| Backed off EVM | BEVM | 54 Mbps OFDM, 64 QAM, P _{OUT} = 8 dBm | | 1.5 | | % |
| 1 dB compression point | P _{1 dB} | | 22.5 | 25 | | dBm |
| Small signal gain | IS ₂₁ I | | | 25 | | dB |
| Small signal gain variation over frequency band | ∆IS ₂₁ I | | | 2 | | dB |
| Gain, 3.2-3.3 GHz | IS ₂₁ I - 3.2 | | | 0 | | dB |
| Harmonics | 2f, 3f | P _{OUT} = 18 dBm, 1 Mbps, CCK, 802.11b | | -50 | -42 | dBm/MHz |
| Tx switching time | t_sw | 50 % of V _{CTL} to 90/10 % RF output | | | 500 | ns |
| Input return loss | IS ₁₁ I | Tx In | | -10 | | dB |
| Output return loss | IS ₂₂ I | Ant A or Ant B | | -8 | | dB |
| Stability | STAB | $P_{OUT} \le 18$ dBm, load VSWR = 3:1 | All non-harmonically related outputs less than -50 dBc/1 MHz | | | utputs |

802.11b,g Receive Specifications

Conditions: $V_{CC}=3.3$ V, $V_{REF}G=2.9$ V, $T_{OP}=25$ °C. PA enables and control voltages set according to Truth Table. Measurements made on Skyworks EVB with all losses de-embedded. All unused ports terminated into 50 Ω unless otherwise specified.

| Parameter | Symbol | Condition | Min. | Тур. | Max. | Unit |
|------------------------------|--|---|------|------|------|------|
| Frequency range | F | | 2.4 | | 2.5 | GHz |
| Insertion loss | IS ₂₁ I | | | 1.1 | 1.6 | dB |
| Input/output return loss | IS ₁₁ I, IS ₂₂ I | RxG, Ant 0, 1 | | -15 | | dB |
| Antenna to Rx isolation | | PA off, switch in Tx-Ant0 (Ant1) mode | | 23 | | dB |
| Antenna to antenna isolation | | Isolation between AntO and Ant1 parts Switch in any mode | | 19 | | dB |


802.11b,g Power Detector Specification

Conditions: $V_{CC}=3.3~V$, $V_{REF}G=2.9~V$, $T_{OP}=25~^{\circ}C$. PA enables and control voltages set according to Truth Table. Measurements made on Skyworks EVB with all losses de-embedded. All unused ports terminated into 50 Ω unless otherwise specified.


| Parameter | Symbol | Condition | Min. | Тур. | Max. | Unit |
|---------------------------------------|----------|------------------|------|------|------|------|
| Power detect range | PDR | Ant 0 or Ant 1 | 5 | | 22 | dBm |
| Power detector accuracy | PDacc2 | Over 3:1 VSWR | | ±1 | | dB |
| P _{DET} load impedance | | | | 27 | | kΩ |
| P _{DET} output impedance | | | | | 6 | kΩ |
| Voltage limits | | Over power range | 0.1 | | 1.1 | V |
| Voltage range | | | 0.3 | 0.6 | | V |
| Power detector -3 dB corner frequency | LPF-3 dB | 10 kΩ load | 270 | 300 | 400 | kHz |

Typical Performance Data (2.4–2.5 GHz)


V_{CC} = 3.3 V, T_A = 25 °C, OFDM 54 Mbps, Z_0 = 50 Ω , unless otherwise noted




EVM vs. Frequency




Gain vs. Frequency




EVM vs. Output Power




Gain vs. Output Power




Detector Voltage vs. Output Power




Supply Current vs. Output Power




Parameters @ 18 dBm vs. V_{REG}



Parameters vs. V_{REG}




Gain vs. V_{REG}




Parameters vs. V_{REG}


Pin Out



Application Circuit



Branding Specifications



Pin Descriptions

| Pin Number | Symbol | Description |
|------------|--------------------|--|
| 1 | GND | Ground |
| 2 | TxG | Transmit input port. Internally matched to 50 Ω . External DC block required (2200 pF recommended) |
| 3 | GND | Ground |
| 4 | V _{REF} G | External reference voltage for the PA |
| 5 | P _{DET} | Directional power detector output |
| 6 | GND | Ground |
| 7 | V _{CC} | Power supply 3.3 V |
| 8 | RxA0 | Digital control input DPDT |
| 9 | TxA0 | Digital control input DPDT |
| 10 | TxA1 | Digital control input DPDT |
| 11 | RxA1 | Digital control input DPDT |
| 12 | NC | Not connected to anything externally |
| 13 | GND | Ground |
| 14 | GND | Ground |
| 15 | Ant1 | Auxiliary antenna port. Internally matched to 50 Ω . External DC block required (22 pF recommended) |
| 16 | Ant0 | Main antenna port. Internally matched to 50 Ω . External DC block required (22 pF recommended) |
| 17 | GND | Ground |
| 18 | GND | Ground |
| 19 | RxG | Receive output port. Internally matched to 50 Ω and DC blocked. No external DC block required |
| 20 | NC | Not connected to anything externally |


Recommended Solder Reflow Profiles

Refer to the "<u>Recommended Solder Reflow Profile</u>" Application Note.


Tape and Reel Information

Refer to the "<u>Discrete Devices and IC Switch/Attenuators</u> Tape and Reel Package Orientation" Application Note.


Test Evaluation Board



Test Evaluation Board (Center Enlarged)



Layer Stackup



Dimensions in mm.


Design Information

| RF line width | 19.3 (0.49) | mils (mm) |
|---------------------|-------------|-----------|
| DC line width | 11.3 (0.29) | mils (mm) |
| Dielectric constant | 4.2 | |


SMT BOM

| Ref Des | Qty. | Description | Value | Tolerance | Size |
|---------|------|-------------|---------|-----------|----------|
| C4 | 1 | Capacitor | 4.7 μF | ± 5% | SMT 0603 |
| C7 | 1 | Capacitor | 2200 pF | ± 5% | SMT 0402 |
| C8 | 1 | Resistor | 0 Ω | ± 5% | SMT 0402 |
| C9 | 1 | Capacitor | 22 pF | ± 5% | SMT 0402 |
| C10 | 1 | Capacitor | 22 pF | ± 5% | SMT 0402 |
| R1 | 1 | Resistor | 27 kΩ | ± 5% | SMT 0201 |
| R3 | 1 | Resistor | 0 Ω | ± 5% | SMT 0201 |


Package Dimensions




Solder Mask Opening (Top View)



Stencil Aperture (Top View)



Footprint (Top View)



Thermal Via Array under PA areas. 0.3 mm on 0.6 mm pitch. Additional vias will improve thermal performance. Note: Thermal vias should be tented and filled with solder mask. 30–35 µm Cu plating is recommended.

Copyright $\ @$ 2006, 2007, Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks, the Skyworks symbol, and "Breakthrough Simplicity" are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.