

# DATA SHEET

# SKY85712-11: 5 GHz WLAN Front-End Module

# **Applications**

- 802.11ac networking and personal computing systems
- PC cards, PCMCIA cards, mini-cards, and half mini-cards
- WLAN-enabled wireless video systems

## **Features**

- $\bullet$  Integrated high-performance 5 GHz PA, LNA with bypass, and T/R switch
- Fully matched input and output
- Integrated power detector and directional coupler
- Transmit gain: 27 dB
- Receive gain: 12 dB
- Output power: +17 dBm @ 1.8% EVM, HT80, MCS9
- Output power: +18 dBm @ 3% EVM, HT40, MCS7
- Small QFN (16-pin, 3 x 3 mm) package (MSL1, 260 °C per JEDEC J-STD-020)



Skyworks Green<sup>™</sup> products are compliant with all applicable legislation and are halogen-free. For additional information, refer to *Skyworks Definition of Green<sup>™</sup>*, document number SQ04–0074.





Figure 1. SKY85712-11 Block Diagram

## Description

The SKY85712-11 is a highly integrated, 5 GHz front-end module (FEM) incorporating a 5 GHz single-pole, double-throw (SPDT) transmit/receive (T/R) switch, a 5 GHz low-noise amplifier (LNA) with bypass, and a 5 GHz power amplifier (PA) intended for mobile/portable 802.11ac applications and systems.

The LNA and PA disable functions ensure low leakage current in off mode. An integrated power detector is included to provide closed-loop power control within the system.

The device is provided in a compact, 16-pin 3 x 3 mm Quad Flat No-Lead (QFN) package. A functional block diagram is shown in Figure 1. The pin configuration and package are shown in Figure 2. Signal pin assignments and functional pin descriptions are provided in Table 1.

| Pin | Name  | Description             | Pin | Name   | Description            |
|-----|-------|-------------------------|-----|--------|------------------------|
| 1   | GND   | Ground                  | 9   | N/C    | No connection          |
| 2   | RX    | RF receive output       | 10  | VCC1   | PA supply voltage      |
| 3   | GND   | Ground                  | 11  | VCC2   | PA supply voltage      |
| 4   | VDD   | LNA supply voltage      | 12  | GND    | Ground                 |
| 5   | VDET  | Detector output voltage | 13  | ANT    | Antenna                |
| 6   | PA_EN | PA enable               | 14  | GND    | Ground                 |
| 7   | GND   | Ground                  | 15  | CRX    | Switch control voltage |
| 8   | ТХ    | RF transmit input       | 16  | LNA_EN | LNA enable             |

#### Table 1. SKY85712-11 Signal Descriptions

#### **Technical Description**

The SKY85712-11 is comprised of a high-performance 5 GHz PA, 5 GHz LNA, and broadband SPDT switch. The device is fully-matched, and requires few external components for optimal performance, which makes it ideal for small portable/mobile applications. The FEM provides up to +27 dB of gain over the frequency band. The LNA supports an enable/disable mode for power savings when not in receive mode and a bypass function for increased receive dynamic range. The PA can be shut off using the PA\_EN signal (pin 6).

The low-loss broadband switch provides the T/R switching function on the SKY85712-11 and has a 1 dB output compression point (OP1dB) of approximately +25 dBm.

## **Electrical and Mechanical Specifications**

The absolute maximum ratings of the SKY85712-11 are provided in Table 2. The recommended operating conditions are specified in Table 3 and electrical specifications are provided in Table 4.

The state of the SKY85712-11 is determined by the logic provided in Table 5.

#### Table 2. SKY85712-11 Absolute Maximum Ratings<sup>1</sup>

| Parameter                                     | Symbol     | Minimum | Maximum | Units |
|---|------------|---------|---------|-------|
| Supply voltage                                | VCC1, VCC2 | -0.3    | +4.0    | V     |
| Supply voltage                                | Vdd        |         | +4.0    | V     |
| DC input on control pins (PA_EN, LNA_EN, CRX) | VIN        | -0.3    | +3.6    | V     |
| Input power (50 $\Omega$ load)                | Pin        |         | +10     | dBm   |
| Supply current                                | lcc        |         | 400     | mA    |
| Storage temperature                           | Тѕт        | -40     | +150    | °C    |
| Junction temperature                          | TJ         |         | 150     | °C    |
| Electrostatic discharge:                      | ESD        |         |         |       |
| Human Body Model (HBM), Class 1C              |            |         | 1000    | V     |

<sup>1</sup> Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to device with only one parameter set at the limit and all other parameters set at or below their nominal value. Exceeding any of the limits listed here may result in permanent damage to the device.

**ESD HANDLING**: Although this device is designed to be as robust as possible, electrostatic discharge (ESD) can damage this device. This device must be protected at all times from ESD when handling or transporting. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD handling precautions should be used at all times.

#### Table 3. SKY85712-11 Recommended Operating Conditions

| Parameter                     | Symbol          | Min      | Тур | Мах        | Units  |
|-------------------------------|-----------------|----------|-----|------------|--------|
| Supply voltage                | VCC1, VCC2, VDD | 3.0      | 3.3 | 3.6        | V      |
| Control logic:<br>High<br>Low | Vih<br>Vil      | 2.5<br>0 |     | 3.6<br>0.4 | V<br>V |
| Operating temperature         | Тор             | -40      |     | +85        | °C     |

| Table 4. SKY85712-11 Electrical Specifications <sup>1</sup>      |  |  |  |  |  |
|--|--|--|--|--|--|
| (Vcc1 = Vcc2 = Vdd = 3.3 V, Top = 25 °C, Unless Otherwise Noted) |  |  |  |  |  |

| Parameter  | Symbol   | Test Condition   | Min        | Тур        | Мах   | Units      |
|--|----------|--|------------|------------|-------|------------|
| Frequency range                                  | f        | Main frequency band  | 5.15       |            | 5.85  | GHz        |
| Transmit Mode                                    |          |  |            |            |       |            |
| Gain   | G        |  | 24         | 27         | 31    | dB         |
| Gain flatness                                    |          | Over any 40 MHz bandwidth  | -0.5       |            | +0.5  | dB         |
|  |          | With -45 dB EVM source:  |            |            |       |            |
| Output power                                     | Роит     | MCS9, HT80, 1.8 % DEVM, AT off                                   | +15        | +17        |       | dBm        |
|  |          | MCS7, HT40, 3 % DEVM, AT off<br>MCS0_mask_compliance             | +16<br>+18 | +18<br>+20 |       | dBm<br>dBm |
|  |          | Modulated signal:  | 110        | 120        |       | dDin       |
|  |          | Quiescent  |            | 190        |       | mA         |
| Current consumption                              |          | +17 dBm  |            | 240        |       | mA         |
|  |          | +10 dBm<br>+20 dBm   |            | 255        |       | mA         |
| Harmonics (2 <sup>nd</sup> and 3 <sup>rd</sup> ) | 2fo, 3fo | +19 dBm MCS0   |            |            | -50   | dBm/MHz    |
| All spurious                                     |          | +19.5 dBm OFDM, 6 Mbps   |            | -28        | -25   | dBm        |
| Isolation  |          | From ANT to either TX or RX pin                                  |            | 40         |       | dB         |
| Input return loss                                | S11      |  | 7          | 10         |       | dB         |
| Output return loss                               | IS221    |  | 10         | 12         |       | dB         |
| Power detector output:                           |          |  |            |            |       |            |
| +10 dBm  |          |  |            | 0.40       |       | V          |
| +23 dBm  |          |  |            | 1.20       |       | V          |
| Power detector output impedance                  | ZOUT_DET | RF output = -30 dBm  |            | 700        |       | Ω          |
| PA enable current                                | IENABLE  |  |            | 0.5        |       | mA         |
| Receive Mode                                     |          |  |            |            |       |            |
| Gain   | G        |  | 9          | 12         | 16    | dB         |
| 1 dB input compression point                     | IP1dB    | LNA active   |            | -5         |       | dBm        |
|  |          | LNA bypass   |            | +10        |       | dBm        |
| Gain step  |          |  | 19         | 21         | 23    | dB         |
| Gain flatness                                    |          | Over any 40 MHz bandwidth  | -0.25      |            | +0.25 | dB         |
| Noise figure                                     | NF       |  |            | 2.7        |       | dB         |
| Input return loss                                | IS11I    | LNA active<br>LNA bypass   | 6<br>10    |            |       | dB<br>dB   |
| Output return loss                               | S22      |  | 5          | 8          |       | dB         |
| Third order input intercept point                | IIP3     |  |            | +8         |       | dBm        |
|  |          | $LNA \leftrightarrow bypass$                                     |            |            | 200   | ns         |
| Switching time                                   | tsw      | $RX \leftrightarrow TX$ :  |            |            |       |            |
| -  |          | From 10% ↔ 90% power change<br>of rising or falling edge_state 1 |            |            | 400   | ns         |
| I NA hias current                                | Inn      |  |            | 11         | 15    | mA         |
| LNA enable current                               |          |  |            |            | 10    | υ <b>Α</b> |
| CRX enable current                               |          |  |            |            | 10    | μ <b>Α</b> |
| Receive Bypass Mode                              | 1        | 1  | 1          |            |       |            |
| Insertion loss                                   | IS211    |  |            | -9         |       | dB         |

<sup>1</sup> Performance is guaranteed only under the conditions listed in this table.

#### Table 5. SKY85712-11 Logic

| Mode                        | State | CRX (J5, Pin 10) | LNA_EN (J5, Pin 4) <sup>1</sup> | PA_EN (J5, Pin 9) <sup>2</sup> |
|-----------------------------|-------|------------------|---------------------------------|--------------------------------|
| All off (switch in TX mode) | 1     | 0                | 0                               | 0                              |
| WLAN receive                | 2     | 1                | 1                               | 0                              |
| WLAN receive bypass mode    | 3     | 1                | 0                               | 0                              |
| WLAN transmit               | 4     | 0                | 0                               | 1                              |

 $^1\,\text{LNA}$  is on while LNA\_EN is high. LNA is off and in bypass mode when LNA\_EN is low.

 $^2\,\text{PA}\_\text{EN}$  controls only the PA. It does not control the switch.

## **Evaluation Board Description**

The SKY85712-11 Evaluation Board is used to test the performance of the SKY85712-11 FEM. A suggested application schematic diagram is shown in Figure 3. A photograph of the Evaluation Board is shown in Figure 4. Table 6 provides the Bill of Materials (BOM) list for Evaluation Board components.

#### **Evaluation Board Setup Procedure**

- 1. Connect system ground to pin 2 of the J4 header and to pin 2 of the J5 header.
- 2. Apply 3.3 V to pins 1 and 3 of the J4 header and to pin 3 of the J5 header.
- 3. Select a path according to the information in Table 5: L = 0 V
  - H = 3.3 V
- 4. Connect a DMM to pin 12 of the J5 header to monitor the power detector voltage.

#### **Circuit Design Considerations**

The following design considerations are general in nature and must be followed regardless of final use or configuration:

- Paths to ground should be made as short as possible.
- The ground pad of the SKY85712-11 has special electrical and thermal grounding requirements. This pad is the main thermal conduit for heat dissipation. Since the circuit board acts as the heat sink, it must shunt as much heat as possible from the device.

Therefore, design the connection to the ground pad to dissipate the maximum wattage produced by the circuit board. Multiple vias to the grounding layer are required.

- **NOTE:** A poor connection between the ground pad and ground increases junction temperature (Tj), which reduces the life of the device.
- Place component C7 close to pin 11.
- Place component C6 close to pin 10.
- The ANT port is DC-blocked and does not require a DC blocking capacitor.
- There is no DC present on the RX port. This pin needs to be DC-blocked with a general purpose 4.7 pF capacitor if there is > 2.6 V DC on the trace connecting to the RX port.
- There is no DC present on the TX port. This pin needs to be DC-blocked with a general purpose 4.7 pF capacitor if there is > 3.2 V DC on the trace connecting to the TX port.
- Each VCC pin needs to be individually decoupled as shown in the Evaluation Board schematic. Place C7 close to pin 11. Place C6 close to pin 10.
- VCC1 and VCC2 should not be shorted together at the device pins. Refer to the layout for details.
- The DNI components and 0  $\Omega$  resistors can be eliminated.
- The ANT and LNA OUT trace losses are 0.18 dB. The TX IN trace losses are 0.22 dB.



Note:  $0 \Omega$  resistors and DNI components are not shown in schematic.

Figure 3. SKY85712-11 Application Schematic



Figure 4. SKY85712-11 Evaluation Board

| Component | Value    | Size | Vendor | Part Number       | Description               |
|-----------|----------|------|--------|-------------------|---------------------------|
| C6        | 0.22 μF  | 0402 | Murata | GRM155R60J224KE01 | Multilayer ceramic        |
| C7        | 47000 pF | 0402 | Murata | GRM155R71E473KA86 | Multilayer ceramic        |
| C19, C20  | 0.3 pF   | 0402 | Murata | GJM1555C1HR30BB01 | Multilayer ceramic        |
| L1        | 1.3 nH   | 0402 | Murata | LQG15HN1N3S02D    | High-frequency multilayer |

#### Table 6. SKY85712-11 Evaluation Board Bill of Materials<sup>1</sup>

 $^{1}$  0  $\Omega$  resistors and DNI components are not shown in the Bill of Materials.

## **Package Dimensions**

The PCB layout footprint for the SKY85712-11 is shown in Figure 5. Typical part markings are shown in Figure 6. Package dimensions for the 16-pin QFN are shown in Figure 7, and tape and reel dimensions are provided in Figure 8.

# **Package and Handling Information**

Instructions on the shipping container label regarding exposure to moisture after the container seal is broken must be followed. Otherwise, problems related to moisture absorption may occur when the part is subjected to high temperature during solder assembly.

The SKY85712-11 is rated to Moisture Sensitivity Level 1 (MSL1) at 260 °C. It can be used for lead or lead-free soldering. For additional information, refer to the Skyworks Application Note, *Solder Reflow Information*, document number 200164.

Care must be taken when attaching this product, whether it is done manually or in a production solder reflow environment. Production quantities of this product are shipped in a standard tape and reel format.



1. Via hole recommendations:

0.025 mm Cu via wall plating (minimum), solder mask on the far side should tent or plug via holes. 2. Solder mask recommendations:

- Contact board fabricator for recommended solder mask offset and tolerance.
- З. Stencil recommendations:
- 0.125 mm stencil thickness, laser cut apertures, trapezoidal walls and rounded corners offer better paste release.
  4. Dimensions and tolerances according to ASME Y14.5M-1994.
- 5. Unless specified, dimensions are symmetrical about center lines.
- 6. All dimensions are in millimeters.

## Figure 5. SKY85712-11 PCB Layout Footprint (Top View)

S3179



All measurements are in millimeters.
 Dimensioning and tolerancing according to ASME Y14.5M-1994.
 Coplanarity applies to the exposed heat sink slug as well as the terminals.

Figure 7. SKY85712-11 Package Dimensions



#### Notes:

- 1. Measured from center line of sprocket hole to center line of pocket.
- 2. Cumulative tolerance of 10 sprocket holes is  $\pm$  0.20 mm.
- 3. Other material available.
- Typical ESD surface resistivity is from 10<sup>5</sup> to 10<sup>11</sup> Ohms/square per EIA, JEDEC tape and reel specification.
- 5. All measurements are in millimeters.

#### Figure 8. SKY85712-11 Tape and Reel Dimensions





S2615

#### **Ordering Information**

| Product Description                      | Product Part Number | Evaluation Board Part Number |  |
|--|---------------------|------------------------------|--|
| SKY85712-11: 5 GHz WLAN Front-End Module | SKY85712-11         | SKY85712-11EK1               |  |

Copyright © 2013-2015, 2017-2018 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.