

DATA SHEET

SKY12236-11: High IIP3, 2.6 to 5.0 GHz Voltage-Controlled Variable Attenuator

Applications

- Automatic power leveling/gain control circuits in cellular base stations and point-to-point radio IF chains
- General wireless systems including WiMAX, LTE, WCDMA, VSAT, and military communications

Features

- Broadband operating range: 2.6 to 5.0 GHz
- Maximum attenuation: 25 dB
- Control voltage range: 0 to 5 V
- High IIP3: +43 dBm
- Low current consumption: <2 mA @ maximum attenuation
- Small, MCM (8-pin, 4.9 x 3.2 mm) package (MSL3, 260 °C per JEDEC J-STD-020)



Skyworks GreenTM products are compliant with all applicable legislation and are halogen-free. For additional information, refer to *Skyworks Definition of Green*TM, document number SQ04–0074.





Figure 1. SKY12236-11 Block Diagram

Description

The SKY12236-11 is a voltage-controlled variable attenuator from the Skyworks series of high third order input intercept point (IIP3) components. The device has been designed to operate over the 2.6 to 5.0 GHz frequency band, but is specifically optimized for use as a wide dynamic range, low distortion attenuator.

The SKY12236-11 provides monotonic attenuation performance over its entire control voltage range. This attenuator is comprised of a pair of matched PIN diodes that terminate two ports of its internal 90-degree hybrid coupler. The diodes are biased using an external control voltage signal. The attenuator requires no external components. It operates with a control voltage range of 0 to 5 V and a 1.7 mA typical control current at maximum attenuation.

A functional block diagram is shown in Figure 1. The pin configuration and package are shown in Figure 2. Signal pin assignments and functional pin descriptions are provided in Table 1.



(Top View)

Pin	Name	Description	Pin	Name	Description
1	GND	Ground. Must be connected to PCB ground using lowest possible inductance path.	5	GND	Ground. Must be connected to PCB ground using lowest possible inductance path.
2	V_CONTROL	Control voltage input (voltage applied is nominally equal to the voltage applied to pin 4)	6	J1	RF input/output
3	GND	Ground. Must be connected to PCB ground using lowest possible inductance path.	7	GND	Ground. Must be connected to PCB ground using lowest possible inductance path.
4	V_CONTROL	Control voltage input (voltage applied is nominally equal to the voltage applied to pin 2)	8	J2	RF output/input

Table 1. SKY12236-11 Signal Descriptions

Technical Description

The SKY12236-11 is a 50 Ω matched voltage-controlled variable attenuator with monotonic attenuation performance from 2.6 to 5.0 GHz over its entire control voltage range. This attenuator requires no external biasing or RF matching components.

Monotonic performance means the attenuation increases as the applied DC voltage increases. This attenuator is comprised of a pair of matched PIN diodes that terminate two ports of an internal 90-degree hybrid coupler.

The diodes are biased using an external control voltage signal that sets the bias current through a resistive network. The attenuator operates with a control voltage range of 0 to 5 V and a 1.7 mA typical control current at maximum attenuation. As the control voltage increases, the bias current through each of the PIN diodes also increases.

This increased bias current lowers the resistance of the PIN diodes. Maximum attenuation occurs when the resistance of the PIN diodes equals the characteristic impedance of the hybrid coupler ports, which they terminate. This occurs at a control voltage of approximately 5 VDC.

Electrical and Mechanical Specifications

The absolute maximum ratings of the SKY12236-11 are provided in Table 2. Electrical specifications are provided in Table 3.

Performance characteristics for the SKY12236-11 are illustrated in Figures 3 through 8.

Parameter	Symbol	Minimum	Maximum	Units
Control voltage	Vdc		10	V
RF input power (CW)	Pin		4	W
Control current	ICC		50	mA
Diode reverse bias voltage			50	V
Storage temperature	Tstg	-40	+85	°C
Operating temperature	Тор	-40	+85	°C
Electrostatic discharge:	ESD			
Charged-Device Model (CDM), Class 3 Human Body Model (HBM), Class 1A Machine Model (MM), Class A			500 250 50	V V V

Table 2. SKY12236-11 Absolute Maximum Ratings¹

¹ Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to device with only one parameter set at the limit and all other parameters set at or below their nominal value. Exceeding any of the limits listed here may result in permanent damage to the device.

ESD HANDLING: Although this device is designed to be as robust as possible, electrostatic discharge (ESD) can damage this device. This device must be protected at all times from ESD when handling or transporting. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD handling precautions should be used at all times.

Table 3. SKY12236-11 Electrical Specifications¹

(Top = +25 °C, VCONTROL = 0 to 5 V, PIN = 0 dBm, Characteristic Impedance [Zo] = 50 Ω, Unless Otherwise Noted)

Parameter	Symbol	Test Condition	Min	Typical	Мах	Units
Attenuation	Attn	f = 3.5 GHz, Vcontrol = 5 V	22	25		dB
Control current	Icc	$V_{CONTROL} = 5 V$		1.7		mA
Insertion loss	IL	$V_{CONTROL} = 0 V,$ f = 2.6 to 5.0 GHz $V_{CONTROL} = 0 V,$ f = 3.5 GHz		2.5 1.7	2.1	dB dB
Return loss	RL	$ V_{\text{CONTROL}} = 0 \text{ V}, \\ f = 2.6 \text{ to } 5.0 \text{ GHz} $		20		dB
Third order input intercept point IIP3 Vcoi f1 =		$P_{IN} = +8 \text{ dBm each tone,}$ $V_{CONTROL} = 0 \text{ V,}$ f1 = 3.50 GHz, f2 = 3.51 GHz		+43		dBm

¹ Performance is guaranteed only under the conditions listed in this table.

Typical Performance Characteristics

(Top = +25 °C, V_{CONTROL} = 0 to 5 V, P_{IN} = 0 dBm, Characteristic Impedance [Zo] = 50 Ω , J1 = Input Port, J2 = Output Port, Unless Otherwise Noted)




Figure 3. Attenuation vs Frequency Over Control Voltage




Figure 5. Attenuation Flatness vs Control Voltage (f = 3.3 to 4.3 GHz)




Figure 7. Input Return Loss vs Frequency Over Control Voltage




Figure 4. Attenuation vs Control Voltage Over Temperature (f = 3.8 GHz)




Figure 6. S-Parameters vs Frequency




Figure 8. Output Return Loss vs Frequency Over Control Voltage

Evaluation Board Description

The SKY12236-11 Evaluation Board is used to test the performance of the SKY12236-11 variable attenuator. An assembly drawing for the Evaluation Board is shown in Figure 9. The Evaluation Board layer detail is shown in Figure 10.

The attenuation level of the SKY12236-11 is controlled by applying 0 to 5 V to the V_CONTROL pins.

Package Dimensions

The PCB layout footprint for the SKY12236-11 is shown in Figure 11. Typical part markings are shown in Figure 12. Package dimensions are shown in Figure 13, and tape and reel dimensions are provided in Figure 14.

Package and Handling Information

Since the device is sensitive to moisture absorption, it is baked and vacuum packed before shipping. Instructions on the shipping container label regarding exposure to moisture after the container seal is broken must be followed. Otherwise, problems related to moisture absorption may occur when the part is subjected to high temperature during solder assembly.

The SKY12236-11 is rated to Moisture Sensitivity Level 3 (MSL3) at 260 °C. It can be used for lead or lead-free soldering. For additional information, refer to the Skyworks Application Note, *PCB Design & SMT Assembly/Rework Guidelines for MCM-L Packages*, document number 101752.

Care must be taken when attaching this product, whether it is done manually or in a production solder reflow environment. Production quantities of this product are shipped in a standard tape and reel format.





Figure 9. SKY12236-11 Evaluation Board Assembly Diagram



Note: Adjust this thickness to meet total thickness goal of 0.062 ± 0.005 inches.

202529-010

Figure 10. Layer Detail Physical Characteristics




Figure 11. SKY12236-11 PCB Layout Footprint




Figure 12. Typical Part Markings (Top View)





Figure 13. SKY12236-11 Package Dimensions

Skyworks Solutions, Inc. • Phone [781] 376-3000 • Fax [781] 376-3100 • sales@skyworksinc.com • www.skyworksinc.com 202529H • Skyworks Proprietary Information • Products and Product Information are Subject to Change Without Notice • May 31, 2019



202529-014

Figure 14. SKY12236-11 Tape and Reel Dimensions

Ordering Information

Part Number	Product Description	Evaluation Board Part Number	
SKY12236-11	2.6 to 5.0 MHz Voltage-Controlled Variable Attenuator	SKY12236-11-EVB	

Copyright © 2012-2014, 2016, 2019 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.