

DATA SHEET

OLS2249: Dual-Channel, Radiation-Tolerant Phototransistor Hermetic Surface-Mount Optocoupler

Features

- Dual channels of OLS049/0LS249
- CTR guaranteed over -55 °C to +100 °C ambient temperature range
- 1500 Vpc electrical isolation
- Radiation tolerant
- High-reliability screening is available

Description

The OLS2249 is specifically designed for high-reliability applications that require optical isolation in radiation environments such as gamma, neutron, and proton radiation with high current transfer ratio (CTR) and low saturation VCE. Each optocoupler channel consists of an LED and N-P-N silicon phototransistor that is electrically isolated, but optically coupled inside a hermetic eight-pin Leadless Chip Carrier (LCC) package.

The OLS2249 has 100 percent high-reliability screening parts available (contact Isolink for more information).




Figure 1. OLS2249 Block Diagram

Figure 1 shows the OLS2249 functional block diagram. Table 1 provides the OLS2249 absolute maximum ratings. Table 2 provides the OLS2249 electrical specifications.

Figures 2 through 4 illustrate the OLS2249 typical performance characteristics. Figure 5 shows the OLS2249 switching test circuit. Figure 6 provides the OLS2249 package dimensions.

Table 1. OLS2249 Absolute Maximum Ratings¹

Parameter	Symbol	Minimum	Maximum	Units
Coupled				
Input to output isolation voltage ²	Vdc	-1500	+1500	V
Channel to channel isolation voltage ³		-500	+500	V
Storage temperature range	Tstg	-65	+150	٥C
Operation temperature range	Та	-55	+125	٥C
Lead temperature for 10 seconds			240	٥C
Input Diode				·
Average input current ⁴	lod		40	mA
Peak forward current	lF		1	А
Reverse voltage	VR		2	V
Power dissipation	Po		70	mW
Output Detector				
Collector to emitter voltage	VCE		65	V
Emitter to collector voltage	Vec		7	V
Continuous collector current	Icc		50	mA
Power dissipation ⁵	PD		300	mW

¹ Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to device with only one parameter set at the limit and all other parameters set at or below their nominal value. Exceeding any of the limits listed here may result in permanent damage to the device.

 2 Measured between pins 1, 2, 3, and 4 shorted together, and pins 5, 6, 7, and 8 shorted together. TA = 25 °C and duration = 1 s.

 3 Measured between pins 1, 2, 7, and 8 shorted together, and pins 3, 4, 5, and 6 shorted together. TA = 25 °C and duration = 1 s.

 4 Value applies for Pw $\leq 1~~\mu$ s, PRR $\leq 300~pps.$

⁵ Derate linearly at 3 mW/°C above 25 °C.

ESD HANDLING: Although this device is designed to be as robust as possible, electrostatic discharge (ESD) can damage this device. This device must be protected at all times from ESD when handling or transporting. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD handling precautions should be used at all times.

Table 2. OLS2249 Electrical Specifications (Each Channel)¹ ($T_A = 25 \text{ °C}$, Unless Otherwise Noted)

Parameter Symbol **Test Condition** Min Max Units $I_F = 1 \text{ mA}, V_{CE} = 5 \text{ V}$ 2 12 $I_F = 2 \text{ mA}, V_{CE} = 5 \text{ V}, T_A = -55 \text{ °C}$ On-state collector current Ic_on +2.8 mΑ $I_F = 2 \text{ mA}, V_{CE} = 5 \text{ V}, T_A = 100 \text{ °C}$ 2 Saturation voltage $I_F = 2.0 \text{ mA}$. $I_C = 2.0 \text{ mA}$ ٧ VCE SAT 0.3 Breakdown voltage: Collector to emitter BVCEO $I_{CE} = 1 \text{ mA}$ 65 ۷ Emitter to collector **BV**ECO $I_{EC} = 100 \ \mu A$ 5 ۷ $V_{CE} = 20 V$ 100 nA Off-state leakage current, collector to emitter ICE_OFF VCE = 20 V, TA = 100 °C 50 μA Input: $I_F = +10.0 \text{ mA}, T_A = -55 \text{ °C}$ ۷ Forward voltage VF +1.4 +2.0 IF = 10.0 mA 1.2 1.8 V $I_F=10.0~mA,\,T_A=100~^\circ C$ 1.1 1.7 ۷ Reverse current $V_R = 2 V$ 100 IR μA Output resistance² RI_0 $V_{I} 0 = \pm 1000 V_{DC}$ 10¹¹ Ω Output capacitance² $V_{I_0} = 0 V, f = 1 MHz$ **C**I_0 5 pF Time: Rise tr $V_{CC} = 10 \text{ V}$. $R_L = 100 \Omega$ 25 US Fall tf I⊧ = 5 mA 25 μs

¹ Performance is guaranteed only under the conditions listed in the above table.

 2 Measured between pins 1, 2, 3, and 4 shorted together, and pins 5, 6, 7, and 8 shorted together. TA = 25 °C and duration = 1 s.

Typical Performance Characteristics




Figure 2. Forward Current vs Diode Forward Voltage




Figure 3. Normalized Collector Current vs Forward Current





Figure 4. Normalized CTRCE vs Temperature








Figure 6. OLS2249 Package Dimensions

Ordering Information

Part Number	Product Description
0LS2249	Dual Channel, Radiation Tolerant, Phototransistor Hermetic Surface Mount Optocoupler

Copyright © 2012-2015, 2017, 2019 Isolink, Inc. All Rights Reserved.

Information in this document is provided in connection with Isolink, Inc. ("Isolink"), a wholly-owned subsidiary of Skyworks Solutions, Inc. These materials, including the information contained herein, are provided by Isolink as a service to its customers and may be used for informational purposes only by the customer. Isolink assumes no responsibility for errors or omissions in these materials or the information contained herein. Isolink may change its documentation, products, services, specifications or product descriptions at any time, without notice. Isolink makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Isolink assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Isolink products, information or materials, except as may be provided in Isolink Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. ISOLINK DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. ISOLINK SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Customers are responsible for their products and applications using lsolink products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Isolink assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Isolink products outside of stated published specifications or parameters.

Isolink is a trademark of Isolink Inc. in the United States and other countries. Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners.