

#### **DATA SHEET**

## **MCT4/4R: Photo-Transistor Hermetic Optocouplers**

#### **Features**

- 1000 Vpc electrical isolation
- Small size
- Standard T0–72 hermetic package
- · Screened version is available on MCT4R

### **Description**

The MCT4 and MCT4R products are designed especially for high-reliability applications that require optical isolation with high Current Transfer Ratio (CTR) and low saturation Vce.

Each optocoupler consists of an LED and N-P-N silicon phototransistor that is mounted and optically coupled in a four-leaded hermetic TO-18 package.




Figure 1. MCT4/4R Block Diagram

A functional block diagram of the MCT4/4R is shown in Figure 1. The absolute maximum ratings of the MCT4/4R are provided in Table 1. Electrical specifications are provided in Table 2.

Typical performance characteristics of the MCT4/4R are illustrated in Figures 2 through 4. A typical switching test circuit is shown in Figure 5 and package dimensions for the MCT4/4R are provided in Figure 6.

#### DATA SHEET • MCT4/4R: PHOTO-TRANSISTOR HERMETIC OPTOCOUPLERS

Table 1. MCT4/4R Absolute Maximum Ratings <sup>1</sup>

Parameter	Symbol	Minimum	Maximum	Units	
Coupled		•			
Input to output isolation voltage <sup>2</sup>	VDC	-1000	+1000	٧	
Storage temperature range	TSTG	-65	+150	°C	
Operating temperature range	ТА	<b>-</b> 55	+125	°C	
Lead soldering temperature range (1.6 mm from case for 10 sec.)	Тмтс		+260	°C	
Total power dissipation	PD		250	mW	
Derate linearly from 25 °C			3.3	mW/25 °C	
Input Diode					
Average input current	IDD		40	mA	
Peak forward current <sup>3</sup>	lF		3	А	
Reverse voltage	VR		3	V	
Power dissipation at 25 °C	PD		90	mW	
Derate linearly from 25 °C			1.2	mW/25 °C	
Output Detector					
Collector to emitter voltage	VCE		30	V	
Emitter to collector voltage	VEC		7	V	
Power dissipation at 25 °C	PD		200	mW	
Derate linearly from 25 °C			2.67	mW/25 °C	

<sup>1</sup> Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to the device with only one parameter set at the limit and all other parameters set at or below their nominal value. Exceeding any of the limits listed in the above table may result in permanent damage to the device.

**CAUTION**: Although this device is designed to be as robust as possible, electrostatic discharge (ESD) can damage this device. This device must be protected at all times from ESD. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD precautions should be used at all times.

 $<sup>^2</sup>$  Measured between pins 1 and 3 shorted together, and pins 2 and 4 shorted together. TA = 25 °C and duration = 1 s.

<sup>&</sup>lt;sup>3</sup> Value applies for PW  $\leq 1$  µs, PRR  $\leq 300$  pps.

# Table 2. MCT4/4R Electrical Specifications <sup>1</sup> (TA = 25 °C, Unless Otherwise Noted)


Parameter	Symbol	Test Condition	Min	Typical	Max	Units
Current transfer ratio	CTR	IF = 10 mA, VcE = 10 V	15	100		%
Saturation voltage	VCE_SAT	$I_F = 10.0 \text{ mA}, I_C = 500.0 \mu\text{A}$		0.1		V
		$I_F = 50.0 \text{ mA}, I_C = 2.0 \text{ mA}$		0.2	0.5	V
Breakdown voltage:						
Collector to emitter	BVcEo	Ice = 1 mA	30			٧
Emitter to collector	BVeco	lec = 100 μA	7			٧
Collector to emitter dark current	ICEO	VCE = 10 V			50	nA
Capacitance collector to emitter		Vce = 0 V		2		pF
Input:						
Forward voltage	VF	IF = 40.0 mA		1.3	1.5	V
Reverse current	IR	V <sub>R</sub> = 3 V			10	μΑ
Output leakage current <sup>2</sup>	"'   II_0	RH ≤50%, VI_0 = 1000 VDC			1	μΑ
Rise and Fall time	tr/tf	$Vcc = 10 \text{ V}, RL = 100 \Omega, Ic = 2 \text{ mA}$		2		μs

<sup>1</sup> Performance is guaranteed only under the conditions listed in the above table.


 $<sup>^2</sup>$  Measured between pins 1 and 3 shorted together, and pins 2 and 4 shorted together. TA = 25 °C and duration = 1 s.

## **Typical Performance Characteristics**


(T<sub>A</sub> = -55 °C to +125 °C, Unless Otherwise Noted)



**Figure 2. Forward Current vs Forward Voltage** 



**Figure 3. Normalized Collector Current vs Forward Current** 



**Figure 4. Normalized CTRcE vs Temperature** 





Figure 5. MCT4/4R Switching Test Circuit



<sup>\*</sup> LED Anode is Case.

Figure 6. MCT4/4R Package Dimensions

#### **Ordering Information**

Model Name	Manufacturing Part Number
MCT4/4R: Photo-Transistor Hermetic Optocouplers	MCT4/4R

Copyright  $\ @$  2012, 2017 Isolink, Inc. All Rights Reserved.

Information in this document is provided in connection with Isolink, Inc. ("Isolink"), a wholly-owned subsidiary of Skyworks Solutions, Inc. These materials, including the information contained herein, are provided by Isolink as a service to its customers and may be used for informational purposes only by the customer. Isolink assumes no responsibility for errors or omissions in these materials or the information contained herein. Isolink may change its documentation, products, services, specifications or product descriptions at any time, without notice. Isolink makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Isolink assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Isolink products, information or materials, except as may be provided in Isolink Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. ISOLINK DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. ISOLINK SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Isolink products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Isolink products could lead to personal injury, death, physical or environmental damage. Isolink customers using or selling Isolink products for use in such applications do so at their own risk and agree to fully indemnify Isolink for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Isolink products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Isolink assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Isolink products outside of stated published specifications or parameters.

Isolink is a trademark of Isolink Inc. in the United States and other countries. Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners.