


### **PRODUCT DESCRIPTION**

The AWB7227 is a fully matched, Multi-Chip-Module (MCM) designed for picocell, femtocell, and customer premises equipment (CPE) applications. Its high linearity and efficiency meet the extremely demanding needs of small cell infrastructure architectures. Designed for WCDMA, HSDPA, and LTE air interfaces operating in the 2.11 GHz to 2.17 GHz band, the AWB7227 delivers up to +27 dBm of WCDMA (64 DPCH) power with an ACPR better than -50 dBc. It

operates from a convenient +4.5 V supply and provides 30 dB of gain. The device is manufactured using an advanced InGaP HBT MMIC technology offering state-of-the-art reliability, temperature stability, and ruggedness. The self-contained 7 mm x 7 mm x 1.3 mm surface mount package incorporates RF matching networks optimized for output power, efficiency, and linearity in a 50  $\Omega$  system.



May 8, 2019 • Skyworks Proprietary Information • Products and Product Information are Subject to Change Without Notice • 204241C

2




Figure 2: Pinout (X-ray Top View)

PIN NAME DESCRIPTION				
PIN	NAME	DESCRIPTION		
1	VREF	Reference Voltage		
2	GND	Ground		
3	GND	Ground		
4	V <sub>CC1</sub>	Supply Voltage		
5	RFℕ	RF Input		
6	GND	Ground		
7	Vdet	Detector Output		
8	GND	Ground		
9	GND	Ground		
10	GND	Ground		
11	Vcc2	Supply Voltage		
12	RFout	RF Output		
13	GND	Ground		
14	GND	Ground		

Table 1: Pin Description

# **ELECTRICAL CHARACTERISTICS**

Table 2: Absolute Minimum and Maximum Ratings						
PARAMETER	MIN	MAX	UNIT			
Supply Voltage (Vcc)	0	+5	<b>&gt;</b> v )			
Reference Voltage (VREF)		+3.5				
RF Output Power (Pour)		+30	dBm, modulated			
RF Input Power (PIN)	<u>,0</u> `	+10	dBm, CW			
ESD Rating Human Body Model <sup>(1)</sup> Charged Device Model <sup>(2)</sup>	Class 1C Class IV	-				
MSL Rating <sup>(3)</sup>	3	-				
Junction Temperature (TJ)	-	+150	°C			
Storage Temperature (Tstg)	-40	+150	°C			

Table 2: Absolute Minimum and Maximum Ratings

Functional operation is not implied under these conditions. Exceeding any one or a combination of the Absolute Maximum Rating Conditions may cause permanent damage to the device. Exposure to absolute ratings for extended periods of time may adversely affect reliability.

Notes:

JEDEC JS-001-2010.
JEDEC JESD22-C101D.
260 °C peak reflow.

PARAMETER	MIN	ТҮР	MAX	UNIT	COMMENTS
Operating Frequency (f)	2110	-	2170	MHz	
Supply Voltage (Vcc)	+3.6	+4.5	+4.65	V	
Reference Voltage (VREF)	+2.80 0	+2.85 -	+2.90 +0.5	V	PA "on" PA "shut down"
RF Output Power (Pour) (1)	-	+27	-	dBm	
Case Temperature (Tc) (2)	-40	-	+85	°C	

**Table 3: Operating Ranges** 

The device may be operated safely over these conditions; however, parametric performance is guaranteed only over the conditions defined in the electrical specifications. *Notes:* 

(1) Typ RF Output Power is used during production test.

3

(2) Case Temperature references the board temperature at the ground paddle on the backside of the package.

### Data Sheet

PARAMETER	MIN	TYP	MAX	UNIT	COMMENTS
Gain <sup>(2)</sup>	27	30.5	34	dB	2110 2170 MHz
ACPR <sup>(1), (2), (3)</sup> @ 5 MHz @ 10 MHz	-	-52 -63	-47 -60	dBc	Res BW 100 kHz Res BW 1 MHz
Power-Added Efficiency (1), (2), (3)	12	15	/-	%	
Thermal Resistance (RJc) (4)	-	14	2	C/W	Junction to Case
Supply Current <sup>(1), (2), (3)</sup>	-	740	939	mA	total through Vcc pins
Quiescent Current (Icq)	180	250	320	mA	
Reference Current	10	13	18	mA	through VREF pin
Leakage Current	-	3	10	μA	Vcc = +5 V, Vref = 0 V
Harmonics 2fo 3fo, 4fo	-	-50 -54	-45 -50	dBc	
Input Return Loss	15	20	-	dB	
Output Return Loss	15	20	-	dB	
P1dB	-	+34.5	-	dBm	CW tone
Spurious Output Level (all spurious outputs)	-	-	-60	dBc	Pout ≤ +27 dBm In-band load VSWR < 5:1 Out-of-band load VSWR < 10:1 Applies over all voltage and temperature operating ranges
Load mismatch stress with no permanent degradation or failure	8:1	-	-	VSWR	Vcc = +4.5 V, Pout = +27 dBm Applies over full operating temperature range

Table 4: Electrical Specifications (Tc = +25 °C, Vcc = +4.5 V, V<sub>REF</sub> = +2.85 V, 50  $\Omega$  system)

Notes:

(1) ACPR and Efficiency measured at 2140 MHz.

(2) Pour = +27 dBm.

(3) TM1 WCDMA 64 DPCH


(4) Use only V<sub>CC2</sub> (pin 11) current when calculating device junction temperature.

4

## **APPLICATION INFORMATION**

To ensure proper performance, refer to all related Application Notes.


#### Shutdown Mode



1. 10uF and 100uF capacitors are optional.


2. Applications that have large supply voltage transients may benefit from the use of TVS diodes. For such applications, recommended TVS diodes are SM05T1G or SMJ5.0A.







# PACKAGE OUTLINE




°∿_	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.	
A	1.17	1.27	1.37	0.046	0.05	0.054	-
ь	0.375	0.400	0.425	0.0148	0.0157	0.0167	14X
с	1	0.10	-	-	0.004	-	I
D	6.90	7.00	7.10	0.272	0.276	0.280	-
D1	-	5.40	-	-	0.213	-	-
D2	-	0.30	-	-	0.0118	-	
D3	-	2.90	-	-	0.114	-	
E	6.90	7.00	7.10	0.272	0.276	0.280	-
E1	-	6.80	-	-	0.268	-	-
E2	1	0.89	-	-	0.035	-	
е	-	1.067	-	-	0.0420	-	6X
L	0.375	0.400	0.425	0.0148	0.0157	0.0167	14X

#### NOTES:

- 1. CONTROLLING DIMENSIONS: MILLIMETERS
- 1. CONTROLLING DIMENSIONS: MILLIMETERS 2. UNLESS SPECIFIED TOLERANCE=±0.076[0.003]. 3. PADS (INCLUDING CENTER) SHOWN UNIFORM SIZE FOR <u>REFERENCE</u> ONLY. ACTUAL PAD SIZE AND LOCATION WILL VARY WITHIN MIN. AND MAX. DIMENSIONS ACCORDING TO SPECIFIC LAMINATE DESIGN.

Figure 5: Package Outline - 14 Pin 7 mm x 7 mm x 1.3 mm Surface Mount Module



#### Data Sheet

May 8, 2019 • Skyworks Proprietary Information • Products and Product Information are Subject to Change Without Notice • 204241C

7

## **COMPONENT PACKAGING**




Figure 7: Tape & Reel Packaging

Table 5: Tape & Reel Dimensions

PACKAGE TYPE	TAPE WIDTH	POCKET PITCH	REEL CAPACITY	MAX REEL DIA
7 mm x 7 mm x 1.3 mm	16 mm	12 mm	2500	13"

## **ORDERING INFORMATION**

ORDER NUMBER	TEMPERATURE RANGE	PACKAGE DESCRIPTION	COMPONENT PACKAGING
AWB7227RM52P7	-40 °C to +85 °C	RoHS-compliant 14 Pin 7 mm x 7 mm x 1.3 mm Surface Mount Module	Loose in Bag
AWB7227RM52P8	-40 °C to +85 °C	RoHS-compliant 14 Pin 7 mm x 7 mm x 1.3 mm Surface Mount Module	Tape and Reel, 2500 pieces per Reel
AWB7227RM52P9	-40 °C to +85 °C	RoHS compliant 14 Pin 7 mm x 7 mm x 4.3 mm Surface Mount Module	Partial Reel

 $\checkmark$ 

Copyright © 2016, 2019 Skyworks Solutions, Inc. Al Rights Reserved.

CONTINUED ved. Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS. PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND. WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skvworksinc.com. are incorporated by reference.

#### Skyworks Solutions, Inc.

Phone [781] 376-3000 • Fax [781] 376-3100 • sales@skyworksinc.com • www.skyworksinc.com Skyworks Proprietary Information • Products and Product Information are Subject to Change Without Notice