

DATA SHEET

OLH300: High-Speed Hermetic Optocoupler

Features

- Electrical parameters guaranteed over –55 °C to +125 °C ambient temperature range
- 1000 Vpc electrical isolation
- . High-speed, 1 Mbps typical
- · Open collector output
- 300 KHz bandwidth
- T0-5 hermetic package
- Similar to 6N135/6N136, 4N55
- Radiation tolerant
- Offers 100% high-reliability screening

Cathode VCC VCC VOUT Anode GND 202681-001

Figure 1. OLH300 Block Diagram

Description

The OLH300 is suitable for interfacing Transistor-to-Transistor Logic (TTL) to Low Power Schottky Transistor-Transistor Logic (LSTTL), TTL, or Complementary Metal Oxide Semiconductor (CMOS), as well as wide bandwidth analog applications.

Each OLH300 has an LED and an integrated photodiode transistor detector that is mounted and coupled in a ceramic substrate inside a hermetic T0-5 package, that provides 1000 Vpc of electrical isolation between the input and output. The integrated photodiode transistor improves the switching speed by orders of magnitude as compared to standard photo-transistors by reducing the base-to-collector capacitance. The internal shield provides excellent common-mode immunity performance.

Figure 1 shows the OLH300 functional block diagram. Table 1 provides the OLH300 absolute maximum ratings. Table 2 provides the OLH300 electrical specifications.

Figures 2 through 4 illustrate the OLH300 typical performance characteristics. Figure 5 shows the OLH300 switching test circuit. Figure 6 provides the OLH300 package dimensions.

DATA SHEET • OLH300: HIGH-SPEED HERMETIC OPTOCOUPLER

Table 1. OLH300 Absolute Maximum Ratings¹

Parameter	Symbol	Minimum	Maximum	Units
Coupled	·	•		
Input to output isolation voltage ²	VDC	-1000	+1000	V
Storage temperature range	Тѕтс	-65	+150	°C
Operating temperature range	Та	-55	+125	°C
Lead temperature 1.6 mm from the case for 10 seconds			+240	°C
Input Diode				
Average input current	Idd		20	mA
Peak forward current (≤1 ms duration)	l _F		40	mA
Reverse voltage	V R		5	V
Power dissipation	Po		36	mW
Output Detector				
Average output current			8	mA
Peak output current			16	mA
Supply voltage	Vcc	-0.5	+18.0	V
Output voltage	Vouт	-0.5	+18.0	V
Power dissipation	Po		50	mW

Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to the device with only one parameter set at the limit and all other parameters set at or below their nominal value. Exceeding any of the limits listed here may result in permanent damage to the device.

ESD HANDLING: Although this device is designed to be as robust as possible, electrostatic discharge (ESD) can damage this device. This device must be protected at all times from ESD when handling or transporting. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD handling precautions should be used at all times.

 $^{^{2}\}text{ Measured between pins 1, 2, and 3 shorted together, and pins 5, 6, and 7 shorted together. TA = 25 ^{\circ}\text{C} \text{ and duration} = 1 \text{ s.}$

Table 2. OLH300 Electrical Specifications¹ ($T_A = -55$ °C to +125 °C, Unless Otherwise Noted)

Parameter	Symbol	Test Condition	Minimum	Typical	Maximum	Units
Current transfer ratio (CTR) ²	CTR	$I_F = 10.0 \text{ mA}, V_0 = 0.4 \text{ V}, V_{CC} = 4.5 \text{ V}$	20.0	45.0		%
Logic:						
Low output voltage	VoL	$I_F = 10.0 \text{ mA}, I_{OL} = 1.5 \text{ mA}, V_{CC} = 4.5 \text{ V}$		0.25	0.4	V
High output current	Іон	$I_F = 0 \text{ mA}, V_0 = V_{CC} = 15.0 \text{ V}$		0.05	100.0	μΑ
Low supply current	ICCL	IF = 0 mA, Vcc = 15.0 V, Vo = Open		0.05	10.0	μΑ
High supply current	Іссн	IF = 10 mA, Vcc = 15 V, Vo = Open		40	200	μΑ
Input:						
Forward voltage	V F	IF = 10.0 mA		1.7	2.5	٧
Reverse breakdown voltage	Bvr	IR = 10 μA	3			٧
To output leakage current ³	lı_o	$R_H \le 50\%$, $T_A = 25$ °C, $V_{1_0} = 1000 \text{ Vdc}$			1	μΑ
Temperature coefficient of the input	ΔVF	IF = +5.0 mA		-2.3		mV
diode forward voltage	ΔΤΑ					°C
Propagation delay time logic:						
High to low	t PHL	If = 10.0 mA, Vcc = 5.0 V, RL = 4.1 k Ω		0.3	1.0	μs
Low to high	t PLH	If = 10.0 mA, Vcc = 5.0 V, RL = 4.1 k Ω		0.5	2.0	μs

Performance is guaranteed only under the conditions listed in the above table.

² Current transfer ratio is defined as the ratio of the output collector current Ic to the forward LED current IF, multiplied by 100%.

 $^{^3}$ Measured between pins 1, 2, and 3 shorted together, and pins 5, 6, and 7 shorted together. Ta = 25°C and duration = 1 second.

Typical Performance Characteristics




Figure 2. LED Forward Voltage vs Temperature




Figure 3. Normalized Output Current vs Temperature




Figure 4. Propagation Delay vs Temperature




Figure 5. OLH300 Switching Test Circuit




Figure 6. OLH300 Package Dimensions

Ordering Information

Model Name	Manufacturing Part Number
OLH300: High-Speed Hermetic Optocoupler	0LH300

Copyright © 2013-2017 Isolink, Inc. All Rights Reserved.

Information in this document is provided in connection with Isolink, Inc. ("Isolink"), a wholly-owned subsidiary of Skyworks Solutions, Inc. These materials, including the information contained herein, are provided by Isolink as a service to its customers and may be used for informational purposes only by the customer. Isolink assumes no responsibility for errors or omissions in these materials or the information contained herein. Isolink may change its documentation, products, services, specifications or product descriptions at any time, without notice. Isolink makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Isolink assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Isolink products, information or materials, except as may be provided in Isolink Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. ISOLINK DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. ISOLINK SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SLICH DAMAGE

Customers are responsible for their products and applications using Isolink products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Isolink assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Isolink products outside of stated published specifications or parameters.

Isolink is a trademark of Isolink Inc. in the United States and other countries. Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners.