

DATA SHEET

OLI149: Radiation Tolerant, Photo-Transistor Optocoupler

Features

- Radiation tolerant
- High current transfer ratio (CTR)—guaranteed over –55 °C to +100 °C ambient temperature range
- 1500 VDc electrical isolation
- High breakdown voltage, collector to emitter, base open (BVCEO), >60 V
- Small surface mount size

Description

The OL1149 is designed especially for high-reliability applications that require optical isolation in radiation environments such as gamma, neutron, and proton radiation with high CTR and low saturation V_{CE} .

Each optocoupler consists of an LED and N-P-N silicon phototransistor that is electrically isolated, but optically coupled on a ceramic Leadless Chip Carrier (LCC) surface mount package. The epoxy coating on the OLI149 allows the device to withstand normal solvent cleaning operations.

Surface mounting can be accomplished with either conductive epoxies or by reflow soldering.

Special electrical parametric selections are available upon request.



Figure 1. OLI149 Block Diagram

A functional block diagram of the OLI149 is shown in Figure 1. The absolute maximum ratings of the OLI149 are provided in Table 1. Electrical specifications are provided in Table 2.

Typical performance characteristics of the OLI149 are illustrated in Figures 2 and 3. A rise and fall time test circuit is shown in Figure 4, and package dimensions for the OLI149 are provided in Figure 5.

Table 1. OLI149 Absolute Maximum Ratings ¹

Parameter	Symbol	Minimum	Maximum	Units			
Coupled							
Input to output isolation voltage ²	VDC	-1500	+1500	V			
Storage temperature range	TSTG	-65	+150	٥C			
Operating temperature range	Та	-55	+125	°C			
Input Diode							
Average input current	IDD		40	mA			
Peak forward current	lF		60	mA			
Reverse voltage	VR		3	V			
Power dissipation	PD		70	mW			
Output Detector							
Collector to emitter voltage	VCE		60	V			
Power dissipation ³	PD		200	mW			

¹ Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to the device with only one parameter set at the limit and all other parameters set at or below their nominal value. Exceeding any of the limits listed in the above table may result in permanent damage to the device.

 2 Measured between LED pins shorted together, and output pins shorted together. TA = 25 °C and duration = 1 s.

³ Derate linearly at 2 mW/°C above 25 °C.

CAUTION: Although this device is designed to be as robust as possible, electrostatic discharge (ESD) can damage this device. This device must be protected at all times from ESD. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD precautions should be used at all times.

Table 2. OLI149 Electrical Specifications ¹ (TA = 25 °C, Unless Otherwise Noted)

Parameter	Symbol	Test Condition	Min	Max	Units
On-state collector current	Іс_ол	$I_F = 1 \text{ mA}, V_{CE} = 5 \text{ V}$	2	12	mA
		If = +2 mA, VCe = +5 V, Ta = -55 °C	+2.8		mA
		$I_F=2~mA,~V_{CE}=5~V,~T_A=100~^\circ C$	2		mA
Saturation voltage	VCE_SAT	$I_F = 2.0 \text{ mA}, I_C = 2.0 \text{ mA}$		0.3	V
Breakdown voltage:					
Collector to emitter	BVCEO	Ice = 1 mA	60		V
Emitter to collector	BVeco	$Iec = 100 \ \mu A$	5		V
Off-state leakage current collector to emitter	ICE_OFF	Vce = 20 V		100	nA
		$V_{CE} = 20 \text{ V}, \text{ Ta} = 100 \text{ °C}$		100	μA
Input:					
Forward voltage	VF	$I_F = +10.0 \text{ mA}, T_A = -55 \text{ °C}$	+1.6	+2.2	V
		IF = 10.0 mA	1.3	1.8	V
		$I_F = 10.0 \text{ mA}, T_A = 100 \text{ °C}$	1.2	1.6	V
Reverse current	IR	$V_R = 3 V$		100	μA
Output resistance ²	Ri_o	$V_{I-O} = \pm 1500 \text{ Vdc}$	1011		Ω
Time:					
Rise	tr	$Vcc = 10 \text{ V}, \text{ RL} = 100 \ \Omega$		25	μs
Fall	tr	lc = 2 mA		25	μs

¹ Performance is guaranteed only under the conditions listed in the above table.

 2 Measured between LED pins shorted together, and output pins shorted together. TA = 25 °C and duration = 1 s.

Typical Performance Characteristics

0.1

0.9 1.1



Figure 2. Forward Current vs Forward Voltage

1.3 1.5 1.7 Forward Voltage (V)

1.9 2.1



Figure 3. On-State Collector Current vs Temperature



Figure 4. OLI149 Rise and Fall Time Test Circuit



Figure 5. OLI149 Package Dimensions

Ordering Information

Model Name	Manufacturing Part Number
OLI149: Radiation Tolerant, Photo-Transistor Optocoupler	0LI149

Copyright © 2012, 2017 Isolink, Inc. All Rights Reserved.

Information in this document is provided in connection with Isolink, Inc. ("Isolink"), a wholly-owned subsidiary of Skyworks Solutions, Inc. These materials, including the information contained herein, are provided by Isolink as a service to its customers and may be used for informational purposes only by the customer. Isolink assumes no responsibility for errors or omissions in these materials or the information contained herein. Isolink may change its documentation, products, services, specifications or product descriptions at any time, without notice. Isolink makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Isolink assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Isolink products, information or materials, except as may be provided in Isolink Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. ISOLINK DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. ISOLINK SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Isolink products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Isolink products could lead to personal injury, death, physical or environmental damage. Isolink customers using or selling Isolink products for use in such applications do so at their own risk and agree to fully indemnify Isolink for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Isolink products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Isolink assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Isolink products outside of stated published specifications or parameters.

Isolink is a trademark of Isolink Inc. in the United States and other countries. Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners.