

DATA SHEET

OLI920: Hybrid Smart Photovoltaic Optocoupler

Features

- Isolated MOSFET/IGBT gate drive
- · Fast turn-off circuitry
- dV/dt protection circuitry
- Performance guaranteed over -55 °C to +125 °C ambient temperature range
- 2500 VDc electrical isolation
- High open-circuit voltage
- High short-circuit current
- Small size for hybrid assembly
- High reliability construction
- Radiation tolerant

Description

The OLI920 consists of a pair of LEDs that are optically coupled to a dielectrically isolated photovoltaic diode array, packaged on a thick film ceramic substrate. When the LED is energized, the infrared emission is detected by the photovoltaic array and a DC output voltage is generated. This electrically isolated voltage can be used to drive the gates of Metal Oxide Semiconductor (MOS) devices. Additional control circuitry provides fast turn-off, protection for false turn-on, and gate protection.

Surface mounting can be accomplished with conductive epoxies or reflow soldering.




Figure 1. OLI920 Block Diagram

Figure 1 shows the OLI920 functional block diagram. Table 1 provides the OLI920 absolute maximum ratings. Table 2 provides the OLI920 electrical specifications.

Figures 2 through 6 illustrate the OLI920 typical performance characteristics. Figure 7 shows the OLI920 package dimensions.

Table 1. OLI920 Absolute Maximum Ratings¹

Parameter	Symbol	Minimum	Maximum	Units
Coupled				
Input to output isolation voltage ²	Vdc	-1500	+1500	۷
Storage temperature range	Тята	-65	+150	٥°
Operating temperature range	Та	-55	+125	°C
Mounting temperature range (3 minutes maximum)			+240	٥°
Input Diode				
Average input current	lod		100	mA
Peak forward current (≤1 ms duration)	lF		180	mA
Reverse voltage	VR		5	۷
Power dissipation	Po		200	mW
Output Detector				
Forward voltage	VF		14	۷
Reverse voltage	VR		15	V

Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to the device with only one parameter set at the limit and all other parameters set at or below their nominal value. Exceeding any of the limits listed here may result in permanent damage to the device.

 2 Measured between LED pins shorted together and output pins shorted together. TA = 25°C and duration = 1 s.


ESD HANDLING: Although this device is designed to be as robust as possible, electrostatic discharge (ESD) can damage this device. This device must be protected at all times from ESD when handling or transporting. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD handling precautions should be used at all times.

Parameter	Symbol	Test Condition	Minimum	Typical	Maximum	Units
Open circuit voltage	Voc	IF = 10 mA	7.5	10		۷
Short circuit current	lsc	IF = 10 mA	-7	-20		μA
Input:						
Forward voltage	VF	$ I_F = 10 \text{ mA}, T_A = 25 \text{ °C} $ $ I_F = 10 \text{ mA}, T_A = -55 \text{ °C} $ $ I_F = 10 \text{ mA}, T_A = 125 \text{ °C} $	2.4 2.8 2.2	2.8	3.4 3.85 3.0	V V V
Reverse breakdown voltage	Bvr	$I_R = 10 \ \mu A$	5			V
Output leakage current ²	lı_o	R_{H} ${\leq}50\%,$ 1500 Vdc, T_{A} = 25 °C, Duration = 1 s			1	μA
Time:						
Turn-on	ton	$\label{eq:lf} \begin{array}{l} {\sf IF}=10 \mbox{ mA}, {\sf PW}=100 \mu {\sf s}, f=1 {\sf Hz}, C=15 pf, \\ {\sf TA}=25 \mbox{ °C}, {\sf R}_L=10 \Omega\Omega \end{array}$		60		μs
Turn-off	toff	ton = 0% to 90% toff = 100% to 10%		30		μs

Table 2. OLI920 Electrical Specifications¹ ($T_A = -55$ °C to +125 °C, Unless Otherwise Noted)

¹ Performance is guaranteed only under the conditions listed in the above table.

 2 Measured between LED pins shorted together and output pins shorted together. TA = 25°C and duration = 1 s.



Typical Performance Characteristics






Figure 4. Open Circuit Voltage vs Input Current




Figure 3. Short Circuit Current vs Input Current




Figure 5. Normalized Short Circuit Current vs Temperature




Figure 6: Open Circuit Voltage vs Temperature




Figure 7. OLI920 Package Dimensions

4

Ordering Information

Part Number	Product Description	Manufacturing Part Number
OLI920	Hybrid Smart Photovoltaic Optocoupler	0LI920

Copyright © 2014, 2017, 2019, 2022 Isolink, Inc. All Rights Reserved.

Information in this document is provided in connection with Isolink, Inc. ("Isolink"), a wholly-owned subsidiary of Skyworks Solutions, Inc. These materials, including the information contained herein, are provided by Isolink as a service to its customers and may be used for informational purposes only by the customer. Isolink assumes no responsibility for errors or omissions in these materials or the information contained herein. Isolink may change its documentation, products, services, specifications or product descriptions at any time, without notice. Isolink makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Isolink assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Isolink products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. ISOLINK DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. ISOLINK SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Isolink products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Isolink products could lead to personal injury, death, physical or environmental damage. Isolink customers using or selling Isolink products for use in such applications do so at their own risk and agree to fully indemnify Isolink for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using lsolink products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Isolink assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Isolink products outside of stated published specifications or parameters.

Isolink is a trademark of Isolink, Inc. in the United States and other countries. Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners.