

DATA SHEET

SKY66298-11: 900 to 990 MHz High-Efficiency 4 W Power Amplifier

Applications

- FDD and TDD 2G/3G/4G LTE systems
- 3GPP band 8 small-cell base stations
- Driver amplifier for micro-base and macro-base stations
- Active antenna array and massive MIMO


Features

- High efficiency: PAE = 40% @ +28 dBm
- High linearity: +28 dBm with < -50 dBc linearized ACLR (20 MHz LTE, 8.5 dB PAR signal)
- High gain: 34 dB
- ullet Excellent input and output return loss: to 50 Ω system
- Integrated active bias: performance compensated over temp
- Integrated enable On/Off function: PAEN = 1.7 to 2.5 V
- Single supply voltage: 5.0 V
- Pin-to-pin compatible PA family supporting all 3GPP bands
- Compact (16-pin, $5 \times 5 \times 1.3$ mm) package (MSL3, 260 °C per JEDEC J-STD-020)





Skyworks GreenTM products are compliant with all applicable legislation and are halogen-free. For additional information, refer to *Skyworks Definition of Green*TM, document number SQ04-0074.



Description

SKY66298-11 is a high-efficiency fully input/output matched power amplifier (PA) with high gain and linearity. The compact 5×5 mm PA is designed for FDD and TDD 2G/3G/4G LTE small cell base stations operating from 900 to 990 MHz. The active biasing circuitry is integrated to compensate PA performance over temperature, voltage, and process variation.

The SKY66298-11 is part of high efficiency, pin-to-pin compatible PA family supporting all 3GPP bands.

A block diagram of the SKY66298-11 is shown in Figure 1. The device package and pinout for the 16-pin device are shown in Figure 2. Table 1 lists the pin-to-pin compatible parts in the PA family. Signal pin assignments and functional pin descriptions are described in Table 2.

Table 1. Pin-to-Pin Compatible PA Family

Part Number	Frequency (MHz)	3GPP Band		
SKY66296-11	700 to 800	Bands 12, 13, 14, 17, 29, and 44		
SKY66289-11	750 to 850	Bands 20, 28, and 68		
SKY66295-11	800 to 900	Bands 5, 18, 19, 20, 26 and 27		
SKY66298-11	900 to 990	Band 8		
SKY66291-11	1805 to 1880	Bands 3 and 9		
SKY66299-11	1900 to 2000	Bands 2, 25, 33, 36, and 37		
SKY66294-11	2000 to 2300	Bands 1, 4, 10, and 23		
SKY66292-11	2300 to 2400	Bands 30 and 40		
SKY66297-11	2490 to 2690	Bands 7, 38, and 41		
SKY66293-21	3400 to 3600	CBRS, Bands 22, 42,43, and 48		
SKY66288-11	5150 to 5925	Band 46		




Figure 2. SKY66298-11 Pinout (Top View)

Table 2. SKY66298-11 Signal Descriptions¹

Pin	Name	Description	Pin	Name	Description
1	GND	Ground	9	RFOUT	RF output port
2	RFIN	RF input port	10	GND	Ground
3	GND	Ground	11	GND	Ground
4	GND	Ground	12	VCC3	Stage 3 collector voltage
5	VBIAS	Bias voltage	13	GND	Ground
6	PAEN	PA enable	14	N/U	Not used
7	GND	Ground	15	GND	Ground
8	GND	Ground	16	VCC1	Stage 1 collector voltage

¹ The center ground pad must have a low inductance and low thermal resistance connection to the application's printed circuit board ground plane.

Technical Description

The matching circuits are contained within the device. An on-chip active bias circuit is included within the device for both input and output stages, which provides excellent gain tracking over temperature and voltage variations.

The SKY66298-11 is internally matched for maximum output power and efficiency. The input and output stages are independently supplied using the VCC1 and VCC3 supply lines (pins 16 and 12, respectively). The DC control voltage that sets the bias is supplied by the VCBIAS signal (pin 5).

Electrical and Mechanical Specifications

The absolute maximum ratings of the SKY66298-11 are provided in Table 3. Recommended operating conditions are specified in Table 4 and electrical specifications are provided in Table 5.

DATA SHEET • SKY66298-11: 900 TO 990 MHz HIGH-EFFICIENCY 4 W POWER AMPLIFIER

Table 3. SKY66298-11 Absolute Maximum Ratings¹

Parameter	Symbol	Minimum	Maximum	Units
RF input power (CW,50 Ω load)	PIN		+8	dBm
Supply voltage (VCC1, VCC3, VBIAS)	Vcc		5.5	V
PA enable	VEN		3	V
Operating temperature	Tc	-40	+100	°C
Storage temperature	Тѕтс	-55	+125	°C
Junction temperature	TJ		+150	°C
Power dissipation	PD		1.2	W
Device thermal resistance	θυς		20.5	°C/W
Electrostatic discharge:				
Charged Device Model (CDM) Human Body Model (HBM)			500 1000	V V

Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to device with only one parameter set at the limit and all other parameters set at or below their nominal value. Exceeding any of the limits listed here may result in permanent damage to the device.

ESD HANDLING: Industry-standard ESD handling precautions must be adhered to at all times to avoid damage to this device.

Table 4. SKY66298-11 Recommended Operating Conditions

Parameter	Symbol	Min	Тур	Max	Units
Supply voltage (VCC1, VCC3, VBIAS)	VCC1, VCC3, VBIAS	4.75	5	5.25	V
PA enable:	PAEN				
ON OFF		1.7	2.0 0	2.5 0.5	V V
PA enable current	len		1	12	μΑ
Operating frequency	f	900		990	MHz
Operating temperature	Tc	-40	+25	+85	°C

Table 5. SKY66298-11 Electrical Specifications¹ (Vcc1 = Vcc3 = Vbias = 5 V, PAEN = 2.0 V, f = 942.5 MHz, Tc = +25 °C, Input/Output Load = 50 Ω , Unless Otherwise Noted)

Parameter	Symbol	Test Condition	Min	Тур	Max	Units
Frequency	f		925		960	MHz
Small signal gain	IS21I	PiN = -30 dBm	32.5	34		dB
Input return loss	IS11I	PIN = -20 dBm	9.5	16		dB
Output return loss	IS22I	Pin = -20 dBm	9.5	12.3		dB
Reverse isolation ²	IS12I	PiN = -30 dBm		55		dB
ACLR @ +28 dBm	ACLR	POUT = +28 dBm (20 MHz LTE, 8.5 dB PAR signal)		-29	-27	dBc
Saturated output power	PSAT	CW, PIN = +5 dBm	+34	+35		dBm
Output power at 3 dB gain compression	P3dB	CW	+32.8	+33.8		dBm
2 nd harmonic	2f0	CW, Pout = +28 dBm		-55	-40	dBc
3 rd harmonic	3f0	CW, Pout = +28 dBm		-75	-60	dBc
Power-added efficiency	PAE	CW, Pout = +28 dBm	31	34		%
Quiescent current	Iccq	No RF signal		85	105	mA

Performance is guaranteed only under the conditions listed in this table.

Evaluation Board Description

The SKY66298-11 Evaluation Board is used to test the performance of the SKY66298-11 PA. An Application schematic is provided in Figure 3. Table 6 provides the Bill of Materials (BOM) list for Evaluation Board components.

An assembly drawing for the Evaluation Board is shown in Figure 4. Layer details are shown in Figure 5. Layer details physical characteristics are noted in Figure 6.

Circuit Design Considerations

The following design considerations are general in nature and must be followed regardless of final use or configuration:

- Paths to ground should be made as short as possible.
- The ground pad of the SKY66298-11 has special electrical and thermal grounding requirements. This pad is the main thermal conduit for heat dissipation. Because the circuit board acts as the heat sink, it must shunt as much heat as possible from the device.

Therefore, design the connection to the ground pad to dissipate the maximum wattage produced by the circuit board. Multiple vias to the grounding layer are required.

NOTE: A poor connection between the ground pad and ground increases junction temperature (T_J), which reduces the life of the device.

Evaluation Board Test Procedure

Turn-On Sequence


- 1. Connect 50 Ω test equipment or load to the input and output RF ports of the Evaluation Board.
- 2. Connect the DC ground.
- 3. Connect all VCCs and VBIAS lines to a +5 V supply. Connect PAEN to a 2.0 V supply.
- Without applying RF, turn on the 5 V supply, then turn on the 2 V PAEN.
- Apply RF signal data at -30 dBm and observe that the gain of the device complies with the values in Table 5. Begin measurements.

Turn-Off Sequence

- 1. Turn off the RF input to the device.
- Turn off PAEN (set to 0 V).
- 3. Turn off all VCCs and VBIAS.

NOTE: It is important to adjust the VCC voltage sources so that +5 V is measured at the board. High collector currents drop the collector voltage significantly if long leads are used. Adjust the bias voltage to compensate.

² Not tested in production. Verified by design.




Note: The C1 component shown in this assembly is a 0 Ω resistor.

203647-003

Figure 3. SKY66298-11 Application Schematic

Table. 6. SKY66298-11 Evaluation Board Bill of Materials (BOM)

Component	Description	Size
C8, C12	Capacitor, optional 10 μF , 16 V, $\pm 10\%$, X7R	1206
C3, C4, C7, C11	Capacitor, ceramic, 3300 pF, X7R, ±10%, 50 V	0402
C6	Capacitor, ceramic, 100 pF	0402
L1, C9, C10	DNI	DNI
C1	Resistor, 0 Ω, jumper, 0.063 W	0402



- - 203647-004

Figure 4. Evaluation Board Assembly Drawing




Figure 5. Evaluation Board Layer Details

50 Ohm	Cross Section	Name	Thickness (mm)	Materials
W = 0.500 mm		TMask L1 Dielectric L2 Dielectric L3 Dielectric	0.010 0.035 0.250 0.035 0.350 0.035	Solder Resist Cu, 1 oz. R04350 Cu, 1 oz. FR4 Cu, 1 oz. FR4
		L4 BMask	0.035 0.010	Cu, 1 oz. Solder Resist

Figure 6. Layer Detail Physical Characteristics

203647-006

Application Circuit Notes

Center Ground. It is extremely important to sufficiently ground the bottom ground pad of the device for both thermal and stability reasons. Multiple small vias are acceptable and work well under the device if solder migration is an issue.

GND (pins 1, 3, 4, 7, 8, 10, 11, 13, and 15). Attach all ground pins to the RF ground plane with the largest diameter and lowest inductance via that the layout allows. Multiple small vias are acceptable and will work well under the device if solder migration is an issue.

VBIAS (pin 5). The bias supply voltage for each stage, nominally set to +5 V.

RFOUT (**pin 9**). Amplifier RF output pin (Zo = $50~\Omega$). The module includes an onboard internal DC blocking capacitor. All impedance matching is provided internal to the module.

VCC1 and **VCC3** (pin 16 and 12, respectively). Supply voltage for each stage collector bias is nominally set to 5 V. The evaluation board has inductors L1 and L2. These are place holders, and should be populated with 0 Ω resistors. Bypass and decoupling capacitors C6 through C12 should be placed in the approximate location shown on the evaluation board assembly drawing, although exact placement is not critical.

RFIN (pin 2). Amplifier RF input pin (Zo = 50 Ω). The module includes an onboard internal DC blocking capacitor. All impedance matching is provided internal to the module.

Package Dimensions

The typical part marking for the SKY66298-11 is shown in Figure 7. The PCB layout footprint for the SKY66298-11 is shown in Figure 8. Package dimensions are shown in Figure 9, and tape and reel dimensions are provided in Figure 10.

Package and Handling Information

Since the device package is sensitive to moisture absorption, it is baked and vacuum packed before shipping. Instructions on the shipping container label regarding exposure to moisture after the container seal is broken must be followed. Otherwise, problems related to moisture absorption may occur when the part is subjected to high temperature during solder assembly.

The SKY66298-11 is rated to Moisture Sensitivity Level 3 (MSL3) at 250 °C. It can be used for lead or lead-free soldering. For additional information, refer to Skyworks Application Note, *PCB Design and SMT Assembly/Rework Guidelines for MCM-L Packages*, document number 101752.

Care must be taken when attaching this product, whether it is done manually or in a production solder reflow environment. Production quantities of this product are shipped in a standard tape and reel format.





Figure 7. Typical Part Marking



Notes:

- 1. Thermal vias should be resin filled and capped in accordance with IPC-4761 type VII vias.
- 2. Recommended Cu thickness is 30 to 35 μm.

203647-008

Figure 8. SKY66298-11 PCB Layout Footprint





Figure 9. SKY66298-11 Package Dimensions



- 3. Cover tape shall be transparent conductive material.
- 4. ESD-surface resistivity shall be $\leq 1 \times 10^{10} \Omega$ /square per EJA, JEDEC TNR specification.
- 5. All measurements are in millimeters.

203647-010

Figure 10. SKY66298-11 Tape and Reel Dimensions

Ordering Information

Part Number	Product Description	Evaluation Board Part Number
SKY66298-11	900 to 990 MHz High-Efficiency 4 W Power Amplifier	SKY66298-11-EVB

Copyright © 2015, 2017-2018, 2022 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF STICH DAMAGE

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks, the Skyworks symbol, Sky5®, Sky0ne®, SkyBlueTM, Skyworks GreenTM, Clockbuilder®, DSPLL®, ISOmodem®, ProSLIC®, and SiPHY® are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.