

DATA SHEET

SKY73086-11: 650 – 900 MHz High Gain and Linearity Diversity Downconversion Mixer

Applications

- 2G/3G base station transceivers:
 GSM/EDGE, CDMA, UMTS/WCDMA
- Land mobile radio
- · High performance radio links

Features

• Operating frequency range: 650 to 900 MHz

• IF frequency range: 100 to 500 MHz

Conversion gain: 8.7 dB
Input IP3: +24.4 dBm
Output IP3: +33.1 dBm
Noise figure: 11 dB

Integrated LO drivers

- Integrated low loss RF baluns
- High linearity IF amplifiers
- On-chip SPDT LO switch (greater than 60 dB LO-to-LO isolation)
- Small, MCM (36-pin, 6 x 6 mm) Pb-free package (MSL3, 260 °C per JEDEC J-STD-020)



Skyworks GreenTM products are compliant with all applicable legislation and are halogen-free. For additional information, refer to *Skyworks Definition of Green*TM, document number SQ04-0074.

Description

The SKY73086-11 is a fully integrated diversity mixer that includes Local Oscillator (LO) drivers, an LO switch, high linearity mixers, and large dynamic range Intermediate Frequency (IF) amplifiers. Low loss RF baluns have also been included to reduce design complications and lower system cost.

The StV73086-11 reatures an input IP3 of \pm 24.4 dBm and a Noise Figure (NF) of 11 dB, making the device an ideal solution for high dynamic range systems such as 2G/3G base station receivers. The LO switch provides more than 60 dB of isolation between LO inputs and supports the switching time required for GSM/EDGE base stations.

The SKY73086-11 is manufactured using a robust silicon BiCMOS process and has been designed for optimum long-term reliability. The SKY73086-11 diversity downconversion mixer is provided in a compact, 36-pin Multi-Chip Module (MCM). A functional block diagram is shown in Figure 1. The pin configuration and package are shown in Figure 2. Signal pin assignments and functional pin descriptions are provided in Table 1.




Figure 1. SKY73086-11 Block Diagram




Figure 2. SKY73086-11 Pinout – 36-Pin MCM (Top View)

Table 1. SKY73086-11 Signal Descriptions

Pin#	Name	Description	Pin#	Name	Description
1	RFA	RF channel A input	19	L01	Local oscillator #1 input
2	N/C	No connect	20	GND	Ground
3	GND	Ground	21	VCC_LOIN	DC supply, +5 V
4	VCC_LO	DC supply, +5 V	22	GND	Ground
5	GND	Ground	23	LO_SEL	Local oscillator switch select
6	VCC_LO	DC supply, +5 V	24	GND	Ground
7	GND	Ground	25	GND	Ground
8	N/C	No connect	26	GND	Ground
9	RFB	RF channel B input	27	L02	Local oscillator #2 input
10	VCC_RFB	DC supply, +5 V	28	N/C	No connect
11	N/C	No connect	29	RIFA	IF channel A bias control
12	GND	Ground	30	VCC_IFA	DC supply, +5 V
13	IFB+	IF channel B positive output	31	N/C	No connect
14	IFB-	IF channel B negative output	32	IFA+	IF channel A positive output
15	N/C	No connect	33	IFA-	IF channel A negative output
16	VCC_IFB	DC supply, +5 V	34	GND	Ground
17	RIFB	IF channel B bias control	35	N/C	No connect
18	N/C	No connect	36	VCC_RFA	DC supply, +5 V

Functional Description

The SKY73086-11 is a high gain diversity mixer, optimized for base station receiver applications. The device consists of two diversity channels, each consisting of a low loss RF balun, high linearity passive mixer, and a low noise IF amplifier.

LO amplifiers are also included that allow the SKY73086-11 to connect directly to the output of a Voltage Controlled Oscillator (VCO). This eliminates the extra gain stages needed by most discrete passive mixers. A Single Pole, Double Throw (SPDT) switch has been included to select between two different LO inputs for frequency hopping applications (i.e., GSM).

RF Baluns and Passive Mixer

The RF baluns provide a single ended input, which can easily be matched to 50 Ω using a simple matching circuit. The RF baluns offer very low loss and excellent amplitude and phase balance.

The high linearity mixer is a passive, double balanced mixer that provides a very low insertion loss, and excellent 3° Order Input Insertion Point (IIP3) and linearity performance

Additionally, the balanced nature of the mixer provides for excellent port-to-port isolation.

LO Buffers and SPDT LO Switch

The LO buffers allow the input power of the SKY73086-11 to be programmed in the range of –6 to +6 dBm. The LO section has been optimized for high-side LO injection. However, the LO can be driven over a wide frequency range with only slight degradation in performance.

A high isolation SPDT switch allows the SKY73086-11 to be used for frequency hopping applications. This switch provides greater than 60 dB of LO1 to LO2 isolation:

LO_SEL Logic:	State:
High	LO1 enabled
Low	LO2 enabled

For applications that do not require frequency hopping, LO_SEL is fixed to one state and the appropriate LO input is used.

IF Amplifier

The SKY73086-11 includes high dynamic range IF amplifiers that follow the passive mixers in the signal path. The outputs require a supply voltage connection using inductive chokes. These choke inductors should be high-Q and have the ability to handle 200 mA or greater.

A simple matching network allows the output ports to be matched to a balanced 200 Ω impedance. The IF amplifiers are optimized for IF frequencies between 100 and 500 MHz. The IF amplifiers can be operated outside of this range, but with a slight degradation in performance.

Electrical and Mechanical Specifications

The absolute maximum ratings of the SKY73086-11 are provided in Table 2. The recommended operating conditions are specified in Table 3 and electrical specifications are provided in Table 4.

Table 2. SKY73086-11 Absolute Maximum Ratings

	-				
Parameter	Symbol	Minimum	Typical	Maximum	Units
Supply voltage, +5 V (VCC_LO, VCC_RFB, VCC_IFB, VCC_LOIN, VCC_IFA, VCC_RFA)	VCC	4.5	5.0	5.5	V
Supply current	Icc		370	430	mA
RF input power	Pre			+20	dBm
L0 input power	PLO		0	+20	dBm
Operating case temperature	Tc	-40		+85	°C
Junction temperature	TJ			+150	°C
Storage case temperature	Тѕтс	-40		+125	°C

Notes: Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to device with only one parameter set at the limit and all other parameters set at or below their nominal value.

Nominal thermal resistance (junction to center ground pad) is 5.1 $^{\circ}$ C/W.

CAUTION: Although this device is designed to be as robust as possible, Electrostatic Discharge (ESD) can damage this device. This device must be protected at all times from ESD. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD precautions should be used at all times.

Table 3. SKY73086-11 Recommended Operating Conditions (Note 1)

Parameter	Symbol	Minimum	Typical	Maximum	Units
Supply voltage, +5 V (VCC_LO, VCC_RFB, VCC_IFB, VCC_LOIN, VCC_IFA, VCC_RFA)	VCC	4.75	5.00	5.25	V
Supply current	Icc		370		mA
RF frequency range	FRF	650		900	MHz
L0 frequency range (Note 1)	FLO	750		1400	MHz
IF frequency range	Fif	100		500	MHz
LO input power	PLO	-6	0	+6	dBm
LO select logic: high low	LO_SELH LO_SELL	2.2	7	0.8	V V
Operating case temperature	Tc	-40	(Q;	+85	°C

Note 1: The SKY73086-11 has been optimized for high-side LO injection. However, the LO can be used outside of the specified frequency range with degraded performance.

Table 4. SKY73086-11 Electrical Specifications (1 of 2) (Note 1) (Voltage Supply = +5 V, $T_c = +25$ °C, LO = 0 dBm, RF Frequency = 750 MHz, IF Frequency = 450 MHz, LO Frequency = 1200 MHz, Unless Otherwise Noted)

Parameter	Symbol	Test Condition	Min	Typical	Max	Units
Conversion gain	G ($F_{RE} = 750 \text{ MHz}$ VCC = 4.75 to 5.25 V, $P_{L0} = -3 \text{ to } +3 \text{ dBm}$	7.5	8.7		dB
Noise Figure	NF	Fre = 750 MHz		11		dB
Noise Figure with a blocker signal	NFBLK	Blocking signal input power = +8 dBm			25	dB
Third order input intercept point	IIP3	$F_{RF} = 750 \text{ and } 750.8 \text{ MHz}, \\ P_{RF} = -10 \text{ dBm/each tone}, \\ VCC = 4.75 \text{ to } 5.25 \text{ V}, \\ P_{L0} = -3 \text{ to } +3 \text{ dBm}$		+24.4		dBm
Third order output intercept point	OIP3	$F_{RF} = 750 \text{ and } 750.8 \text{ MHz}, \\ P_{RF} = -10 \text{ dBm/each tone}, \\ VCC = 4.75 \text{ to } 5.25 \text{ V}, \\ P_{L0} = -3 \text{ to } +3 \text{ dBm}$		+33.1		dBm
2RF – 2L0	2x2	P _{RF} = −10 dBm		-80		dBc
3RF – 3L0	3x3	PRF = −10 dBm		-90		dBc
4RF – 3LO, spurious	4x3	Prf = 0 dBm		-92		dBc
2RF – 1LO, spurious	2x1	Prf = 0 dBm		-56		dBc
4RF – 2LO, spurious	4x2	Prf = 0 dBm		-95		dBc
Input 1 dB compression point	IP1dB		+9.5			dBm
LO1 to LO2 isolation		Frf = 900 MHz, Flo = 1250 MHz		55		dB
Channel-to-channel isolation		F _{RF} = 900 MHz, F _{L0} = 1250 MHz		35		dB
RF to IF isolation		Frf = 900 MHz		33		dB

Table 4. SKY73086-11 Electrical Specifications (2 of 2) (Note 1) (Voltage Supply = +5 V, $T_c = +25$ °C, LO = 0 dBm, RF Frequency = 750 MHz, IF Frequency = 450 MHz, LO Frequency = 1200 MHz, Unless Otherwise Noted)

Parameter	Symbol	Test Condition	Min	Typical	Max	Units
L0 leakage:		Frf = 350 MHz,				
1xLO to RF port		FL0 = 440 MHz		-32		dBm
2xL0 to RF port				-33		dBm
3xL0 to RF port				- 74		dBm
4xL0 to RF port				- 67		dBm
1xLO to IF port				-26		dBm
LO_SEL input			-20	+150	+250	μА
L0 switching time					1.0	μS
RF port input return loss	ZIN_RF	With external matching components	.014			dB
LO port input return loss	ZIN_LO	With external matching components	14			dB
IF port input return loss	Zout_if	With external matching components	14			dB

Note 1: Performance is guaranteed only under the conditions listed in this Table

Evaluation Board Description

The SKY73086-11 Evaluation Board is used to test the performance of the SKY73086-11 downconversion mixer. An assembly drawing for the Evaluation Board is shown in Figure 3 and the layer detail is provided in Figure 4. A schematic diagram of the SKY73086-11 Evaluation Board is shown in Figure 5.

Circuit Design Considerations

The following design considerations are general in nature and must be followed regardless of final use or configuration:

- 1. Paths to ground should be made as short as possible.
- The ground pad of the SKY73086-11 has special electrical and thermal grounding requirements. This pad is the main thermal conduit for heat dissipation. Since the circuit board acts as the heat sink, it must shunt as much heat as possible from the device. Therefore, design the connection to the ground pad to dissipate the maximum wattage produced by the circuit board.
- 3. Skyworks recommends including external bypass capacitors on the VCC voltage inputs of the device.
- Components L5, L6, L14, and L15 (see Figure 5) are high-Q low loss inductors. These inductors must be able to pass currents in excess of 200 mA DC.
- 5. Components R1 and R2 (see Figure 5) set the bias current for the IF amplifiers. Skyworks recommends that these resistors have a tolerance of $\pm 1\%$ to optimize performance consistency of the SKY73086-11. These resistors are not required for the Evaluation Board to operate as specified in Tables 3 and 4.

Package Dimensions

The PCB layout footprint for the SKY73086-11 is provided in Figure 6. Figure 7 shows the package dimensions for the 36-pin MCM and Figure 8 provides the tape and reel dimensions.

Package and Handling Information

Since the device package is sensitive to moisture absorption, it is baked and vacuum packed before shipping. Instructions on the shipping container label regarding exposure to moisture after the container seal is broken must be followed. Otherwise, problems related to moisture absorption may occur when the part is subjected to high temperature during solder assembly.

THE SKY73086-11 is rated to Moisture Sensitivity Level 3 (MSL3) at 260 °C. It can be used for lead or lead-free soldering. For additional information, refer to the Skyworks Application Note, *PCB Design & SMT Assembly/Rework Guidelines for MCM-L Packages*, document number 101752.

Care must be taken when attaching this product, whether it is done manually or in a production solder reflow environment. Production quantities of this product are shipped in a standard tape and reel format.




Figure 3. SKY73086-11 Evaluation Board Assembly Diagram




Figure 4. SKY73086-11 Evaluation Board Layer Detail




Figure 5. SKY73086-11 Evaluation Board Schematic




Figure 6. PCB Layout Footprint for the SKY73086-11 6 x 6 mm MCM





Figure 7. SKY73086-11 36-Pin MCM Package Dimensions



For all other 6 x 6 mm MCM/RFLGA products, pin 1 orientation is in top right corner.

S1183

Figure 8. SKY73086-11 Tape and Reel Dimensions

Ordering Information

Model Name	Manufacturing Part Number	Evaluation Board Part Number		
SKY73086-11 650-900 MHz Downconversion Mixer	SKY73086-11	TW17-D890		



Copyright © 2009, 2011, 2019 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks, the Skyworks symbol, and "Breakthrough Simplicity" are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.