

## PRODUCT SUMMARY

# SKY66398-11: 2496 to 2690 MHz Wide Instantaneous Bandwidth High-Efficiency Power Amplifier

## Applications


- High efficiency (DPD) power amplifier for 5G Small Cells
- Driver Amplifier for micro, macro and massive MIMO base stations

## Features

- High power: +30 dBm
- Wide bandwidth: > 100 MHz
- Single 5 V supply voltage and on-chip active temperature compensated bias circuit
- High efficiency
- High Gain
- Integrated enable On/Off function: PAEN = 1.5 V to 2.5 V
- Compact (20-pin, 8 × 8 × 1.3 mm) package (MSL3, 260 °C per JEDEC J-STD-020)
- Pin-to-pin compatible PA family supporting key 5G bands



Skyworks Green™ products are compliant with all applicable legislation and are halogen-free. For additional information, refer to *Skyworks Definition of Green™*, document number SQ04-0074.



**Figure 1. SKY66398-11 Block Diagram**

## Description

The SKY66398-11 is a +30 dBm high-efficiency power amplifier (PA) with high gain and linearity. The SKY66398-11 only requires a single 5 V supply and has integrate active biasing circuit to compensate PA performance over temperature, voltage and process variation.

A block diagram of the SKY66398-11 is shown in Figure 1. The SKY66398-11 is part of a pin-to-pin compatible family of PAs, see Table 1.

**Table 1. Pin-to-Pin Driver PA Family**

Part Number	Frequency (MHz)	3GPP / 5G Band
SKY66398-11	2496 to 2690	B7, B38, B41
SKY66395-11	4800 to 5000	n79
SKY66392-11	3400 to 3600	n78

## Ordering Information

Part Number	Product Description	Evaluation Board Part Number
SKY66398-11	2496 to 2690 MHz Wide Instantaneous High-Efficiency PA	SKY66398-11EK1

Copyright © 2022 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks, the Skyworks symbol, Sky5®, SkyOne®, SkyBlue™, Skyworks Green™, Clockbuilder®, DSPLL®, ISOModem®, ProSLIC®, and SiPHY® are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at [www.skyworksinc.com](http://www.skyworksinc.com), are incorporated by reference.