

PRODUCT SUMMARY

SKY96503-11: 0.4 to 2.7 GHz LTE Diversity Receive Module with MIPI® RFFE Interface

Applications

- 2G/3G/4G multimode cellular tablets and handsets (GSM, EDGE, LTE, UMTS, CDMA2000)
- Embedded data cards

Features

- Broadband frequency range: 0.4 to 2.7 GHz
- Low insertion loss, 0.6 dB typical @ 2.7 GHz
- High isolation and linearity
- Integrated, programmable MIPI Version 2.0 interface
- Multi-ON switch technology to enable carrier aggregation
- High-performance TC-SAW filter technology
- Carrier aggregation support for B1+B3+B26/B8, B34+B39+B41N, B1+B3+B40, and B1+B3+B41N
- Six linear AUX ports with isolation greater than 20 dB @ 2.7 GHz:
 - AUX2, AUX3, and AUX4 (400 to 800 MHz)
 - AUX1, AUX5, and AUX6 (1800 to 2700 MHz)
- Small QFN (24-pin, 3.5 x 3.0 x 0.65 mm) package (MSL3, 260 °C per JEDEC J-STD-020)
- Rx Diversity FEM with the following integrated bands:
 - B8 (925 to 960 MHz)
 - B26 (869 to 894 MHz)
 - B3 (1805 to 1880 MHz)
 - B39 (1880 to 1920 MHz)
 - B1 (2110 to 2170 MHz)
 - B34 (2010 to 2025 MHz)
 - B41N (2535 to 2655 MHz)
 - B40 (2300 to 2400 MHz)
- For RoHS and other product compliance information, see the [Skyworks Certificate of Conformance](#)

Description

The SKY96503-11 is a single-pole, thirteen-throw (SP13T) antenna switch module with integrated filters and a Mobile Industry Processor Interface (MIPI), Version 2.0. Receive filters for bands 8, 26, 3, 39, 1, 34, 41N, and 40 are integrated into the module.

Using advanced switching technologies, the SKY96503-11 maintains low insertion loss and high isolation for receive switching paths. The high-linearity performance and low insertion loss achieved by the SKY96503-11 makes it an ideal choice for UMTS, CDMA2000, and LTE applications.

Switching is controlled by an integrated MIPI interface. Depending on the logic applied to the decoder, the antenna pin is connected to up to 2 of 13 switched RF ports using a low insertion loss path, while the paths between the antenna pin and the other RF pins are in a high isolation state. No external DC blocking capacitors are required on the RF paths.

The SKY96503-11 is manufactured in a compact, 3.5 x 3.0 x 0.65 mm, 24-pin surface-mount Quad Flat No-Lead (QFN) package.

Ordering Information

Part Number	Description	Evaluation Board Part Number
SKY96503-11	LTE Diversity Receive Module with MIPI RFFE Interface	SKY96503-11EK1



Copyright © 2019, 2024, 2026, Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc., and its subsidiaries (“Skyworks”) products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks’ Terms and Conditions of Sale.

THE INFORMATION IN THIS DOCUMENT AND THE MATERIALS AND PRODUCTS DESCRIBED THEREIN ARE PROVIDED “AS IS” WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not designed, intended, authorized, or warranted for use or inclusion in life support or life endangering applications, devices, or systems where failure or inaccuracy might cause death or personal injury. Skyworks customers agree not to use or sell the Skyworks products for such applications, and further agree to, without limitation, fully defend, indemnify, and hold harmless Skyworks and its agents from and against any and all actions, suits, proceedings, costs, expenses, damages, and liabilities including attorneys’ fees arising out of or in connection with such improper use or sale.

Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of Skyworks’ published specifications or parameters. Customers are solely responsible for their products and applications using the Skyworks products.

“Skyworks” and the Skyworks Starburst logo are registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.