

DATA SHEET

PIN Diode Chips Supplied on Film Frame

Applications

- Switches
- Attenuators

Features

- Preferred device for module applications
- PIN diodes supplied are 100% tested, saw cut, and mounted on film frame
- Low cost
- For RoHS and other product compliance information, see the Skyworks Certificate of Conformance.

Description

The PIN diodes that comprise this family of diodes supplied on film frames are designed for high-volume applications from 10 MHz to over 3 GHz. This family contains three groups of PIN diodes:

1. Low-capacitance, low-resistance PIN diodes designed primarily for RF switching applications:
 - SMP1320-099
 - SMP1321-099
 - SMP1322-099
 - SMP1340-099
2. PIN diodes with mid-range I-layers and resistance designed for either RF switching or attenuator applications:
 - SMP1302-099
 - SMP1331-099
 - SMP1353-099
3. PIN diodes with thick I-layers designed for low-distortion RF variable attenuator applications:
 - SMP1304-099
 - SMP1307-099

These PIN diodes are provided as 100 percent tested, diced wafers mounted on film frames for optimal compatibility with high-volume pick-and-place assembly techniques.

Absolute maximum ratings are provided in Table 1. Electrical specifications are provided in Table 2. Chip dimensions are shown in Table 3. Typical performance characteristics are illustrated in Figures 1 through 5. Figure 6 describes the wafer film frame.

Table 1. PIN Diode Chips Absolute Maximum Ratings¹

Parameter	Symbol	Minimum	Maximum	Units
Reverse voltage	VR		Voltage rating	V
Maximum junction temperature	TJ		+175	°C
Operating temperature	TOP	–65	+150	°C
Storage temperature	TSTG	–65	+150	°C
Electrostatic discharge: Human Body Model (HBM), Class 1C	ESD		1000	V

¹ Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to device with only one parameter set at the limit and all other parameters set at or below their nominal value.

ESD HANDLING: Industry-standard ESD handling precautions should be used at all times to prevent damage to this device.

Table 2. PIN Diode Chips Electrical Specifications¹

(TOP = 25 °C)

Part Number	I Region (μm) Nominal	Voltage Rating (V)	CJ (pF) VR = 30 V, f = 1 MHz	Typ VF (mV) @ IF = 10 mA	Max Rs (Ω) IF = 1 mA, f = 100 MHz	Max Rs (Ω) IF = 10 mA, f = 100 MHz	Typ TL (ns) IF = 10 mA	Application
SMP1302-099	50	200	0.12 typ 0.15 max	800	13.5 min 17 typ 21.5 max	3	700	Switch and attenuator
SMP1304-099	100	200	0.07 typ 0.15 max	800	30 min 37 typ 50 max	7	1000	Attenuator
SMP1307-099	175	200	0.08 typ 0.20 max	850	60 min 75 typ 100 max	15	1500	Attenuator
SMP1320-099	7	50	0.12 typ 0.175 max	850	2 typ	0.9	400	Switch
SMP1321-099	12	100	0.07 typ 0.15 max	860	3 typ	2.0	400	Switch
SMP1322-099	7	50	0.66 typ 0.85 max	825	1.5	0.45 typ	400	Switch
SMP1331-099	30	200	0.13 typ 0.16 max	800	14.5	1.7 typ	600	Switch and attenuator
SMP1340-099	5	50	0.10 typ @ 10 V 0.15 max @ 10 V	880	1.7 typ	1.2	100	Switch
SMP1353-099	50	200	0.08 typ @ 20 V 0.13 max @ 20 V	850	15	2.8	2000	Switch and attenuator

¹ Performance is guaranteed only under the conditions listed in this table.

Reverse current is specified @ 10 μA maximum at the voltage rating. This voltage should not be exceeded.

The PIN diodes listed here are processed on 100 mm silicon wafers, 100% DC tested, saw cut, and shipped on 6-inch film frame hoops.

Electrical rejects are identified with black ink on the film frame.

Attenuators are 100% series resistance tested @ 1 mA/100 MHz.

Table 3. PIN Diode Chip Dimensions

Part Number	Quantity of Good Diodes Per Wafer		Chip Size (In)	Chip Height (In)	Anode Contact (In)
	Minimum	Nominal			
SMP1302-099	40000	46000	0.0135 ± 0.001	0.005 ± 0.001	0.0085 ± 0.0005
SMP1304-099	40000	46000	0.0135 ± 0.001	0.009 ± 0.001	0.0085 ± 0.0005
SMP1307-099	20000	25000	0.0185 ± 0.001	0.009 ± 0.001	0.0110 ± 0.0005
SMP1320-099	40000	46000	0.0135 ± 0.001	0.005 ± 0.001	0.0030 ± 0.0003
SMP1321-099	40000	46000	0.0135 ± 0.001	0.005 ± 0.001	0.0030 ± 0.0003
SMP1322-099	40000	46000	0.0135 ± 0.001	0.005 ± 0.001	0.0075 ± 0.0005
SMP1331-099	40000	46000	0.0135 ± 0.001	0.005 ± 0.001	0.0075 ± 0.0005
SMP1340-099	65000	72000	0.0105 ± 0.001	0.005 ± 0.001	0.0029 ± 0.0003
SMP1353-099	65000	72000	0.0105 ± 0.001	0.005 ± 0.001	0.0070 ± 0.0005

DISCONTINUED

Typical Performance Characteristics (TOP = 25 °C)




Figure 1. Series Resistance vs Forward Current @ 1 MHz




Figure 2. Series Resistance vs Forward Current @ 100 MHz




Figure 3. Capacitance vs Reverse Voltage @ 1 MHz




Figure 4. Capacitance vs Reverse Voltage @ 1 MHz




Figure 5. Capacitance vs Reverse Voltage @ 1 MHz




Figure 6. Wafer Film Frame Description



Copyright © 2002-2008, 2011-2013, 2015-2016, 2025, Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc., and its subsidiaries ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks' Terms and Conditions of Sale.

THE INFORMATION IN THIS DOCUMENT AND THE MATERIALS AND PRODUCTS DESCRIBED THEREIN ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not designed, intended, authorized, or warranted for use or inclusion in life support or life endangering applications, devices, or systems where failure or inaccuracy might cause death or personal injury. Skyworks customers agree not to use or sell the Skyworks products for such applications, and further agree to, without limitation, fully defend, indemnify, and hold harmless Skyworks and its agents from and against any and all actions, suits, proceedings, costs, expenses, damages, and liabilities including attorneys' fees arising out of or in connection with such improper use or sale.

Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of Skyworks' published specifications or parameters. Customers are solely responsible for their products and applications using the Skyworks products.

"Skyworks" and the Skyworks Starburst logo are registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.