

# **DATA SHEET**

# SKY65981-11: 5 GHz, 802.11ac/n Low-Noise Amplifier

## **Applications**


- IEEE 802.11ac/n WLANs
- 5 GHz ISM radios
- SmartPhones
- Notebooks, netbooks, tablets
- Access points, routers, gateways
- · Wireless video systems


# **Features**

- Ultra-low Noise Figure
- 4.9 GHz to 5.9 GHz operation
- Enable/disable/bypass modes
- High IIP3
- High gain
- 2.8 V to 3.6 V single-supply operation
- QFN (6-pin, 1.5 x 1.5 mm) package (MSL1, 260 °C per JEDEC J-STD-020)



Skyworks Pb-free products are compliant with all applicable legislation. For additional information, refer to *Skyworks Definition of Lead (Pb)-Free*, document number SQ04-0073.






## **Description**

The SKY65981-11 is an ultra Low-Noise Amplifier (LNA) intended for 5 GHz, IEEE 802.11ac/n wireless receiver applications. Its industry-leading Noise Figure (NF), together with high linearity, make it ideal as a first-stage LNA in IEEE 802.11ac/n Wireless Local Area Network (WLAN) radios.

Operating with a single supply voltage, the SKY65981-11 consumes only 12 mA of current. The device includes a bypass mode for near field applications and to save power when the receiver is inactive.

The tiny package footprint of the SKY65981-11, requiring only four external components, enables the industry's smallest PCB area needed to implement a fully-matched 5 GHz LNA.

A block diagram of the SKY65981-11 is shown in Figure 1. The device package and pinout for the 6-pin Quad Flat No-Lead (QFN) are shown in Figure 2.





## **Technical Description**

The SKY65981-11 is fully matched at 50  $\Omega$  and requires only a simple bypass circuit on pin 6 (VCC). The bypass/shutdown mode is achieved by switching the LNA\_EN signal (pin 1) to 0 V.

## **Package and Handling Information**

Instructions on the shipping container label regarding exposure to moisture after the container seal is broken must be followed. Otherwise, problems related to moisture absorption may occur when the part is subjected to high temperature during solder assembly.

The SKY65981-11 is rated to Moisture Sensitivity Level 1 (MSL1) at 260 °C. It can be used for lead or lead-free soldering. For additional information, refer to the Skyworks Application Note, *Solder Reflow Information*, document number 200164.

Care must be taken when attaching this product, whether it is done manually or in a production solder reflow environment.

Production quantities of this product are shipped in a standard tape and reel format.

## **Electrical and Mechanical Specifications**

Signal pin assignments and functional pin descriptions are described in Table 1. The absolute maximum ratings of the SKY65981-11 are provided in Table 2. The recommended operating conditions are specified in Table 3 and electrical specifications are provided in Table 4.

Performance characteristics for the SKY65981-11 are illustrated in Figures 3 through 9.

An application schematic diagram for the SKY65981-11 is shown in Figure 10. The PCB footprint drawing for the SKY65981-11 is provided in Figure 11. Typical part markings are shown in Figure 12. The package dimensions for the 6-pin QFN are shown in Figure 13, and the tape and reel dimensions are provided in Figure 14.

#### Table 1. SKY65981-11 Signal Descriptions

| Pin | Name          | Description   |  |
|-----|---------------|---|--|
| 1   | LNA_EN/BYPASS | LNA enable (when pulled high) or bypass (when pulled low) control input |  |
| 2   | RF_IN         | LNA RF input  |  |
| 3   | GND           | Ground  |  |
| 4   | GND           | Ground  |  |
| 5   | RF_OUT        | LNA RF output   |  |
| 6   | VCC           | Supply voltage for LNA  |  |

#### Table 2. SKY65981-11 Absolute Maximum Ratings (Note 1)

| Parameter                   | Symbol   | Minimum | Maximum | Units |
|-----------------------------|----------|---------|---------|-------|
| Supply voltage              | VCC      | 0       | 3.6     | V     |
| DC voltage at control ports | VENABLE  | 0       | 3.6     | V     |
| Power into LNA inputs       | Pin, LNA |         | +10     | dBm   |
| Operating temperature       | Та       | -40     | +85     | °C    |
| Storage temperature         | Тѕтс     | -40     | +125    | °C    |

Note 1: Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to device with only one parameter set at the limit and all other parameters set at or below their nominal values. Exceeding any of the limits listed here may result in permanent damage to the device.

**CAUTION**: Although this device is designed to be as robust as possible, Electrostatic Discharge (ESD) can damage this device. This device must be protected at all times from ESD. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD precautions should be used at all times.

3.6

0.2

Units V GHz °C

۷

۷

| Parameter                   | Symbol | Minimum | Typical | Maximum |  |
|-----------------------------|--------|---------|---------|---------|--|
| Supply voltage              | VCC    | 0       |         | 3.6     |  |
| RF frequency range          | f      | 5.15    |         | 5.85    |  |
| Operating temperature range | Та     | -40     |         | +85     |  |

1.8

0

#### Table 3. SKY65981-11 Recommended Operating Conditions (@ +25 °C, VCC = 3.3 V)

Table 4. SKY65981-11 Electrical Characteristics (Note 1) (VCC = 3.3 V, Ta =  $+25 \degree$ C, f = 5.15 to 5.85 GHz, Venable = 3.3 V, Unless Otherwise Noted)

VENABLE\_H

VENABLE\_L

| Parameter  | Symbol    | Test Conditions       | Minimum | Typical | Maximum | Units |
|--|-----------|-----------------------|---------|---------|---------|-------|
| Enable Mode (LNA_EN = 3.3 V)   |           |                       |         | l       | 4       | L     |
| Gain   | S21       |                       | 11      | 13      |         | dB    |
| Gain flatness across 80 MHz channel  | S21       |                       |         | 0.5     |         | dB    |
| Out-of-band gain @ 2.462 GHz   | S21_2.462 |                       |         | -6      |         | dB    |
| Noise Figure   | NF        |                       |         | 1.5     | 1.7     | dB    |
| 3rd Order Input Intercept Point  | IIP3      |                       |         | +7      |         | dBm   |
| In-band 1 dB compression point at input                                    | IP1dB     |                       |         | -1.5    |         | dBm   |
| Out-of-band (2.462 GHz injected signal)<br>1 dB compression point at input | IP1dB     |                       |         | +3      |         | dBm   |
| Input return loss  | S11       | $Z_{S/L} = 50 \Omega$ | 7       |         |         | dB    |
| Output return loss   | IS221     | Zs/L = 50 Ω           | 10      |         |         | dB    |
| Reverse isolation  | S12       |                       |         | -20     |         | dB    |
| Maximum RF input (compliant)   |           |                       |         | -10     |         | dBm   |
| Maximum RF input (no damage)   |           |                       |         | +10     |         | dBm   |
| Drain current  | ISUBCC    |                       |         | 12      | 15      | mA    |
| Control enable current   | len       |                       |         |         | 100     | μA    |
| Bypass Mode (LNA_EN = 0 V)   |           |                       |         |         |         |       |
| Gain   | S21       |                       |         | -7      |         | dB    |
| Gain flatness across 80 MHz channel  | S21       |                       |         | 0.5     |         | dB    |
| Noise Figure   | NF        |                       |         | 7       |         | dB    |
| 1 dB Input Compression Point   | IP1dB     |                       |         | +18.5   |         | dBm   |
| Input return loss  | S11       |                       | 7       |         |         | dB    |
| Output return loss   | IS221     |                       | 12      |         |         | dB    |
| Maximum RF input with harmonic<br>< –50 dBm/MHz (Note 2)                   |           |                       |         |         | +11     | dBm   |
| Switching speed: LNA to bypass mode and bypass mode to LNA                 | ts        |                       |         |         | 300     | ns    |

Note 1: Performance is guaranteed only under the conditions listed in this Table.

Note 2: Harmonic leakage is measured at RF\_IN port.

DC voltage at control port:

High

Low

## **Typical Performance Characteristics**

(Vcc = 3.3 V, TA = +25 °C, f = 4.90 to 5.85 MHz, VENABLE = 3.3 V, Unless Otherwise Noted)




Figure 3. Broadband S-Parameters vs Frequency ("On" State)




Figure 5. Broadband S-Parameters vs Frequency (Bypass Mode)




Figure 7. Noise Figure vs Frequency




Figure 4. Narrow Band S-Parameters vs Frequency ("On" State)




Figure 6. Narrow Band S-Parameters vs Frequency (Bypass Mode)




Figure 8. EVM vs Output Power Over Frequency




Figure 9. IP1dB vs Frequency






Figure 10. SKY65981-11 Schematic Diagram

5








Dimensioning and tolerancing according to ASME Y14.5M-1994. Coplanarity applies to the exposed heat sink slug as well as the terminals.. Plating requirement per source control drawing (SCD) 2504.

Dimension applies to metalized terminal and is measured between 0.15 mm and 0.30 mm from terminal tip.



S1350



Notes:

- s. Carrier tape: black conductive polycarbonate or polystyrene. Cover tape material: transparent conductive PSA. Cover tape size: 5.4 mm width. All measurements are in millimeters.

1. 2. 3. 4.

S1382a

#### Figure 14. SKY65981-11 Tape and Reel Dimensions

#### **Ordering Information**

| Model Name            | Manufacturing Part Number | <b>Evaluation Board Part Number</b> |  |
|-----------------------|---------------------------|-------------------------------------|--|
| SKY65981-11 5 GHz LNA | SKY65981-11               | SKY65981-11-EK1                     |  |

Copyright © 2011-2014 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks, the Skyworks symbol, and "Breakthrough Simplicity" are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.