

PRODUCT SUMMARY

SKY78188-11: SkyOne® LiTE Mid / High Band Front-End Module with 3G/4G Power Amplifiers for LTE Applications

Applications

- Multi-band 2G / 3G / 4G Mobile Devices
- Handsets, Data Cards, M2M
- LTE Advanced Carrier Aggregation (CA)
- Supports 4 Downlink CA and 2 Uplink CA

Features

- Paired with SKY78180, SKY78181 or SKY78185 Low Band FEM for a complete 2G / 3G / 4G solution
- Two separate MIPI® RFFE 2.0 control interfaces w/ 1.8 V nominal supply
- Multi-close antenna switches support a single antenna
- Integrated quadplexer filter for Bands 1/3
- Integrated diplexer filter for Bands 34/39
- Integrated diplexer filter for Bands 40/41
- Two auxiliary Tx outputs for external filters
- Three auxiliary TRx ports to support additional bands
- Auxiliary Mid-Band antenna switch input for 2G Tx output from low band FEM
- Integrated bi-directional RF coupler with cascade support
- All RF I/O ports matched to 50 ohm impedance
- 8 kV ESD compliant on both antenna ports
- Small, low profile package:
 - 8.6 mm x 6.5 mm x 0.75 mm
 - 62-pad Large Grid Array (LGA) configuration

3G Features:

- WCDMA, HSPA+
- TD-SCDMA, TD-HSPA
- CDMA2000 1x RC1, RC3, EVDO (Rev A)



Skyworks Green™ products are compliant with all applicable legislation and are halogen-free. For additional information, refer to Skyworks Definition of Green™, document number SQ04-0074.

4G Features:

- FDD/TDD LTE (includes Band 34)
- Uplink QPSK, 16QAM, and 64QAM
- Intra-band Uplink Carrier Aggregation
- 35 MHz (175RB) for Band 39
- 40 MHz (200RB) for Bands 1, 2, 3, 7, 40 and 41
- 60 MHz (300RB) for Bands 40 and 41
- Inter-band Downlink/Uplink CA support (MB-to-MB supported by SKY77782 PA module as add-on)

Description

The SKY78188-11 Multimode Multiband Tx-Rx Front-End Module (FEM) supports 2G / 3G / 4G mobile devices and operates efficiently in 3G / 4G modes. The FEM consists of separate 3G/4G PA blocks operating Mid- and high bands, a silicon controller containing the MIPI RFFE interface, RF band switches, MB and HB antenna switches, bi-directional couplers, and integrated filters for Bands 1, 2, 3, 7, 34, 39, 40 and 41. RF I/O ports are internally matched to 50 ohms to minimize the need for external components. Extremely low leakage current maximizes device standby time.

The IC die and passive components are mounted on a multi-layer laminate substrate. The assembly encapsulated in a 8.6 mm x 6.5 mm x 0.8 mm, 62-pad LGA, SMT, plastic package allows a highly manufacturable, low cost solution.

The SKY78188-11 FEM is optimized for LTE Advanced, where Carrier Aggregation is utilized for higher data rates. The combined filtering, RF matching, and TRx switching internal to the FEM optimizes performance for popular Downlink (DL) CA band combinations, all in a compact and low cost solution. The FEM contains all necessary components between the antenna and RFIC transceiver and are optimized to provide superior Rx sensitivity and Tx efficiency.

Exceptional RF coexistence planning and system techniques are employed to minimize Rx de-sensitizing (“de-sense”).

For the Uplink, the PA blocks support very wide bandwidth operation by intra-band CA up to 40 MHz (200RB) for Bands 1, 2, 3 and 7, and up to 60 MHz (300RB) for Bands 40 and 41. The FEM also supports Downlink/Uplink CA.

Ordering Information

Product Description	Product Part Number	Evaluation Board Part Number
SKY78188-11 SkyOne® LiTE Mid / High Band Front-End Module with 3G/4G Power Amplifiers for LTE Applications	SKY78188-11	SKY78188-11EK1

Copyright © 2017, 2018, Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks and the Skyworks symbol are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.