

PRODUCT SUMMARY

SKY77638-51 SkyLiTE™ Multimode Multiband Power Amplifier Module

Applications

- Cellular IoT modules
- Handheld computers
- Mobile hotspots / CPE
- Wearable devices
- Tracking and logistics
- 3G/4G LTE
 - Bands 1, 2, 3, 4, 5, 8, 9, 12, 13, 17, 20, 25, 26, 28

Features

- Five LB and four MB RF outputs
- Industry-leading PAE for 3G/4G
- Optimized for APT DCDC operation
- Fully programmable Mobile Industry Processor Interface (MIPI) control
- Dual Low Band RF inputs support separate transceiver outputs or interstage filtering
- MIPI programmable bias modes optimize best efficiency / linearity trade-off for 3G and 4G; minimizes DG09 for 3G.
- Small, low profile package:
 - 4.0 x 6.8 x 0.71 mm
 - 42-pad configuration

Description

Skyworks SKY77638-51 SkyLiTE™ is a multimode multiband (MMMB) Power Amplifier Module (PAM) that supports 3G/4G devices and operates efficiently in CDMA, WCDMA, and LTE modes. The module is fully programmable through a Mobile Industry Processor Interface (MIPI®).

The PAM consists of a WCDMA/LTE block for low and mid-bands, and a Multi-Function Control (MFC) block, RF input/output ports internally matched to 50 Ω to reduce the number of external components. A CMOS integrated circuit uses standard MIPI controls to provide the internal MFC interface and operation. Extremely low leakage current maximizes handset standby time.

The InGaP die and the silicon die and passive components are mounted on a multi-layer laminate substrate. The assembly is encapsulated in a 4.0 mm x 6.8 mm x 0.71 mm, 42-pad MCM, SMT package which is a more highly manufacturable, low cost solution.

3G: The SKY77638-51 supports CDMA, WCDMA, High-Speed Downlink Packet Access (HSDPA), High Speed Uplink Packet Access (HSUPA), and High-Speed Packet Access (HSPA+) modulations. Varying the input power level provides output power control. V_{CC} is adjusted using a DCDC converter to maximize efficiency for each power level and modulation type.

4G: The SKY77638-51 supports 1.4, 3, 5, 10, 15, 20, 30, 35, and 40 MHz channel bandwidths. Similar to 3G operation, output power is controlled by varying the input power and V_{CC} is adjusted using a DCDC converter to maximize efficiency for each power level.

3G/4G modulation scheme includes:

- WCDMA Voice Release 99
- HSDPA categories
- HSUPA
- HSPA+
- CDMA2000 1xRC1, 1xRC3
- CDMA2000 EVDO
- FDD LTE
- TDD LTE
- Uplink Carrier Aggregation (CA) support for Bands 1, 2/25, and 3 (up to 40 MHz)



Skyworks Green™ products are compliant with all applicable legislation and are halogen-free. For additional information, refer to Skyworks Definition of Green™, document number SQ04-0074.




Figure 1. SKY77638-51 Functional Block Diagram

Ordering Information

Part Number	Part Description	Evaluation Board Part Number
SKY77638-51	SkyLiTE™ Multimode Multiband Power Amplifier Module	SKY77638-51EK1

Copyright © 2022 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. (“Skyworks”) products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks’ Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED “AS IS” WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of Skyworks’ published specifications or parameters.

Skyworks, the Skyworks symbol, Sky5®, SkyOne®, SkyBlue™, Skyworks Green™, Clockbuilder®, DSPLL®, ISOmodem®, ProSLIC®, and SiPHY® are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.