





### Description

The Si530/531 XO utilizes Skyworks' advanced DSPLL circuitry to provide a low-jitter clock at high frequencies. The Si530/531 is available with any-rate output frequency from 10 to 945 MHz and select frequencies to 1400 MHz. Unlike a traditional XO, where a different crystal is required for each output frequency, the Si530/531 uses one fixed-frequency crystal to provide a wide range of output frequencies. This IC-based approach allows the crystal resonator to provide exceptional frequency stability and reliability. In addition, DSPLL clock synthesis provides superior supply noise rejection, simplifying the task of generating low-litter clocks in noisy environments typically found in communication systems. The Si530/531 IC-based XO is factory-configurable for a wide variety of user specifications including frequency, supply voltage, output format, and temperature stability. Specific configurations are factoryprogrammed at time of shipment, thereby eliminating long lead times associated with custom oscillators.

#### **Features**

- Available with any-rate output frequencies from 10 to 945 MHz and select frequencies to 1.4 GHz
- Ultra-low jitter: 0.3 ps RMS (12 kHz-20 MHz)
- 3x tighter stability than SAW oscillators
- 3.3 V, 2.5 V and 1.8 V V<sub>DD</sub> supply operation
- Differential (LVPECL, LVDS, CML) or CMOS output options
- Standard frequencies in stock and available for rapid delivery
- Custom frequencies available with < 2-week lead times

#### **Applications**

- SONET/SDH/OTN
- Networking
- HD-SDI/3G-SDI Video
- Test and measurement
- · Clock and data recovery
- FPGA/ASIC Clock generation

Product Selector Guide				
XO Series	Description			
Si530	Single frequency oscillator, OE pin 2			
Si531	Single frequency oscillator, OE pin 1			

A complete Si530-531 data sheet can be found here: www.skyworksinc.com/support-ia

	Pin-ot	Ιτ	
NC/OE	1	6	VDD
OE/NC	2	5	CLK-
GND	3	4	CLK+
	(top viev	v)	

	Pin Description
Pin	Description
1	Si530: NC = No Connect Si531: OE = Output Enable
2	Si530: OE = Output Enable Si531: OE = No Connect
3	GND = Ground
4	CLK+ = Clock output
5	CLK- = Complementary Clock output
6	VDD = Power Supply

### **Selected Electrical Specifications**

 $V_{DD}$  = 2.5 or 3.3 V ±10%,  $T_A$  = -40 to 85 °C

Parameter	Symbol	Test Condition/Comment	Min	Тур	Max	Unit
Frequency Range <sup>1</sup>	F <sub>CLK</sub>	LVPECL/LVDS	10	_	945	MHz
Supply Voltage	V	3.3 V option	2.97	3.3	3.63	V
Supply Voltage	$V_{DD}$	2.5 V option	2.25	2.5	2.75	V
		LVPECL (output enabled)	_	111	121	mA
Supply Current	I <sub>DD</sub>	LVDS (output enabled)	_	90	98	mA
		Tristate (output disabled)	_	60	75	mA
Total Stability	F <sub>STAB</sub>	Temperature stability: ±7 ppm	-20	_	20	ppm
Rise/Fall Time	$T_R/T_F$	LVPECL/LVDS option	_	_	350	ps
Phase Jitter (RMS) for F <sub>CLK</sub> ≥ 500 MHz	фЈ	12 kHz to 20 MHz integration BW <sup>2</sup>	_	0.25	0.40	ps
Phase Jitter (RMS) for F <sub>CLK</sub> of 125 to 500 MHz	фл	12 km2 to 20 Mm2 integration BW		0.36	0.50	ps
Duty Cycle	DC	All formats	45	_	55	%
Output Enable (OE) <sup>3</sup>	$V_{IH}$		$0.75 \times V_{DD}$	_	_	V
Output Enable (OE)	$V_{IL}$		_	_	0.5	V
LVPECL Output Option <sup>4</sup>	V <sub>oc</sub>	mid-level	$V_{DD} - 1.42$	_	$V_{DD} - 1.25$	V
LVF LOL Output Option	Vo	swing (diff)	1.1	_	1.9	$V_{PP}$
LVDS Output Option <sup>5</sup>	Voc	mid-level	1.125	1.20	1.275	V
LVD3 Output Option	Vo	swing (diff)	0.5	0.7	0.9	$V_{PP}$

### Notes:

- 1. Also available in frequencies from 970 to 1134 MHz and 1213 to 1417 MHz.
- 2. All Crystal Oscillator (XO) devices are screened for jitter at production test.
- 3. OE pin includes a 17  $k\Omega$  pullup resistor to VDD.
- 4. 50 Ω to VDD 2.0 V.
- 5.  $R_{term} = 100 \Omega$  (differential).



# 10 MHz to 1.4 GHz Crystal Oscillator (XO) Series

## Absolute Maximum Ratings<sup>1</sup>

Parameter	Symbol	Rating	Unit
Maximum Operating Temp.	T <sub>AMAX</sub>	85	٥C
Storage Temperature	Ts	-55 to 125	°C
Supply Voltage	$V_{DD}$	-0.5 to 3.8	٥C
Input Voltage	V <sub>IN</sub>	0.5 to V <sub>DD</sub> +0.3	V
ESD HBM (JESD22-A114)	HBM	2.5	kV
Solder Temperature <sup>2</sup>	T <sub>PEAK</sub>	260	٥C
Solder Time at T <sub>PEAK</sub> <sup>2</sup>	T <sub>P</sub>	20-40	sec

- Stresses beyond those listed in this table may cause permanent damage to the device. Functional operation specification compliance is not implied at these conditions. Exposure to maximum rating conditions for extended periods may affect device reliability.
- The device is compliant with JEDEC J-STD-020.

## **Environmental Compliance and Package Information**

Parameter	Test Condition
Mechanical Shock	MIL-STD-883, Method 2002
Mechanical Vibration	MIL-STD-883, Method 2007
Solderability	MIL-STD-883, Method 2003
Gross and Fine Leak	MIL-STD-883, Method 1014
Resistance to Solder Heat	MIL-STD-883, Method 2036
Moisture Sensitivity Level (MSL)	1
Contact Pads	Gold over Nickel

### **Thermal Conditions**


Parameter	Symbol	Test Condition	Value	Unit
Thermal Impedance	$\Theta_{JA}$	Still air	84.6	°C/W

### **Standard Frequency Orderable Part Numbers**

Si530 5x7mm	106.25 MHz	125 MHz	148.3517 MHz	148.5 MHz	155.52 MHz	156.25 MHz
3.3V LVPECL	530AC106M250DG	530AC125M000DG	530AC000110DG	530AC148M500DG	530AC155M520DG	530AC156M250DG
3.3V LVDS	530BC106M250DG	530BC125M000DG	530BC000110DG	530BC148M500DG	530BC155M520DG	530BC156M250DG
2.5V LVPECL	530EC106M250DG	530EC125M000DG	530EC000110DG	530EC148M500DG	530EC155M520DG	530EC156M250DG
2.5V LVDS	530FC106M250DG	530FC125M000DG	530FC000110DG	530FC148M500DG	530FC155M520DG	530FC156M250DG
Si531 5x7mm	106.25 MHz	125 MHz	148.3517 MHz	148.5 MHz	155.52 MHz	156.25 MHz
3.3V LVPECL	531AC106M250DG	531AC125M000DG	531AC000110DG	531AC148M500DG	531AC155M520DG	531AC156M250DG
3.3V LVDS	531BC106M250DG	531BC125M000DG	531BC000110DG	531BC148M500DG	531BC155M520DG	531BC156M250DG
2.5V LVPECL	531EC106M250DG	531EC125M000DG	531EC000110DG	531EC148M500DG	531EC155M520DG	531EC156M250DG
2.5V LVDS	531FC106M250DG	531FC125M000DG	531FC000110DG	531FC148M500DG	531FC155M520DG	531FC156M250DG

Si530 5x7mm	187.5 MHz	200 MHz	250 MHz	311.04 MHz	312.5 MHz	622.08 MHz
3.3V LVPECL	530AC187M500DG	530AC200M000DG	530AC250M000DG	530AC311M040DG	530AC312M500DG	530AC622M080DG
3.3V LVDS	530BC187M500DG	530BC200M000DG	530BC250M000DG	530BC311M040DG	530BC312M500DG	530BC622M080DG
2.5V LVPECL	530EC187M500DG	530EC200M000DG	530EC250M000DG	530EC311M040DG	530EC312M500DG	530EC622M080DG
2.5V LVDS	530FC187M500DG	530FC200M000DG	530FC250M000DG	530FC311M040DG	530FC312M500DG	530FC622M080DG
Si531 5x7mm	187.5 MHz	200 MHz	250 MHz	311.04 MHz	312.5 MHz	622.08 MHz
	<b>187.5 MHz</b> 531AC187M500DG			• • • • • • • • • • • • • • • • • • • •	0 : 2 : 0 : : : : : : :	
3.3V LVPECL		531AC200M000DG	531AC250M000DG	531AC311M040DG	531AC312M500DG	531AC622M080DG
3.3V LVPECL 3.3V LVDS	531AC187M500DG	531AC200M000DG 531BC200M000DG	531AC250M000DG 531BC250M000DG	531AC311M040DG 531BC311M040DG	531AC312M500DG 531BC312M500DG	531AC622M080DG 531BC622M080DG

For customized frequencies: www.skyworksinc.com/en/products/timing









www.skyworksinc.com/CBPro



**Quality** www.skyworksinc.com/quality



**Support & Resources** www.skyworksinc.com/support

### Copyright © 2021 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks' Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of Skyworks' published specifications or parameters.

Skyworks, the Skyworks symbol, Sky5®, SkyOne®, SkyBlue™, Skyworks Green™, Clockbuilder®, DSPLL®, ISOmodem®, ProSLIC®, and SiPHY® are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.