

SE5501L: Dual-Band 802.11n WLAN/BT Front-End

Applications

- IEEE802.11b DSSS WLAN
- IEEE802.11a,g,n OFDM WLAN
- Embedded applications with Bluetooth (Mobile)

Features

- Direct to Battery operation
- All RF ports matched to 50 Ω
- Integrated 2.4/5 GHz PA, 2.4/5 GHz LNA, T/R switches and filtering
- Integrated Power Detector
- 20 dBm @ 3 % EVM, 802.11gn, 54 Mbps
- 18 dBm @ 3.0 % EVM, 802.11an, 54 Mbps
- Lead free, Halogen Free and RoHS compliant.
- Compact package, 3 x 5 x 0.9 mm, MSL 3

Ordering Information

Part No.	Package	Remark
SE5501L	30 pin QFN	Samples
SE5501L-R	30 pin QFN	Tape & Reel
SE5501L-EK1	N/A	Evaluation kit

Product Description

The SE5501L is a complete 802.11n WLAN RF frontend module providing all the functionality of the power amplifiers, LNAs, power detector, Antenna switches, filtering and associated matching. The SE5501L provides a complete 2.4 GHz and 5 GHz WLAN RF solution from the output of the transceiver to the antennas in a compact form factor.

The receive path is designed to maximize performance by providing both a low noise amplifier as well as a bypass state, for use when high power signals are being received.

Designed for ease of use, all RF ports are matched to 50 Ω to simplify PCB layout and the interface to the transceiver RFIC. The SE5501L also includes a transmitter power detector for each band with 20 dB of dynamic range.

The SE5501L is optimized for mobile applications with direct to battery operation



DATA SHEET SE5501L: Dual-Band 802.11n WLAN/BT Front-End

Functional Block Diagram




Figure 1: Functional Block Diagram



SE5501L: Dual-Band 802.11n WLAN/BT Front-End

Pin Out Diagram CREF PEN2 LEN2 RX5 CRX GND $^{\circ}$ RX2 DISCONTINUED TX2 GND SP5 **BTRX** VCC **BTALL** DET GND TX5 ANT2 GND GND PEN5 CBT ANT5 **VCC** \ C C LEN5 SP2

Figure 2: SE5501L Pin Out (Top View Through Package)

Pin Out Description

Pin No.	Name	Description
1	RX2	2.4 GHz RX output
2	GND	Ground
3	RX5	5 GHz RX output
4	VCC	Supply Voltage
5	CREF	Logic Reference Voltage
6	PEN2	Enable for 2.4 GHz PA and TX Switch
7	DNC	Do Not Connect
8	LEN2	Enable for 2.4 GHz LNA and RX Switch
9	CRX	Switch control for RX Switches
10	GND	Ground
11	TX2	2.4 GHz Transmit Port
12	SP5	5 GHz bias speedup
13	VCC	Supply Voltage

Pin No.	Name	Description
14	DET	Power Detector Output
15	TX5	5 GHz Transmit Port
16	SP2	2.4 GHz bias speedup
17	VCC	Supply Voltage
18	VCC	Supply Voltage
19	LEN5	Enable for 5 GHz LNA and RX Switch
20	PEN5	Enable for 5 GHz PA and TX Switch
21	CBT	Switch control for BT
22	GND	Ground
23	GND	Ground
24	ANT5	5 GHz Antenna Port
25	GND	Ground
26	ANT2	2.4 Ghz Antenna Port



SE5501L: Dual-Band 802.11n WLAN/BT Front-End

Pin No.	Name	Description	Pin No.	Name
27	GND	Ground	29	BTR)
28	BTALL	BT Port	30	GND

Pin No.	Name	Description
29	BTRX	BT RX Port
30	GND	Ground

Absolute Maximum Ratings

These are stress ratings only. Exposure to stresses beyond these maximum ratings may cause permanent damage to, or affect the reliability of the device. Avoid operating the device outside the recommended operating conditions defined below. This device is ESD sensitive. Handling and assembly of this device should be at ESD protected workstations.

Symbol	Definition	Min.	Max.	Unit
Vcc	Supply Voltage	-0.3	5.5	V
V_{IN}	Control Pin Voltages	-0.3	3.6	V
TXRFIN	TX2/TX5, with ANT2/ANT5 terminated in 50Ω	-	+10	dBm
TA	Operating Temperature Range	-40	85	°C
Тѕтс	Storage Temperature Range	-40	125	°C
ESD _{HBM}	JEDEC JESD22-A114 All pins		1000	V

Recommended Operating Conditions

Symbol	Parameter	Min.	Тур.	Max.	Unit
Vcc	Supply Voltage	3.0	3.3	4.8	V
TA	Ambient Temperature	-40	25	85	°C

Control Logic Characteristics

Conditions: Vcc = 3.3 V, T_A = 25 °C, as measured on Skyworks Solutions' SE5501L-EK1 evaluation board (dembedded to device), all unused ports terminated with 50 ohms, unless otherwise noted.



SE5501L: Dual-Band 802.11n WLAN/BT Front-End

Parameter	min	nom	max	Units
Logic high reference : VREF	1.7		3.6	V
Logic input high : VIH	VREF-0.3		3.6	V
Logic input low : VIL	6		0.3	V
Logic input current : IIH	1	0.5	5	μA
Logic input current : IIL	M	0.1	1	μA
/ 6	4 /			



SE5501L: Dual-Band 802.11n WLAN/BT Front-End

DC Electrical Characteristics

Conditions: Vcc = 3.3 V,, T_A = 25 °C, as measured on Skyworks Solutions' SE5501L-EK1 evaluation board (deembedded to device), all unused ports terminated with 50 ohms, unless otherwise noted

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
TXIcc-g	Total 802.11g Transmit Supply	P _{OUT} = 20 dBm, 54 Mbps OFDM signal, 64QAM, PEN2 = Hi,	-	180	190	mA
	Current	P _{OUT} = 18 dBm, 54 Mbps OFDM signal, 64QAM, PEN2 = Hi,		160	170	
TXIcq-g	Quiescent current , 802.11g Transmit supply Current	No RF applied, PEN2=Hi	-	100	-	mA
TVIce	Total 802.11a Transmit Supply	Роит = 18 dBm, 54 Mbps OFDM signal, 64QAM, PEN5= Hi		190	200	m
TXIcc-A	Current	P _{OUT} = 16 dBm, 54 Mbps OFDM signal, 64QAM, PEN5= Hi	-	170	180	mA
TXIcq-A	Quiescent current , 802.11a Transmit supply Current	No RF applied, PEN5- Hi	-	120	-	mA
RXIcc-g	Total 802.11b/g Receive Supply	LEN= Hi	_	15		mA
10000	Current	LEN = Lo		0.2		1117 (
RXIcc-A	Total 802.11a Receive Supply	LEN= Hi	_	15		mA
TOTAL CO-M	Current	LEN = Lo		0.2		111/1
I _{CC-BT}	Total BT Supply Current	CBT = Hi	-	0.2		mA
Icc_off	Total Supply Current	No RF, PEN2=PEN5=LEN2=LEN5=0V	-	10		μΑ



SE5501L: Dual-Band 802.11n WLAN/BT Front-End

Operating Modes

Mode#	Mode Description	PEN2	LEN2	PEN5	LEN5	CRX	СВТ	CREF
0	All Off	0	0	0	0	0	0	Х
1	вт	0	0	0	0	0	1	1
2	BT + RX5 Low Gain	8	20		0	1	1	1
3	BT + RX5 High Gain	0	5 %	0	1	1	1	1
4	BT + TX5	197	0	1	0	0	1	1
5	RX2 Low Gain + RX5 Low Gain	0	0	0	0	1	0	1
6	RX2 High Gain + RX5 Low Gain	0	1	0	0	1	0	1
7	RX2 Low Gain + RX5 High Gain	0	0	0	1	1	0	1
8	TX2	1	0	0	0	0	0	1
9	TX5	0	0	1	0	0	0	1
10	RX2 High Gain + RX5 High Gain	0	1	0	1	1	0	1



SE5501L: Dual-Band 802.11n WLAN/BT Front-End

AC Electrical Characteristics

2.4 GHz Transmit Characteristics

Conditions: Vcc = 3.3 V, PEN2= CREF=Hi, T_A = 25 °C, as measured on Skyworks Solutions' SE5501L-EK1 evaluation board (de-embedded to device), all unused ports terminated with 50 ohms, unless otherwise

noted.

Symbol Parameter Condition Min. Тур. Max. Unit 2400 Frequency Range 2485 MHz FIN Pout = 19.5 dBm2.5 3.5 **EVM EVM** % Pout = 18 dBm 2.0 2.5 2400 **2**485 MH 19 22 25 S_{21} Gain dΒ 1600 - 1660 MHz -10 Out of Band Gain dBc S₂₁ 00B 3200 – 3**215** MHz -10 Over 2400-2485 MHz Gain Variation 2 ΔS_{21} 1.5 dBpp Band -14 -10 S_{11} Input Return Loss dΒ **Output Return Loss** -10 -6 dB S_{22} P_N Wideband Noise 800 - 2170 MHz -140 dBm/Hz NF Noise Figure 10 dB 2f 2f @ Pout= 22 dBm -25 -20 11b Harmonics dBm/MHz 3f 3f @ Pout = 22 dBm -35 -30 11b @ Pout=22 dBm: dBc ACP11b fc +/- 11 MHz -34 -32 fc +/- 22 MHz -54 -52 11g @ Pout=20 dBm: dBc fc +/- 11 MHz -20 -23 ACP11g fc +/- 20 MHz -28 Spectral Mask -30 fc +/- 30 MHz -43 -40 11n @ Pout=18 dBm: dBc fc +/- 11 MHz -23 -20 ACP11n fc +/- 20 MHz -30 -28 fc +/- 30 MHz -48 -45 Pout ≤ 20dBm All non-harmonically related outputs less than **STAB** Stability Load VSWR = 10:1 -45 dBm/MHz



SE5501L: Dual-Band 802.11n WLAN/BT Front-End

2.4 GHz Receive Characteristics

Conditions: VCC = 3.3V, LEN2=CRX=CREF = Hi, $T_A = 25$ °C, as measured on Skyworks Solutions' SE5501L-EK1 evaluation board (de-embedded to device), all unused ports terminated with 50 ohms, unless otherwise noted.

Symbol	Parameter	Condition	Min.	Тур.	Max.	Unit
Fout	Frequency Range	. /	2400	-	2485	MHz
S 21	Gain	LEN2 = Hi	13	15	17	dB
3 21	Gain	LEN2 = Lo		-8		uБ
S _{21_OOB}	Out of Band Gain	800 – 1990 MHz		7		dB
Δ\$21	Gain Variation	2400 – 2485 MHz, Over any 20MHz band		0.25	0.4	dB
NF	Noise Figure	LEN2 Hi	-	2.0	2.5	dB
IIP3	Input Third Order Intercept	LEN2 = Hi	0	2	-	dBm
ISOL _{RRX}	Reverse Isolation)	-25	-	-	dB
INT	Interferer	1710-1990, max gain change 0.5 dB	-10	-8	-	dBm
S ₁₁	Input Return Loss	-	-	-12	-10	dB
ID44P	Input D1dP	LEN2 = Hi	-8	-7	-	dBm
IP1dB	Input P1dB	LEN2 = Lo	+5	+10	-	UDIII
T _{EN}	Enable Time	10% to 90% of RX RF power, from time that LEN2 is at 50%	-	-	800	nsec



SE5501L: Dual-Band 802.11n WLAN/BT Front-End

5 GHz Transmit Characteristics

Conditions: VCC = 3.3 V, PEN5=CREF= Hi, T_A = 25 °C, as measured on Skyworks Solutions' SE5501L-EK1 evaluation board (de-embedded to device), all unused ports terminated with 50 ohms, unless otherwise noted.

Symbol	Parameter	Condition	Min.	Тур.	Max.	Unit
Fin	Frequency Range	- / .	5150	-	5850	MHz
EVM	EVM	Pout = 18 dBm Pout = 17 dBm		2.5 2.0	3.5 2.5	%
S ₂₁	Gain	7.	15	18	21	dB
S _{21_OOB}	Out of Band Gain	3265 – 3900 MHz 6900 – 7250 MHz 7250 – 7800 MHz			-15 -8 -15	dBc
ΔS ₂₁	Gain Variation	Over 5150-5850 MHz Band		2.0	3.0	dBpp
S ₁₁	Input Return Loss)		-10	-8	dB
S ₂₂	Output Return Loss			-10	-6	dB
P_N	Wideband Noise	800 – 2170 MHz		-150		dBm/Hz
NF	Noise Figure				10	dB
2f	Harmonics	2f @ Pout= 18 dBm		-40	-35	dBm/MHz
3f	Haimonics	3f @ Pout = 18 dBm		-50	-45	UDIII/IVITIZ
ACP11a		11a @ Pout=18 dBm: fc +/- 11 MHz fc +/- 20 MHz fc +/- 30 MHz		-23 -30 -43	-20 -28 -40	dBc
ACP11n	Spectral Mask	11n @ Pout=16 dBm: fc +/- 11 MHz fc +/- 20 MHz fc +/- 30 MHz		-23 -30 -48	-20 -28 -45	dBc
	Stability	Pout ≤ 18dBm Load VSWR = 10:1	All non-harmonically related outputs less than -45 dBm/MHz			



SE5501L: Dual-Band 802.11n WLAN/BT Front-End

5 GHz Receive Characteristics

Conditions: VCC = 3.3 V, LEN5=CREF=CRX= Hi, TA = 25 °C, as measured on Skyworks Solutions' SE5501L-EK1 evaluation board (de-embedded to device), all unused ports terminated with 50 ohms, unless otherwise noted.

Symbol	Parameter	Condition	Min.	Тур.	Max.	Unit
Fouт	Frequency Range	. /	5150	-	5850	MHz
004	Gain	LEN5 = Hi	\ 8	11	14	dB
S21		LEN5 = Lo	-19	-14	-9	dB
S _{21_OOB}	Out of Band Gain	800 – 1990 MHz			-10	dB
Δ\$21	Gain Variation	5150 - 5850 MHz, Over any 40MHz band		0.25	0.4	dB
NF	Noise Figure	LEN5=Hi	-	2.5	3	dB
IIP3	Input Third Order Intercept	LENS HI	3	5	-	dBm
ISOL _{RRX}	Reverse Isolation	` /	20	-	-	dB
INT	Interferer	1710 - 2500 MHz, max gain change = 0.5 dB	-10	-	-	dBm
S ₁₁	Input Return Loss	-	-	-6		dB
IP1dB	Input P1dB	LEN5 = Hi	-7	-5	-	dBm
		LEN5 = Lo	+5	+10	-	
T _{EN}	Enable Time	10% to 90% of RX RF power, from time that LEN5 is at 50%	-	-	800	nsec

Bluetooth Characteristics

Conditions: Vcc = 3.3 V, CBT=CREF= Hi, TA = 25 °C, as measured on Skyworks Solutions' SE5501L-EK1 evaluation board (de-embedded to device), all unused ports terminated with 50 ohms, unless otherwise

noted.

Symbol	Parameter	Condition	Min.	Тур.	Max.	Unit
Fouт	Frequency Range	-	2400	-	2485	MHz
BTı∟	Insertion Loss	ANT2 to BTALL (CBT= Hi)	-	1.0	2.0	
		BTALL to BTRX (LEN2=Hi)		0.8		dB
S ₁₁	BT Port Return Loss	CBT= Hi	-	-14	-10	dB
ISOLsw	Switch Isolation	CBT= Hi	20	-	-	dB
T _{EN}	Enable Time	10% to 90% of BT RF power, from time that CBT is at 50%	-	-	800	nsec



SE5501L: Dual-Band 802.11n WLAN/BT Front-End

Power Detector Characteristics

Conditions: Vcc = 3.3 V, T_A = 25 °C, as measured on Skyworks Solutions' SE5501L-EK1 evaluation board (dembedded to device), all unused ports terminated with 50 ohms, unless otherwise noted.

Symbol	Parameter	Condition	Min.	Тур.	Max.	Unit
Fоuт	Frequency Range	PEN2= Hi PEN5 = Hi	2400 5150	-	2500 5850	MHz
PDR	Power detect range, peak power	Measured at ANT	0	-	22	dBm
PDZLOAD	DC load impedance		_	2.5		kΩ
PDV _{P20}	Output Voltage, Pout = 20 dBm	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \		0.8	1.3	V
PDVpnoRF	Output Voltage, Pout = No RF			0.130	-	V
PD_{VAR}	Power Detector Accuracy	Pout>10 dBm	-1.5		+1.5	dB
PD_{BW}	Power Detector Output Bandwidth)		350		KHz



DATA SHEET SE5501L: Dual-Band 802.11n WLAN/BT Front-End

Package Diagram




Figure 4: Package Outline Drawing



SE5501L: Dual-Band 802.11n WLAN/BT Front-End

Recommended PCB Footprint




Figure 5: Recommended PCB footprint

Package Handling Information

Because of its sensitivity to moisture absorption, instructions on the shipping container label must be followed regarding exposure to moisture after the container seal is broken, otherwise, problems related to moisture absorption may occur when the part is subjected to high temperature during solder assembly. The SE5501L is capable of withstanding a Pb free solder reflow. Care must be taken when attaching this product, whether it is done manually or in a production solder reflow environment. If the part is manually attached, precaution should be taken to insure that the device is not subjected to temperatures above its rated peak temperature for an extended period of time. For details on both attachment techniques, precautions, and handling procedures recommended, please refer to:

- "Quad Flat No-Lead Module Solder Reflow & Rework Information", Document Number QAD-00045.
- "Handling, Packing, Shipping and Use of Moisture Sensitive QFN", Document Number QAD-00044.



SE5501L: Dual-Band 802.11n WLAN/BT Front-End

Branding Information




Figure 6: SE5501L Branding Information

Document Change History

Revision	Date	Notes
1.0	06/17/09	Created
1.1	07/14/2009	Updated pin-out
1.2	12/11/2009	Updated Package Outline and specifications
1.3	January-14-2011	Updated specifications
1.4	February-24-2011	Updated specifications
1.5	April-12-2011	Updated specifications
1.6	June-08-2011	Updated specifications
1.7	July-07-2011	Updated MSL rating
1.8	August-21-2011	Updated specifications
1.9	April-11-2012	Updated with Skyworks logo and disclaimer statement



SE5501L: Dual-Band 802.11n WLAN/BT Front-End



Copyright © 2012, 2019 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of stated published specifications or parameters.

Skyworks, the Skyworks symbol, and "Breakthrough Simplicity" are trademarks or registered trademarks of Skyworks Solutions, Inc., in the United States and other countries. Third-party brands and names are for identification purposes only, and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.