

4-PLL ANY-FREQUENCY PRECISION CLOCK MULTIPLIER/JITTER ATTENUATOR

Features

- Highly-integrated, 4 PLL clock multiplier/jitter attenuator
- Four independent DSPLLs support any-frequency synthesis and jitter attenuation
- 8 inputs/8 outputs
- Each DSPLL can generate any frequency from 2 kHz to 808 MHz from a 2 kHz to 710 MHz input
- 350 fs rms (12 kHz- 20 MHz) and 410 fs rms (50 kHz-80 MHz) typical
- Meets ITU-T G.8251 and Telcordia GR-253-CORE OC-192 jitter specifications
- Programmable loop bandwidth: 60 Hz to 8 kHz
- Faster lock acquisition compared to the Si5374: <1.2 s
- For a very low-loop BW version, see the Si5374

- Supports all ITU G.709 and any custom FEC ratios (239/237, 255/238, 255/237, 255/236, 253/226)
- Integrated loop filter with programmable bandwidth
- Simultaneous free-run and synchronous operation
- Automatic/manual hitless input clock switching
- Selectable output clock signal format (LVPECL, LVDS, CML, CMOS)
- LOL and interrupt alarm outputs
- I²C programmable
- Single 1.8 V ±5% or 2.5 V ±10% operation with high PSRR on-chip voltage regulator
 - 10x10 mm PBGA




Applications

- High-density, any-port, any-protocol, 1/2/4/8/10G Fibre Channel any-frequency line cards
- ITU-T G.709 OTN custom FEC
- 10/40/100G
- OC-48/192, STM-16/64
- GbE/10 GbE Synchronous Ethernet
- Carrier Ethernet, multi-service switches and routers
- MSPP, ROADM, P-OTS, muxponders

Description

The Si5376 is a highly-integrated, 4-PLL, jitter-attenuating precision clock multiplier for applications requiring sub-1 ps jitter performance. Each of the DSPLL® clock multiplier engines accepts two input clocks ranging from 2 kHz to 710 MHz and generates two independent synchronous output clocks ranging from 2 kHz to 808 MHz. The device provides virtually any frequency translation combination across this operating range. For asynchronous, free-running clock generation applications, the Si5376's reference oscillator can be used as a clock source for any of the four DSPLLs. The Si5376 input clock frequency and clock multiplication ratio are programmable through an I²C interface. The Si5376 is based on Skyworks Solutions' third-generation DSPLL® technology, which provides any-frequency synthesis and jitter attenuation in a highly-integrated PLL solution that eliminates the need for external VCXO and loop filter components. Each DSPLL loop bandwidth is digitally-programmable, providing jitter performance optimization at the application level. The device operates from a single 1.8 or 2.5 V supply with on-chip voltage regulators with excellent PSRR. The Si5376 is ideal for providing clock multiplication and jitter attenuation in high-port-count optical line cards requiring independent timing domains.

Functional Block Diagram



3

TABLE OF CONTENTS

Section	Page
1. Electrical Specifications	4
2. Typical Application Schematic	
3. Typical Phase Noise Plot	
4. Functional Description	
5. Si5376 Application Examples and Suggestions	
5.1. Schematic and PCB Layout	
5.2. Thermal Considerations	
5.3. SCL Leakage	
5.4. RSTL x Pins	
5.5. Reference Oscillator Selection	
5.6. Alarms	
5.7. OSC_P and OSC_N Connection	
6. Register Map	
7. Register Descriptions	
•	
7.1. ICAL	
8. Pin Descriptions: Si5376	
9. Ordering Guide	
10. Package Outline	
11. Recommended PCB Layout	
12. Top Markings	
12.1. Si5376 Top Marking (PBGA, Lead-Free)	
12.2. Top Marking Explanation (PBGA, Lead-Free)	
12.3. Si5376 Top Marking (PBGA, Lead-Finish)	65
12.4. Top Marking Explanation (PBGA, Lead-Finish)	65
Contact Information	66

1. Electrical Specifications

Table 1. Recommended Operating Conditions

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Ambient Temperature	T _A		-40	25	85	С
Supply Voltage during	V_{DD}	2.5 V Nominal	2.25	2.5	2.75	V
Normal Operation		1.8 V Nominal	1.71	1.8	1.89	V

Note: All minimum and maximum specifications are guaranteed and apply across the recommended operating conditions. Typical values apply at nominal supply voltages and an operating temperature of 25 °C unless otherwise stated.




Figure 1. Differential Voltage Characteristics




Figure 2. Rise/Fall Time Characteristics

5

Table 2. DC Characteristics

 $(V_{DD} = 1.8 \pm 5\%, 2.5 \pm 10\%, T_A = -40 \text{ to } 85 \text{ °C})$

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Supply Current ¹	I _{DD}	LVPECL Format 622.08 MHz Out All CKOUTs Enabled	_	1000	1100	mA
		LVPECL Format 622.08 MHz Out 4 CKOUTs Enabled	_	870	970	mA
		CMOS Format 19.44 MHz Out All CKOUTs Enabled	_	820	940	mA
		CMOS Format 19.44 MHz Out 4 CKOUTs Enabled	_	780	880	mA
		Disable Mode	_	660	_	mA
CKINn Input Pins ²						
Input Common Mode Voltage (Input Thresh-	V_{ICM}	1.8 V ± 5%	0.9	_	1.4	V
old Voltage)		2.5 V ± 10%	1	_	1.7	V
Input Resistance	CKN _{RIN}	Single-ended	20	40	60	kΩ
Single-Ended Input Voltage Swing	V _{ISE}	f _{CKIN} < 212.5 MHz See Figure 1.	0.2		_	V _{PP}
(See Absolute Specs)		f _{CKIN} > 212.5 MHz See Figure 1.	0.25	_	_	V _{PP}
Differential Input Voltage Swing	V_{ID}	f _{CKIN} < 212.5 MHz See Figure 1.	0.2	_		V_{PP}
(See Absolute Specs)		f _{CKIN} > 212.5 MHz See Figure 1.	0.25	_		V _{PP}
Output Clocks (CKOU	Tn) ^{3,4}					
Common Mode	CKO _{VCM}	LVPECL 100 Ω load line-to-line	V _{DD} – 1.42	_	V _{DD} -1.25	V
Differential Output Swing	CKO _{VD}	LVPECL 100 Ω load line-to-line	1.1	_	1.9	V _{PP}

- 1. Current draw is independent of supply voltage.
- 2. No under- or overshoot is allowed.
- 3. LVPECL outputs require nominal $V_{DD} = 2.5 \text{ V}$.
- **4.** LVPECL, CML, LVDS and low-swing LVDS measured with Fo = 622.08 MHz.

Table 2. DC Characteristics (Continued)

 $(V_{DD} = 1.8 \pm 5\%, 2.5 \pm 10\%, T_{A} = -40 \text{ to } 85 \text{ °C})$

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Single Ended Output Swing	CKO _{VSE}	LVPECL 100 Ω load line-to-line	0.5	_	0.93	V _{PP}
Differential Output Voltage	CKO _{VD}	CML 100 Ω load line-to-line	350	425	500	mV_PP
Common Mode Output Voltage	CKO _{VCM}	CML 100 Ω load line-to-line	_	V _{DD} -0.36	_	V
Differential Output Voltage	CKO _{VD}	LVDS 100 Ω load line-to-line	500	700	900	mV_{PP}
		Low Swing LVDS 100 Ω load line-to-line	350	425	500	mV_PP
Common Mode Output Voltage	CKO _{VCM}	LVDS 100 Ω load line-to-line	1.125	1.2	1.275	٧
Differential Output Resistance	CKO _{RD}	CML, LVPECL, LVDS	_	200	_	Ω
Output Voltage Low	CKO _{VOLLH}	CMOS	_	_	0.4	V
Output Voltage High	CKO _{VOHLH}	V _{DD} = 1.71 V CMOS	0.8 x V _{DD}	_	_	V
Output Drive Current (CMOS driving into	CKO _{IO}	ICMOS[1:0] = 11 V _{DD} = 1.8 V	_	7.5	_	mA
CKO _{VOL} for output low or CKO _{VOH} for output high. CKOUT+ and		ICMOS[1:0] = 10 V _{DD} = 1.8 V	_	5.5	_	mA
CKOUT- shorted externally)		ICMOS[1:0] = 01 V _{DD} = 1.8 V	_	3.5	_	mA
		ICMOS[1:0] = 00 V _{DD} = 1.8 V	_	1.75	_	mA
		ICMOS[1:0] = 11 V _{DD} = 2.5 V	_	20	_	mA
		ICMOS[1:0] = 10 V _{DD} = 2.5 V	_	15		mA
		ICMOS[1:0] = 01 V _{DD} = 2.5 V	_	10	_	mA
		ICMOS[1:0] = 00 V _{DD} = 2.5 V	_	5	_	mA

- 1. Current draw is independent of supply voltage.
- 2. No under- or overshoot is allowed.
- 3. LVPECL outputs require nominal V_{DD} = 2.5 V.
 4. LVPECL, CML, LVDS and low-swing LVDS measured with Fo = 622.08 MHz.

Table 2. DC Characteristics (Continued)

 $(V_{DD} = 1.8 \pm 5\%, 2.5 \pm 10\%, T_A = -40 \text{ to } 85 \text{ °C})$

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
2-Level LVCMOS Inpu	t Pins					
Input Voltage Low	V _{IL}	V _{DD} = 1.71 V	_	_	0.5	V
		V _{DD} = 2.25 V	_		0.7	V
Input Voltage High	V _{IH}	V _{DD} = 1.89 V	1.4	_	_	V
		V _{DD} = 2.25 V	1.8	_	_	V
LVCMOS Output Pins	,		1			1
Output Voltage Low	V _{OL}	IO = 2 mA V _{DD} = 1.71 V	_	_	0.4	V
Output Voltage Low		IO = 2 mA V _{DD} = 2.25 V	_	_	0.4	V
Output Voltage High	V _{OH}	IO = -2 mA $V_{DD} = 1.71 \text{ V}$	V _{DD} – 0.4	_	_	V
Output Voltage High		IO = -2 mA $V_{DD} = 2.25 \text{ V}$	V _{DD} – 0.4	_	_	V

- 1. Current draw is independent of supply voltage.
- 2. No under- or overshoot is allowed.
- 3. LVPECL outputs require nominal V_{DD} = 2.5 V.
 4. LVPECL, CML, LVDS and low-swing LVDS measured with Fo = 622.08 MHz.

Table 3. AC Characteristics

 $(V_{DD} = 1.8 \pm 5\%, 2.5 \pm 10\%, T_A = -40 \text{ to } 85 \text{ °C})$

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Single-Ended Referer	nce Clock Inp	ut Pin OSC_P (OSC_N with	cap to GNE)) ¹		
OSC_P to OSC_N Resistance	OSC _{RIN}	RATE_REG = 0101 or 0110, ac coupled	_	100	_	Ω
Input Voltage Swing	OSC _{VPP}	RATE_REG = 0101 or 0110, ac coupled	0.5	_	1.2	V _{PP}
Differential Reference	Clock Input	Pins (OSC_P/OSC_N) ¹				
Input Voltage Swing	OSC _{VPP}	RATE_REG = 0101 or 0110, ac coupled	0.5	_	2.4	V _{PP}
CKINn Input Pins				•		
Input Frequency	CKN _F		0.002	_	710	MHz
Input Duty Cycle (Minimum Pulse Width)	CKN _{DC}	Whichever is smaller (i.e., the 40% / 60% limitation applies only to high-frequency clocks)	40	_	60	%
			2	_	_	ns
Input Rise/Fall Time	CKN _{TRF}	20–80% See Figure 2	_	_	11	ns
CKOUTn Output Pins						
Output Frequency (Output not config- ured for CMOS or Disabled)	CKO _F		0.002	_	808	MHz
Maximum Output Frequency in CMOS Format	CKO _F		_	_	212.5	MHz
Output Rise/Fall (20–80 %) @ 622.08 MHz output	CKO _{TRF}	Output not configured for CMOS or Disabled See Figure 2	_	230	350	ps
Output Rise/Fall (20–80%) @ 212.5 MHz output	CKO _{TRF}	CMOS Output $V_{DD} = 1.71$ $C_{LOAD} = 5 pF$	_	_	8	ns
Output Rise/Fall (20–80%) @ 212.5 MHz output	CKO _{TRF}	CMOS Output $V_{DD} = 2.25$ $C_{LOAD} = 5 \text{ pF}$	_	_	2	ns

- 1. A crystal may not be used in place of an oscillator.
- 2. Input to output skew after an ICAL is not controlled and can be any value.

9

Table 3. AC Characteristics (Continued)

 $(V_{DD} = 1.8 \pm 5\%, 2.5 \pm 10\%, T_A = -40 \text{ to } 85 \text{ °C})$

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Output Duty Cycle Uncertainty @ 622.08 MHz	CKO _{DC}	100 Ω Load Line-to-Line Measured at 50% Point (differential)	_	_	±40	ps
LVCMOS Input Pins						
Minimum Reset Pulse Width	t _{RSTMN}		1	_	_	μs
Reset to Microproces- sor Access Ready	t _{READY}		_	_	10	ms
LVCMOS Output Pins						
Rise/Fall Times	t _{RF}	C _{LOAD} = 20pf See Figure 2	_	25	_	ns
LOSn Trigger Window	LOS _{TRIG}	From last CKINn ↑ to ↓ Internal detection of LOSn N3 ≠ 1	_	_	4.5 x N3	T _{CKIN}
Time to Clear LOL after LOS Cleared	^t CLRLOL	↓LOS to ↓LOL Fold = Fnew Stable OSC_P, OSC_N reference	_	10	_	ms

- 1. A crystal may not be used in place of an oscillator.
- 2. Input to output skew after an ICAL is not controlled and can be any value.

Table 3. AC Characteristics (Continued)

 $(V_{DD} = 1.8 \pm 5\%, 2.5 \pm 10\%, T_A = -40 \text{ to } 85 \text{ °C})$

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Device Skew ²						
Output Clock Skew	t _{SKEW}	↑ of CKOUTn to ↑ of CKOUT_m, CKOUTn and CKOUT_m at same frequency and signal format PHASEOFFSET = 0 CKOUT_ALWAYS_ON = 1 SQ_ICAL = 1	_	_	100	ps
Phase Change due to Temperature Variation	t _{TEMP}	Max phase changes from -40 to +85 °C	_	300	500	ps

Notes:

- 1. A crystal may not be used in place of an oscillator.
- 2. Input to output skew after an ICAL is not controlled and can be any value.

Table 4. Microprocessor Control

 $(V_{DD} = 1.8 \pm 5\%, 2.5 \pm 10\%, T_A = -40 \text{ to } 85 \text{ °C})$

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit			
² C Bus Lines (SDA, SCL)									
Input Voltage Low	VIL _{I2C}		_	_	0.25 x V _{DD}	V			
Input Voltage High	VIH _{I2C}		0.7 x V _{DD}	_	V _{DD}	V			
Hysteresis of Schmitt Trigger Inputs	VHYS _{I2C}	V _{DD} = 1.8 V	0.1 x V _{DD}	_	_	V			
riigger iiiputs		V _{DD} = 2.5	0.05 x V _{DD}	_	_	V			
Output Voltage Low	VOL _{I2C}	V _{DD} = 1.8 V IO = 3 mA	_	_	0.2 x V _{DD}	V			
		V _{DD} = 2.5 IO = 3 mA	_	_	0.4	V			

Table 5. Performance Specifications $V_{DD} = 1.8 \text{ V} \pm 5\%$ or 2.5 V $\pm 10\%$, $T_A = -40$ to 85 °C

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
PLL Performance*			-		•	
Lock Time	t _{LOCKMP}	Start of ICAL to ↓ of LOL, FASTLOCK disabled	_	35	1200	ms
Output Clock Phase Change	t _{P_STEP}	After clock switch f3 ≥ 128 kHz	_	200	_	ps
Closed Loop Jitter Peaking	J_{PK}		_	0.05	0.1	dB
Jitter Tolerance	J _{TOL}	Jitter Frequency ≥ Loop Bandwidth	5000/BW	_	_	ns pk-pk
Phase Noise	CKO _{PN}	1 kHz Offset	_	-106	_	dBc/Hz
fout = 622.08 MHz		10 kHz Offset	_	-114	_	dBc/Hz
		100 kHz Offset	_	-116	_	dBc/Hz
		1 MHz Offset	_	-132	_	dBc/Hz
Spurious Noise	SP _{SPUR}	Max spur @ n x F3 (n ≥ 1, n x F3 < 100 MHz)	_	-7 0	_	dBc
Jitter Generation	J _{GEN}	$f_{IN} = f_{OUT} = 622.08 \text{ MHz},$ $BW = 120 \text{ Hz}$ $LVPECL \text{ output}$ 12 kHz-20 MHz	_	350	410	fs rms
		50 kHz-80 MHz	_	410	_	fs rms
*Note: fin = fout = 622.08 MHz; B	W = 120 Hz: L	.VDS.	1		1	1

Table 6. Thermal Characteristics 1,2

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Maximum Junction Temperature			_	125	_	°C
Thermal Resistance Junction to Ambient	ΨЈА	Still Air Air Flow 1 m/s Air Flow 2 m/s Air Flow 3 m/s	_ _ _ _	16 14 13 12		°C/W
Thermal Resistance Junction to Case	ФЛС	Still Air	_	3.4	_	°C/W

Notes:

- 1. In most circumstances the Si5376 does not require special thermal management. A system level thermal analysis is strongly recommend. Contact Skyworks Solutions applications for further details if required.
- 2. Thermal characteristic for the 80-pin Si5376 on an 8-layer PCB.


Table 7. Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
DC Supply Voltage	V_{DD}	-0.5 to 2.8	V
LVCMOS Input Voltage	V _{DIG}	-0.3 to (V _{DD} + 0.3)	V
CLKINnP/N_q	CKN _{VIN}	0 to V _{DD}	V
OSC_P, OSC_N Voltage Limits	OSC _{VIN}	0 to 1.2	V
Operating Junction Temperature	T _{JCT}	-55 to 150	°C
Storage Temperature Range	T _{STG}	-55 to 150	°C
ESD HBM Tolerance (100 pF, 1.5 k); All pins except CKINnP/N-q		2	kV
ESD MM Tolerance; All pins except CKINnP/N_q		200	V
ESD HBM Tolerance (100 pF, 1.5 k); CKINnP/N_q		700	V
ESD MM Tolerance; CKINnP/N_q		125	V
Latch-Up Tolerance		JESD78 Compliant	

Note: Permanent device damage may occur if the absolute maximum ratings are exceeded. Functional operation should be restricted to the conditions as specified in the operation sections of this data sheet. Exposure to absolute maximum rating conditions for extended periods of time may affect device reliability.

2. Typical Application Schematic

4-Port 10G Line Card with SyncE and IEEE1588 Independent Port Timing



3. Typical Phase Noise Plot

- 155.52 MHz input
- 698.8123 MHz OTU4 output
- 295 fs RMS jitter (12 kHz to 20 MHz)




Figure 3. Typical Phase Noise Plot

15

4. Functional Description




Figure 4. Functional Block Diagram

The Si5376 is a highly integrated jitter-attenuating clock multiplier that integrates four fully independent DSPLLs and provides ultra-low jitter generation with less than 410 fs RMS. Configuration and control of the Si5376 is mainly handled through the I²C interface. The device accepts clock inputs ranging from 2 kHz to 710 MHz and generates independent, synchronous clock outputs ranging from 2 kHz to 808 MHz for each DSPLL. Virtually any frequency translation (M/N) combination across its operating range is supported. The Si5376 supports a digitally programmable loop bandwidth that can range from 60 Hz to 8.4 kHz requiring no external loop filter components. An external single-ended or differential reference clock or XO is required for the device to enable ultra-low jitter generation and jitter attenuation.

The device monitors each input clock for loss-of-signal (LOS) and provides a LOS alarm when missing pulses on any of the input clocks are detected. The device monitors the lock status of each DSPLL and provides a Loss-of-Lock (LOL) alarm when the DSPLL is unlocked. The lock detect algorithm continuously monitors the phase of the selected input clock in relation to the phase of the feedback clock. The Si5376 provides a holdover capability that allows the device to continue generation of a stable output clock when the input reference is lost. The reference oscillator can be internally routed into CKIN2_q, so free-running clock generation is supported for each DSPLL offering simultaneous synchronous and asynchronous operation.

The output drivers are configurable to support common signal formats, such as LVPECL, LVDS, CML, and CMOS loads. If the CMOS signal format is selected, each differential output buffer generates two in-phase CMOS clocks at the same frequency. For system-level debugging, a DSPLL bypass mode drives the clock output directly from the selected input clock, bypassing the internal DSPLL.

Skyworks Solutions offers a PC-based software utility, Si537xDSPLLsim that can be used to determine valid frequency plans and loop bandwidth settings to simplify device setup. Si537xDSPLLsim provides the optimum input, output, and feedback divider values for a given input frequency and clock multiplication ratio that minimizes phase noise. This utility can be downloaded from https://www.skyworksinc.com/en/Application-Pages/DSPLL. For further assistance, refer to the Si53xx Any-Frequency Precision Clocks Family Reference Manual.

5. Si5376 Application Examples and Suggestions

5.1. Schematic and PCB Layout

For a typical application schematic and PCB layout, see the Si537x-EVB Evaluation Board User's Guide, which can be downloaded from https://www.skyworksinc.com/technical%20documents.

In order to preserve the ultra low jitter of the Si5376 in applications where the four different DSPLL's are each operating at different frequency, special care and attention must be paid to the PCB layout. The following is a list of rules that should be observed:

- 1. The four Vdd supplies should be isolated from one another with four ferrite beads. They should be separately bypassed with capacitors that are located very close to the Si5376 device.
- 2. Use a solid and undisturbed ground plane for the Si5376 and all of the clock input and output return paths.
- 3. For applications that wish to logically connect the four RESET signals, do not tie them together underneath the BGA package. Instead connect them outside of the BGA footprint.
- 4. As much as is possible, do not route clock input and output signals underneath the BGA package. The clock output signals should go directly outwards from the BGA footprint.
- 5. Avoid placing the OSC_P and OSC_N signals on the same layer as the clock outputs. Add grounded guard traces surrounding the OSC_P and OSC_N signals.
- 6. Where possible, place the CKOUT and CKIN signals on separate PCB layers with a ground layer between them. The use of ground guard traces between all clock inputs and outputs is recommended.

For more information, see the Si537x-EVB Evaluation Board User's Guide and Appendix I of the Si53xx Reference Manual, Rev 0.5 or higher.

5.2. Thermal Considerations

The Si5376 dissipates a significant amount of heat and it is important to take this into consideration when designing the Si5376 operating environment. Among other issues, high die temperatures can result in increased jitter and decreased long term reliability. It is therefore recommended that one or more of the following occur:

- 1. Use a heat sink—A heat sink example is Aavid part number 375324B00035G.
- 2. Use a Vdd voltage of 1.8 V.
- 3. Limit the ambient temperature to significantly less that 85 °C.
- 4. Implement very good air flow.

5.3. SCL Leakage

When selecting pull up resistors for the two I^2C signals, note that there is an internal pull down resistor of 18 k Ω from the SCL pin to ground. This comment does not apply to the SDA pin.

5.4. RSTL_x Pins

It is recommended that the four RSTL_x pins (RSTL_A, RSTL_B, RSTL_C and RSTL_D) be logically connected together such that all four DSPLLs are either in or out of reset mode. When a DSPLL is in reset mode, its VCO will not be locked to any signal and may drift across its operating range. If a drifting VCO has a frequency similar to that of an operating VCO, there could be some crosstalk between the two VCOs. To avoid this from occurring during device initialization, DSPLLsim loads each DSPLL with default Free Run frequency plans with VCO values apart from one another. If the four RSTL_x pins are directly connected to one another, the connections should not be made directly underneath the BGA package. Instead, the connections should be made outside the package footprint.

5.5. Reference Oscillator Selection

Care should be taken during the selection of the external oscillator that is connected to the OSC_P and OSC_N pins. There is no jitter attenuation from the OSC reference inputs to the output; so, to achieve low output jitter, a low-jitter reference OSC must be used. Also, the output drift during holdover will be the same as the drift of the OSC reference. For example, a Stratum 3 application will require an OSC reference source that has Stratum 3 stability (though Stratum 3 accuracy is not required).

The OSC frequency can be any value from 109 to 125.5 MHz. See the RATE_REG (reg 2) description. Alternately, for applications with less demanding jitter requirements, the OSC frequency can be in the range from 37 to 41 MHz. For applications that use Free Run mode, the freedom to use any OSC frequency within these bands can be used to select an OSC frequency that has an integer relationship to the desired output frequency, which will make it easier to find a high-performance frequency plan.

If Free Run is not being used, an OSC frequency that is not integer-related to the output frequency is preferred. A recommended choice for an external oscillator is the Skyworks Solutions 530EB121M109DG, which is a 2.5 V, LVPECL device with a temperature stability of 20 ppm. It was used to take the typical phase noise plot on page 14. For more details and a more complete discussion of these topics, see the Si53xx Reference Manual.

5.6. Alarms

To assist in the programming of the IRQ_n pins, refer to the below diagram of the Si5376 alarm structure.




Figure 5. Si5376 Alarm Structure

5.7. OSC_P and OSC_N Connection

Figures 6, 7, and 8 show examples of connecting various OSC reference sources to the OSC_P and OSC_N pins. A crystal may not be used in place of an external oscillator.




Figure 6. Differential OSC Reference Input Example for Si5376




Figure 7. Single-Ended OSC Reference Input Example for Si5376




Figure 8. Single-Ended, 2.5 V, CMOS XO Connection

6. Register Map

The Si5376 has four identical register maps for each DSPLL. Each DSPLL has a unique I²C address enabling independent control and device configuration. The I²C address is 11010 [A1] [A0] for the entire device. Each corresponding DSPLL [A1] [A0] address is fixed as below.

[A1] [A0]

DSPLLA: 0 0
DSPLLB: 0 1
DSPLLC: 1 0
DSPLLD: 1 1

Note: The Si5376 register map is similar, but not identical, to the Si5324 device.

All register bits that are not defined in this map should always be written with the specific reset values. Writing to these bits with values other than the specified reset values may result in undefined device behavior. Registers not listed, such as Register 64, should never be written to.

Table 8. Si5376 Registers

Reg.	D7	D6	D5	D4	D3	D2	D1	D0	
0		FREE_RU N	CKOUT_ ALWAYS_ON				BYPASS_REG		
1					CK_PRI	OR2[1:0]	CK_PRI	CK_PRIOR1[1:0]	
2		BWSEL	_REG[3:0]			RATE_	REG [3:0]		
3	CKSEL_F	REG[1:0]	DHOLD	SQ_ICAL					
4	AUTOSEL_	_REG[1:0]				HIST_DEL[4:0	0]		
5	ICMOS	S[1:0]							
6			SF	OUT2_REG[2:0}		SFOUT1_REG[2:0	0]	
7							FOSREFSEL[2:0]	
8	HLOG_	_2[1:0]	HLOG_	1[1:0]					
9	HIST_AVG[4:0]		0]						
10					DSBL2_REG	DSBL1_REG			
11							PD_CK2	PD_CK1	
19	FOS_EN	FOS_	THR[1:0]	VALTIME[1:0]		LOCKT[2:0]			
20					Write 0	Write 0	LOL_PIN	IRQ_PIN	
21	Write 0	Write 0					CK1_ACT- V_PIN	CKSEL_PIN	
22					CK_ACTV_ POL		LOL_POL	INT_POL	
23						LOS2_MSK	LOS1_MSK	LOSX_MSK	
24						FOS2_MSK	FOS1_MSK	LOL_MSK	
25		N1_HS[2:0]							
31						NC1_L	S[19:16]		
32				N	IC1_LS[15:8]				

Table 8. Si5376 Registers (Continued)

Reg.	D7	D6	D5	D4	D3	D2	D1	D0	
33		1	I	N	IC1_LS[7:0]	l	1	l	
34						NC2_I	LS[19:16]		
35		ı	1	N	C2_LS[15:8]				
36				N	IC2_LS[7:0]				
40		N2_HS[2:0]				N2_L	S[19:16]		
41		·							
42					N2_LS[7:0]				
43							N31[18:16]		
44		N31[15:8]							
45					N31[7:0]				
46							N32[18:16]		
47		N32[15:8]							
48					N32[7:0]				
55			(CLKIN2RATE[2	:0]		CLKIN1RATE[2:0)]	
128							CK2_ACT- V_REG	CK1_ACT- V_REG	
129						LOS2_INT	LOS1_INT	LOSX_INT	
130		DIGHOLD VALID				FOS2_INT	FOS1_INT	LOL_INT	
131						LOS2_FLG	LOS1_FLG	LOSX_FLG	
132					FOS2_FLG	FOS1_FLG	LOL_FLG		
134		1	I	PAR	TNUM_RO[11:4]	l	1	ı	
135		PARTNU	JM_RO[3:0]			REVID	D_RO[3:0]		
136	RST_REG	ICAL							
137								FASTLOCK	
138							LOS2_EN [1:1]	LOS1_EN [1:1]	
139			LOS2_EN[0: 0]	LOS1_EN[0: 0]			FOS2_EN	FOS1_EN	
142				INDEPE	NDENTSKEW1[7	7:0]			
143				INDEPE	NDENTSKEW2[7	7:0]			

7. Register Descriptions

Register 0.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name		FREE_RUN	CKOUT_ALWAYS_ON				BYPASS_REG	
Туре	R	R/W	R/W	R	R	R	R/W	R

Reset value = 0001 0100

Bit	Name	Function
7	Reserved	Reserved.
6	FREE_RUN	Free Run. Internal to the device, route XA/XB to CKIN2. This allows the DSPLL to lock to its XA-XB reference to support free-running clock generation. 0: Disable 1: Enable
5	CKOUT_ALWAYS_ON	CKOUT Always On. This will bypass the SQ_ICAL function. Output will be available even if SQ_I-CAL is on and ICAL is not complete or successful. See Table 9 on page 55. 0: Squelch output until device is calibrated (ICAL). 1: Provide an output. Notes: 1. The frequency may be significantly off until the device is calibrated. 2. Must be set to 1 to control output to output skew.
4:2	Reserved	Reserved.
1	BYPASS_REG	Bypass Register. This bit enables or disables PLL bypass mode. Use only when the device is in digital hold or before the first ICAL. Bypass mode does not support CMOS clock outputs. 0: Normal operation 1: Bypass mode. Selected input clock is connected to CKOUT buffers, bypassing PLL.
0	Reserved	Reserved.

Register 1.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name					CK_PRIC	DR2 [1:0]	CK_PRIC	OR1 [1:0]
Туре		F	₹		R/W R/W		W	

Reset value = 1110 0100

Bit	Name	Function
7:4	Reserved	
3:2	CK_PRIOR2 [1:0]	2nd Priority Input Clock. Selects which of the input clocks will be 2nd priority in the autoselection state machine. 00: CKIN1 is 2nd priority. 01: CKIN2 is 2nd priority. 10: Reserved 11: Reserved
1:0	CK_PRIOR1 [1:0]	1st Priority Input Clock. Selects which of the input clocks will be 1st priority in the autoselection state machine. 00: CKIN1 is 1st priority. 01: CKIN2 is 1st priority. 10: Reserved 11: Reserved

Register 2.

Bit	D7	D6	D5	D4	D3	D2	D1	D0	
Name		BWSEL_I	REG [3:0]		RATE_REG[3:0]				
Туре		R/	W			R/	W		

Reset value = 0100 0010

Bit	Name	Function					
7:4	BWSEL_REG [3:0]	BWSEL_REG.					
		Selects nominal f3dB bandwidth for PLL. See Si53xDSPLLsim for settings. After BWSEL_REG is written with a new value, an ICAL is required for the change to take effect.					
3:0	RATE_REG [3:0]	RATE Setting for Oscillator.					
		An external oscillator or other clock source must be used. It is not possible to use just a crystal.					
		Setting	Minimum	Recommended	Maximum	Units	
		0101	37	40	41	MHz	
		0110 109 121.109 125.5 MHz					
		Others: Reserved					

Register 3.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name	CKSEL_	REG[1:0]	DHOLD	SQ_ICAL				
Туре	R	/W	R/W	R/W	R	R	R	R

Reset value = 0000 0101

Bit	Name	Function
7:6	CKSEL_REG [1:0]	CKSEL_REG.
		If the device is operating in register-based manual clock selection mode (AUTOSEL_REG = 00), and CKSEL_PIN = 0, then these bits select which input clock will be the active input clock. If CKSEL_PIN = 1 and AUTOSEL_REG = 00, the CS_CA input pin continues to control clock selection and CKSEL_REG is of no consequence. 00: CKIN_1 selected. 01: CKIN_2 selected. 10: Reserved
5	DHOLD	DHOLD.
		Forces the device into digital hold. This bit overrides all other manual and automatic clock selection controls. 0: Normal operation.
		1: Force digital hold mode. Overrides all other settings and ignores the quality of the input clocks.
4	SQ_ICAL	SQ_ICAL.
		This bit determines if the output clocks will remain enabled or be squelched (disabled) during an internal calibration. See Table 9 on page 55. 0: Output clocks enabled during ICAL. 1: Output clocks disabled during ICAL.
3:0	Reserved	

Register 4.

Bit	D7	D6	D5	D4	D3	D2	D1	D0	
Name	AUTOSEL_REG [1:0]		HIST_DEL [4:0]						
Туре	R/W		R			R/W			

Reset value = 0001 0010

Bit	Name	Function
7:6	AUTOSEL_REG [1:0]	AUTOSEL_REG [1:0].
		Selects input clock selection control method. 00: Manual (either register or pin controlled, see CKSEL_PIN) 01: Automatic non-revertive 10: Automatic revertive 11: Reserved
5	Reserved	
4:0	HIST_DEL [4:0]	HIST_DEL [4:0].
		Selects amount of delay to be used in generating the history information used for Digital Hold.

Register 5.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name	ICMOS [1:0]							
Туре	R/W		R	R	R	R	R	R

Reset value = 1110 1101

Bit	Name	Function
7:6	ICMOS [1:0]	ICMOS [1:0].
		When the output buffer is set to CMOS mode, these bits determine the output buffer drive strength. The first number below refers to 2.5 V operation; the second to 1.8 V operation. These values assume CKOUT+ is tied to CKOUT 00: 5 mA/1.75 mA 01: 10 mA/3.5 mA 10: 15 mA/5.5 mA
5:0	Reserved	

Register 6.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name			SFO	SFOUT2_REG [2:0]			OUT1_REG [2:0]
Туре	R	R		R/W			R/W	

Reset value = 0010 1101

Bit	Name	Function
7:6	Reserved	
5:3	SFOUT2_ REG [2:0]	SFOUT2_REG [2:0]. Controls output signal format and disable for CKOUT2 output buffer. 000: Reserved 001: Disable CKOUT2 010: CMOS (Bypass mode not supported) 011: Low swing LVDS 100: Reserved 101: LVPECL (not available when V _{DD} = 1.8 V) 110: CML 111: LVDS
2:0	SFOUT1_ REG [2:0]	SFOUT1_REG [2:0]. Controls output signal format and disable for CKOUT1 output buffer. 000: Reserved 001: Disable CKOUT1 010: CMOS (Bypass mode not supported) 011: Low swing LVDS 100: Reserved 101: LVPECL (not available when V _{DD} = 1.8 V) 110: CML 111: LVDS

27

Register 7.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name						FOSREFSEL [2:0]		
Туре	R	R	R	R	R	R/W		

Reset value = 0010 1010

Bit	Name	Function
7:3	Reserved	
2:0	FOSREFSEL [2:0]	FOSREFSEL [2:0]. Selects which input clock is used as the reference frequency for Frequency offset (FOS) monitoring. 000: OSC (External reference) 001: CKIN1 010: CKIN2 011: Reserved 100: Reserved 111: Reserved

Register 8.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name	HLOG.	_2[1:0]	HLOG_1[1:0]					
Туре	R/W		R/W		R	R	R	R

Reset value = 0000 0000

Bit	Name	Function
7:6	HLOG_2 [1:0]	HLOG_2 [1:0]. 00: Normal operation 01: Holds CKOUT2 output at static logic 0. Entrance and exit from this state will occur without glitches or runt pulses. 10:Holds CKOUT2 output at static logic 1. Entrance and exit from this state will occur without glitches or runt pulses. 11: Reserved
5:4	HLOG_1 [1:0]	
3:0	Reserved	

Register 9.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name		Н	IST_AVG [4:0					
Туре			R/W	R	R	R		

Reset value = 1100 0000

Bit	Name	Function
7:3	HIST_AVG [4:0]	HIST_AVG [4:0].
		Selects amount of averaging time to be used in generating frequency history information for Digital Hold.
2:0	Reserved	

Register 10.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name					DSBL2_REG	DSBL1_REG		
Туре	R	R	R	R	R/W	R/W	R	R

Reset value = 0000 0000

Bit	Name	Function
7:4	Reserved	
3	DSBL2_REG	DSBL2_REG. This bit controls the powerdown of the CKOUT2 output buffer. If disable mode is selected, the NC2 output divider is also powered down. 0: CKOUT2 enabled 1: CKOUT2 disabled
2	DSBL1_REG	DSBL1_REG. This bit controls the powerdown of the CKOUT1 output buffer. If disable mode is selected, the NC1 output divider is also powered down. 0: CKOUT1 enabled 1: CKOUT1 disabled
1:0	Reserved	

Register 11.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name							PD_CK2	PD_CK1
Туре	R	R	R	R	R	R	R/W	R/W

Reset value = 0100 0000

Bit	Name	Function
7:2	Reserved	
1	PD_CK2	PD_CK2. This bit controls the powerdown of the CKIN2 input buffer. 0: CKIN2 enabled 1: CKIN2 disabled
0	PD_CK1	PD_CK1. This bit controls the powerdown of the CKIN1 input buffer. 0: CKIN1 enabled 1: CKIN1 disabled

Register 19.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name	FOS_EN	FOS_THR [1:0]		VALTIME [1:0]		LOCKT [2:0]		
Туре	R/W	R/	/W	R/	/W	R/W		

Reset value = 0010 1100

Bit	Name	Function
7:5	FOS_EN	FOS_EN. Frequency Offset Enable globally disables FOS. See the individual FOS enables (FOS-X_EN, register 139). 0: FOS disable 1: FOS enabled by FOSx_EN
6:5	FOS_THR [1:0]	FOS_THR [1:0]. Frequency Offset at which FOS is declared: 00: ± 11 to 12 ppm (Stratum 3/3E compliant, with a Stratum 3/3E used for REFCLK. 01: ± 48 to 49 ppm SONET Minimum Clock (SMC) with SMC used for REFCLK. 10: ± 30 ppm (SONET Minimum Clock (SMC), with a Stratum 3/3E used for REFCLK. 11: ± 200 ppm
4:3	VALTIME [1:0]	VALTIME [1:0]. Sets amount of time for input clock to be valid before the associated alarm is removed. 00: 2 ms 01: 100 ms 10: 200 ms 11: 13 seconds
2:0	LOCKT [2:0]	LOCKT [2:0]. Sets retrigger interval for one shot monitoring phase detector output. One shot is triggered by phase slip in DSPLL. To minimize lock time during an ICAL, a LOCKT value of 001 is recommended. Refer to the Family Reference Manual for more details. 000: 106 ms 001: 53 ms 010: 26.5 ms 011: 13.3 ms 100: 6.6 ms 101: 3.3 ms 110: 1.66 ms 111: 0.833 ms

Register 20.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name					Write 0	Write 0	LOL_PIN	IRQ_PIN
Туре	R	R	R	R	W	W	R/W	R/W

Reset value = 0011 1110

Bit	Name	Function
7:4	Reserved	
3:2	Write 0	Write to zero.
1	LOL_PIN	LOL_PIN. The LOL_INT status bit can be reflected on the LOL output pin. 0: LOL output pin tristated 1: LOL_INT status reflected to output pin
0	IRQ_PIN	IRQ_PIN. Reflects interrupt status on the IRQ output pin. 0: Output is disabled. 1: Output is enabled.

Register 21.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name	Write 0	Write 0					CK1_ACTV_PIN	CKSEL_ PIN
Туре	W	W	R	R	R	R	R/W	R/W

Reset value = 1111 1111

Bit	Name	Function
7:6	Write 0	Write zero.
5:2	Reserved	
1	CK1_ACTV_PIN	CK1_ACTV_PIN. The CK1_ACTV_REG status bit can be reflected to the CS_CA output pin using the CK1_ACTV_PIN enable function. CK1_ACTV_PIN is of consequence only when pin controlled clock selection is being used. 0: CS_CA output pin tristated. 1: Clock Active status reflected to output pin.
0	CKSEL_PIN	CKSEL_PIN. If manual clock selection is used, clock selection can be controlled via the CKSEL_REG[1:0] register bits or the CS_CA input pin. This bit is only active when AUTOSEL_REG = Manual. 0: CS_CA pin ignored. CKSEL_REG[1:0] register bits control clock selection. 1: CS_CA input pin controls clock selection.

Register 22.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name					CK_ACTV_POL		LOL_POL	INT_POL
Туре	R	R	R	R	R/W	R	R/W	R/W

Reset value = 1101 1111

Bit	Name	Function
7:4	Reserved	
3	CK_ACTV_ POL	CK_ACTV_POL. Sets the active polarity for the CS_CA signals when reflected on an output pin. 0: Active low 1: Active high
2	Reserved	
1	LOL_POL	LOL_POL. Sets the active polarity for the LOL status when reflected on an output pin. 0: Active low 1: Active high
0	INT_POL	INT_POL. Sets the active polarity for the interrupt status when reflected on the INT_C1B output pin. 0: Active low 1: Active high

Register 23.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name						LOS2_MSK	LOS1_MSK	LOSX_MSK
Туре	R	R	R	R	R	R/W	R/W	R/W

Reset value = 0001 1111

Bit	Name	Function
7:3	Reserved	
2	LOS2_MSK	LOS2_MSK. Determines if a LOS on CKIN2 (LOS2_FLG) is used in the generation of an interrupt. Writes to this register do not change the value held in the LOS2_FLG register.
		O: LOS2 alarm triggers active interrupt on IRQ output (if IRQ=1). LOS2_FLG ignored in generating interrupt output.
1	LOS1_MSK	LOS1_MSK. Determines if a LOS on CKIN1 (LOS1_FLG) is used in the generation of an interrupt. Writes to this register do not change the value held in the LOS1_FLG register. 0: LOS1 alarm triggers active interrupt on IRQ output (if IRQ=1). 1: LOS1_FLG ignored in generating interrupt output.
0	LOSX_MSK	LOSX_MSK. Determines if a LOS on OSC (LOSX_FLG) is used in the generation of an interrupt. Writes to this register do not change the value held in the LOSX_FLG register. 0: LOSX alarm triggers active interrupt on IRQ output (if IRQ=1). 1: LOSX_FLG ignored in generating interrupt output.

Register 24.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name						FOS2_MSK	FOS1_MSK	LOL_MSK
Туре	R	R	R	R	R	R/W	R/W	R/W

Reset value = 0011 1111

Bit	Name	Function
7:3	Reserved	
2	FOS2_MSK	FOS2_MSK.
		Determines if the FOS2_FLG is used in the generation of an interrupt. Writes to this register do not change the value held in the FOS2_FLG register. 0: FOS2 alarm triggers active interrupt on IRQ output (if IRQ_PIN=1). 1: FOS2_FLG ignored in generating interrupt output.
1	FOS1_MSK	FOS1_MSK.
	_	Determines if the FOS1_FLG is used in the generation of an interrupt. Writes to this register do not change the value held in the FOS1_FLG register. 0: FOS1 alarm triggers active interrupt on IRQ output (if IRQ_PIN=1). 1: FOS1_FLG ignored in generating interrupt output.
0	LOL_MSK	LOL_MSK.
		Determines if the LOL_FLG is used in the generation of an interrupt. Writes to this register do not change the value held in the LOL_FLG register. 0: LOL alarm triggers active interrupt on IRQ output (if IRQ_PIN=1). 1: LOL_FLG ignored in generating interrupt output.

Register 25.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name	N1_HS [2:0]							
Туре	R/W			R	R	R	R	R

Reset value = 0010 0000

Bit	Name	Function
7:5	N1_HS [2:0]	N1_HS [2:0].
		Sets value for N1 high speed divider which drives NCn_LS (n = 1 to 2) low-speed divider. 000: N1 = 4 001: N1 = 5 010: N1 = 6 011: N1 = 7 100: N1 = 8 101: N1 = 9 110: N1 = 10 111: N1 = 11
4:0	Reserved	

Register 31.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name						NC1_LS	S [19:16]	
Туре	R	R	R	R		R/	W	

Reset value = 0000 0000

Bit	Name	Function
7:4	Reserved	
3:0	NC1_LS [19:16]	NC1_LS [19:16]. Sets value for NC1 low-speed divider, which drives CKOUT1 output. Must be 0 or odd. 000000000000000000000 = 1 00000000000

Register 32.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name		NC1_LS [15:8]						
Туре				R/	W			

Reset value = 0000 0000

Bit	Name	Function
7:0	NC1_LS [15:8]	NC1_LS [15:8]. Sets value for NC1 low-speed divider, which drives CKOUT1 output. Must be 0 or odd. 000000000000000000000 = 1 00000000000

Register 33.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name		NC1_LS [7:0]						
Туре				R/	W			

Reset value = 0011 0001

Bit	Name	Function
7:0	NC1_LS [19:0]	NC1_LS [7:0]. Sets value for NC1 low-speed divider, which drives CKOUT1 output. Must be 0 or odd. 000000000000000000000 = 1 00000000000

Register 34.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name						NC2_LS	S [19:16]	
Туре	R	R	R	R		R/	W	

Reset value = 0000 0000

Bit	Name	Function
7:4	Reserved	
3:0	NC2_LS [19:16]	NC2_LS [19:16]. Sets value for NC2 low-speed divider, which drives CKOUT2 output. Must be 0 or odd. 0000000000000000000000000000000000

Register 35.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name		NC2_LS [15:8]						
Туре				R/	W			

Bit	Name	Function
7:0	NC2_LS [15:8]	NC2_LS [15:8].
		Sets value for NC2 low-speed divider, which drives CKOUT2 output. Must be 0 or odd. $00000000000000000000000000000000000$

Register 36.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name		NC2_LS [7:0]						
Туре				R/	W			

Reset value = 0011 0001

Bit	Name	Function
7:0	NC2_LS [7:0]	NC2_LS [7:0].
		Sets value for NC2 low-speed divider, which drives CKOUT2 output. Must be 0 or odd. $00000000000000000000000000000000000$

Register 40.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name	N2_HS [2:0]					N2_LS	[19:16]	
Туре	R/W			R		R/	W	

Reset value = 1100 0000

Bit	Name	Function
7:5	N2_HS [2:0]	N2_HS [2:0].
		Sets value for N2 high speed divider which drives N2LS low-speed divider.
		000: 4
		001: 5
		010: 6
		011: 7
		100: 8
		101: 9
		110: 10
		111: 11
4	Reserved	
3:0	N2_LS [19:16]	N2_LS [19:16].
		Sets value for N2 low-speed divider, which drives phase detector.
		00000000000000001 = 2
		0000000000000011 = 4
		00000000000000101 = 6
		$ 1111111111111111111 = 2^{20}$
		Valid divider values = [2, 4, 6,, 2 ²⁰]

Register 41.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name		N2_LS [15:8]						
Туре				R/	W			

Reset value = 0000 0000

Bit	Name	Function
7:0	N2_LS [15:8]	N2_LS [15:8].
		Sets value for N2 low-speed divider, which drives phase detector. 0000000000000000001 = 2 0000000000000000011 = 4 00000000000000000101 = 6
		1111111111111111 = 2^{20} Valid divider values = [2, 4, 6,, 2^{20}]

Register 42.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name		N2_LS [7:0]						
Туре				R/	W			

Reset value = 1111 1001

Bit	Name	Function
7:0	N2_LS [7:0]	N2_LS [7:0].
		Sets value for N2 low-speed divider, which drives phase detector. $000000000000000001 = 2 \\ 000000000000000011 = 4 \\ 00000000000000101 = 6 \\ \dots \\ 1111111111111111111 = 2^{20}$
		Valid divider values = [2, 4, 6,, 2 ²⁰]

Register 43.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name							N31 [18:16]	
Туре	R	R	R	R	R		R/W	

Reset value = 0000 0000

Bit	Name	Function
7:3	Reserved	
2:0	N31 [18:16]	N31 [18:16].
		Sets value for input divider for CKIN1. 00000000000000000 = 1
		00000000000000001 = 2
		00000000000000010 = 3
		111111111111111 = 2^{19} Valid divider values = [1, 2, 3,, 2^{19}]

Register 44.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name		N31_[15:8]						
Туре				R/	W			

Bit	Name	Function
7:0	N31_[15:8]	N31_[15:8].
		Sets value for input divider for CKIN1. $000000000000000000000000000000000000$

Register 45.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name			N31_[7:0]					
Туре				R/	W			

Reset value = 0000 1001

Bit	Name	Function
7:0	N31_[7:0	N31_[7:0].
		Sets value for input divider for CKIN1.
		00000000000000000 = 1
		00000000000000001 = 2 00000000000000010 = 3
		 1111111111111111 = 2 ¹⁹
		Valid divider values = [1, 2, 3,, 2 ¹⁹]

Register 46.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name							N32_[18:16]	
Туре	R	R	R	R	R		R/W	

Bit	Name	Function
7:3	Reserved	
2:0	N32_[18:16]	N32_[18:16].
		Sets value for input divider for CKIN1. $000000000000000000000000000000000000$

Register 47.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name		N32_[15:8]						
Туре		R/W						

Reset value = 0000 0000

Bit	Name	Function
7:0	N32_[15:8]	N32_[15:8].
		Sets value for input divider for CKIN2. 000000000000000000 = 1 000000000000000001 = 2 000000000000000010 = 3
		1111111111111111 = 2^{19} Valid divider values = [1, 2, 3,, 2^{19}]

Register 48.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name		N32_[7:0]						
Туре				R/	W			

Bit	Name	Function
7:0	N32_[7:0]	N32_[7:0].
		Sets value for input divider for CKIN2.
		00000000000000000 = 1
		00000000000000001 = 2
		0000000000000010 = 3
		 111111111111111 = 2 ¹⁹
		Valid divider values = [1, 2, 3,, 2 ¹⁹]

Register 55.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name			CLKIN2RATE[2:0] CLKIN1RATE[2:0]				:0]	
Туре	R	R	R/W				R/W	

Bit	Name	Function
7:6	Reserved	
5:3	CLKIN2RATE[2:0]	CLKIN2RATE_[2:0].
		CKINn frequency selection for FOS alarm monitoring.
		000: 10–27 MHz
		001: 25–54 MHz
		002: 50–105 MHz
		003: 95–215 MHz
		004: 190–435 MHz
		005: 375–710 MHz
		006: Reserved
		007: Reserved
2:0	CLKIN1RATE [2:0]	CLKIN1RATE[2:0].
		CKINn frequency selection for FOS alarm monitoring.
		000: 10–27 MHz
		001: 25–54 MHz
		002: 50–105 MHz
		003: 95–215 MHz
		004: 190–435 MHz
		005: 375–710 MHz
		006: Reserved
		007: Reserved

Register 128.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name							CK2_ACTV_REG	CK1_ACTV_REG
Туре	R	R	R	R	R	R	R	R

Reset value = 0010 0000

Bit	Name	Function
7:2	Reserved	
1	CK2_ACTV_REG	CK2_ACTV_REG. Indicates if CKIN2 is currently the active clock for the DSPLL input. 0: CKIN2 is not the active input clock. Either it is not selected or LOS2_INT is 1. 1: CKIN2 is the active input clock.
0	CK1_ACTV_REG	CK1_ACTV_REG. Indicates if CKIN1 is currently the active clock for the DSPLL input. 0: CKIN1 is not the active input clock. Either it is not selected or LOS1_INT is 1. 1: CKIN1 is the active input clock.

Register 129.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name						LOS2_INT	LOS1_INT	LOSX_INT
Туре	R	R	R	R	R	R	R	R

Bit	Name	Function
7:3	Reserved	
2	LOS2_INT	LOS2_INT.
		Indicates the LOS status on CKIN2.
		0: Normal operation.
		1: Internal loss-of-signal alarm on CKIN2 input.
1	LOS1_INT	LOS1_INT.
		Indicates the LOS status on CKIN1.
		0: Normal operation.
		1: Internal loss-of-signal alarm on CKIN1 input.
0	LOSX_INT	LOSX_INT.
		Indicates the LOS status of the external reference on the OSC pins.
		0: Normal operation.
		1: Internal loss-of-signal alarm on OSC reference clock input.

Register 130.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name		DIGHOLDVALID				FOS2_INT	FOS1_INT	LOL_INT
Туре	R	R	R	R	R	R	R	R

Bit	Name	Function
7	Reserved	
6	DIGHOLDVALID	Digital Hold Valid.
		Indicates if the digital hold circuit has enough samples of a valid clock to meet digital hold specifications.
		0: Indicates digital hold history registers have not been filled. The digital hold output frequency may not meet specifications.
		1: Indicates digital hold history registers have been filled. The digital hold output frequency is valid.
5:3	Reserved	
2	FOS2_INT	CKIN2 Frequency Offset Status.
		0: Normal operation.
		1: Internal frequency offset alarm on CKIN2 input.
1	FOS1_INT	CKIN1 Frequency Offset Status.
		0: Normal operation.
		1: Internal frequency offset alarm on CKIN1 input.
0	LOL_INT	PLL Loss of Lock Status.
		0: PLL locked.
		1: PLL unlocked.

Register 131.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name						LOS2_FLG	LOS1_FLG	LOSX_FLG
Туре	R	R	R	R	R	R/W	R/W	R/W

Bit	Name	Function
7:3	Reserved	
2	LOS2_FLG	CKIN2 Loss-of-Signal Flag.
		0: Normal operation. 1: Held version of LOS2_INT. Generates active output interrupt if output interrupt pin is enabled (IRQ_PIN = 1) and if not masked by LOS2_MSK bit. Flag cleared by writing 0 to this bit.
1	LOS1_FLG	CKIN1 Loss-of-Signal Flag.
		0: Normal operation 1: Held version of LOS1_INT. Generates active output interrupt if output interrupt pin is enabled (IRQ_PIN = 1) and if not masked by LOS1_MSK bit. Flag cleared by writing 0 to this bit.
0	LOSX_FLG	External Reference (signal on pins XA/XB) Loss-of-Signal Flag.
		0: Normal operation 1: Held version of LOSX_INT. Generates active output interrupt if output interrupt pin is enabled (IRQ_PIN = 1) and if not masked by LOSX_MSK bit. Flag cleared by writing 0 to this bit.

Register 132.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name					FOS2_FLG	FOS1_FLG	LOL_FLG	
Туре	R	R	R	R	R/W	R/W	R/W	R

Bit	Name	Function
7:4	Reserved	
3	FOS2_FLG	CLKIN_2 Frequency Offset Flag.
		0: Normal operation. 1: Held version of FOS2_INT. Generates active output interrupt if output interrupt pin is enabled (IRQ_PIN = 1) and if not masked by FOS2_MSK bit. Flag cleared by writing 0 to this bit.
2	FOS1_FLG	CLKIN_1 Frequency Offset Flag.
		0: Normal operation 1: Held version of FOS1_INT. Generates active output interrupt if output interrupt pin is enabled (IRQ_PIN = 1) and if not masked by FOS1_MSK bit. Flag cleared by writing 0 to this bit.
1	LOL_FLG	PLL Loss of Lock Flag.
		0: PLL locked
		1: Held version of LOL_INT. Generates active output interrupt if output interrupt pin is enabled (IRQ_PIN = 1) and if not masked by LOL_MSK bit. Flag cleared by writing 0 to this bit.
0	Reserved	

Register 134.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name		PARTNUM_RO [11:4]						
Туре				F	₹			

Reset value = 0000 0001

Bi	t	Name	Function		
7:0)	PARTNUM_RO [11:0]	Device ID (1 of 2). 0000 0100 1100: Si5376 Others: Reserved		

Register 135.

Bit	D7	D6	D5	D4	D3	D2	D1	D0	
Name		PARTNUM	1_RO [3:0]		REVID_RO [3:0]				
Туре		R				F	₹		

Reset value = 1010 0010

Bit	Name	Function
7:4	PARTNUM_RO [11:0]	Device ID (2 of 2).
		0000 0100 1010: Si5376
		Others: Reserved
3:0	REVID_RO [3:0]	Indicates Device Revision Level.
		0010: Revision C
		Others: Reserved.

Register 136.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name	RST_REG	ICAL						
Туре	R/W	R/W	R	R	R	R	R	R

Reset value = 0000 0000

Bit	Name	Function
7	RST_REG	Internal Reset (Same as Pin Reset).
		Note: The I ² C port may not be accessed until 10 ms after RST_REG is asserted. 0: Normal operation.
		1: Reset all internal logic. Outputs disabled or tristated during reset.
6	ICAL	Start Internal Calibration Sequence.
		For proper operation, the device must go through an internal calibration sequence. ICAL is a self-clearing bit. Writing a one to this location initiates an ICAL. The calibration is complete once the LOL alarm goes low. A valid stable clock (within 100 ppm) must be present to begin ICAL. Note: Any divider, CLKINn_RATE or BWSEL_REG changes require an ICAL to take effect. 0: Normal operation. 1: Writing a "1" initiates internal self-calibration. Upon completion of internal self-calibration, LOL will go low.
5:0	Reserved	

Register 137.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name								FASTLOCK
Туре	R	R	R	R	R	R	R	R/W

Bit	Name	Function
7:1	Reserved	Do not modify.
0	FASTLOCK	This bit must be set to 1 to enable FASTLOCK.
		This improves initial lock time by dynamically changing the loop bandwidth during PLL lock acquisition.

Register 138.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name							LOS2_EN [1:1]	LOS1_EN [1:1]
Туре	R	R	R	R	R	R	R/W	R/W

Bit	Name	Function
7:2	Reserved	
1	LOS2_EN [1:0]	Enable CKIN2 LOS Monitoring on the Specified Input (2 of 2).
		Note: LOS2_EN is split between two registers. 00: Disable LOS monitoring.
		01: Reserved.
		10: Enable LOSA monitoring. 11: Enable LOS monitoring.
		LOSA is a slower and less sensitive version of LOS. See the Family Reference Manual for details.
0	LOS1_EN [1:0]	Enable CKIN1 LOS Monitoring on the Specified Input (1 of 2).
		Note: LOS1_EN is split between two registers. 00: Disable LOS monitoring. 01: Reserved. 10: Enable LOSA monitoring. 11: Enable LOS monitoring. LOSA is a slower and less sensitive version of LOS. See the Family Reference Manual for details.

53

Register 139.

Bit	D7	D6	D5	D4	D3	D2	D1	D0
Name			LOS2_EN [0:0]	LOS1_EN [0:0]			FOS2_EN	FOS1_EN
Туре	R	R	R/W	R/W	R	R	R/W	R/W

Reset value = 1111 1111

Bit	Name	Function
7:6	Reserved	
5	LOS2_EN [1:0]	Enable CKIN2 LOS Monitoring on the Specified Input (2 of 2).
		Note: LOS2_EN is split between two registers.
		00: Disable LOS monitoring.
		01: Reserved.
		10: Enable LOSA monitoring.
		11: Enable LOS monitoring.
		LOSA is a slower and less sensitive version of LOS. See the family reference manual for details.
	100 51111 01	
4	LOS_EN [1:0]	Enable CKIN1 LOS Monitoring on the Specified Input (1 of 2).
		Note: LOS1_EN is split between two registers.
		00: Disable LOS monitoring. 01: Reserved.
		10: Enable LOSA monitoring.
		11: Enable LOS monitoring.
		LOSA is a slower and less sensitive version of LOS. See the family reference manual
		for details.
3:2	Reserved	
1	FOS2_EN	Enables FOS on a Per Channel Basis.
		0: Disable FOS monitoring.
		1: Enable FOS monitoring.
0	FOS1_EN	Enables FOS on a Per Channel Basis.
		0: Disable FOS monitoring.
		1: Enable FOS monitoring.

Register 142.

Bit	D7	D6	D5	D4	D3	D2	D1	D0	
Name		INDEPENDENTSKEW1 [7:0]							
Туре		R/W							

Reset value = 0000 0000

Bit	Name	Function
7:0	INDEPENDENTSKEW1 [7:0]	INDEPENDENTSKEW1.
		Eight-bit field that represents a 2s complement of the phase offset in terms of clocks from the high speed output divider. Default = 0.

Register 143.

Bit	D7	D6	D5	D4	D3	D2	D1	D0	
Name		INDEPENDENTSKEW2 [7:0]							
Туре		R/W							

Bit	Name	Function
7:0	INDEPENDENTSKEW2 [7:0]	INDEPENDENTSKEW2.
		8 bit field that represents a twos complement of the phase offset in terms of clocks from the high speed output divider. Default = 0.

55


7.1. ICAL

The device registers must be configured for the device operation. After device configuration, a calibration procedure must be performed once a stable clock is applied to the selected CKINn input. The calibration process is triggered by writing a "1" to bit D6 in register 136. See the Family Reference Manual for details. In addition, after a successful calibration operation, changing any of the registers indicated in Table 9 requires that a calibration be performed again by the same procedure (writing a "1" to bit D6 in register 136).

Table 9. ICAL-Sensitive Registers

Address	Register
0	BYPASS_REG
0	CKOUT_ALWAYS_ON
1	CK_PRIOR1
1	CK_PRIOR2
2	BSWEL_REG
2	RATE_REG
4	HIST_DEL
5	ICMOS
7	FOSREFSEL
9	HIST_AVG
10	DSBL1_REG
10	DSBL2_REG
11	PD_CK1
11	PD_CK2
19	FOS_EN
19	FOS_THR
19	LOCKT
19	VALTIME
25	N1_HS
31	NC1_LS
34	NC2_LS
40	N2_HS
40	N2_LS
43	N31
46	N32
55	CLKIN1RATE
55	CLKIN2RATE

8. Pin Descriptions: Si5376



Bottom View

Figure 9. Si5376 Pin Configuration (Bottom View)

Table 10. Si5376 Pin Descriptions

Pin #	Pin Name	I/O	Signal Level	Description
D4 D6 F6 F4	RSTL_A RSTL_B RSTL_C RSTL_D	I	LVCMOS	External Reset. Active low input that performs external hardware reset of all four DSPLLs. Resets all internal logic to a known state and forces the device registers to their default value. Clock outputs are tri-stated during reset. The part must be programmed after a reset or power-on to get a clock output. This pin has a weak pull-up.
B4 D8 H6 F2	IRQ_A IRQ_B IRQ_C IRQ_D	0	LVCMOS	DSPLLq Interrupt Indicator. This pin functions as a device interrupt output. The interrupt output, IRQ_PINn must be set to 1. The pin functions as a maskable interrupt output with active polarity controlled by the IRQ_POLn register bit. 0 = CKINn present 1 = LOS (FOS) on CKINn The active polarity is controlled by CK_BAD_POL. If no function is selected, the pin tri-states.
C1, C4, B5 A7, D5, D7 E7, F5, G9 E3, F3, J3	VDD_A VDD_B VDD_C VDD_D	V _{DD}	Supply	Supply. The device operates from a 1.8 or 2.5 V supply. A 0.1 μF bypass capacitive is required for every VDD_9 pin. Bypass capacitors should be associated with the following VDD_q pins: 0.1 μF per VDD pin. Four 1.0 μF should also be placed as close to each VDD domain as is practical. See recommended layout.
E5 E6	OSC_P OSC_N	ı	Analog	External OSC. An external low jitter reference clock should be connected to these pins. See the any-frequency precision clocks family reference manual for oscillator selection details. e.g., IRQ_PIN. See Si5376 Register Map.

Table 10. Si5376 Pin Descriptions (Continued)

Pin #	Pin Name	I/O	Signal Level	Description
B2 A3 B3 E4 C8 A8 B8 C9 H7 J7 H8 H9 G1 H2 J2 G2	GND	GND	Supply	Ground for each DSPLLq. Must be connected to system ground. Minimize the ground path impedance for optimal performance of this device. See recommended layout.
C2 D2 C3 D3 B7 B6 C7 C6 G8 F8 G7 F7 H3 H4 G3 G4	CKIN1P_A CKIN1N_A CKIN2P_A CKIN2N_A CKIN2N_B CKIN1N_B CKIN2P_B CKIN2N_B CKIN1P_C CKIN1N_C CKIN2P_C CKIN2P_C CKIN2N_C CKIN1P_D CKIN1P_D CKIN1P_D CKIN2P_D CKIN2P_D	I	Multi	Clock Inputs for DSPLLq. Differential input clocks. This input can also be driven with a single-ended signal.
E2 C5 E8 H5	LOL_A LOL_B LOL_C LOL_D	O	LVCMOS	DSPLLq Loss of Lock Indicator. These pins function as the active high PLL loss of lock indicator if the LOL_PIN register bit is set to 1. 0 = PLL locked. 1 = PLL unlocked. If LOL_PINn = 0, this pin will tri-state. Active polarity is controlled by the LOL_POLn bit. The PLL lock status will always be reflected in the LOL_INTn read only register bit. e.g., IRQ_PIN. See Si5376 Register Map.

Table 10. Si5376 Pin Descriptions (Continued)

Pin#	Pin Name	I/O	Signal Level	Description
D1 A6 F9 J4	CS_CA_A CS_CA_B CS_CA_C CS_CA_D	I/O	LVCMOS	DSPLLq Input Clock Select/Active Clock Indicator. Input: In manual clock selection mode, this pin functions as the manual input clock selector if the CKSEL_PIN is set to 1. 0 = Select CKIN1 1 = Select CKIN2 If CKSEL_PIN = 0, the CKSEL_REG register bit controls this function and this input tristates. If configured for input, must be tied high or low. Output: In automatic clock selection mode, this pin indicates which of the two input clocks is currently the active clock. If alarms exist on both clocks, CK_ACTV will indicate the last active clock that was used before entering the digital hold state. The CK_ACTV_PIN register bit must be set to 1 to reflect the active clock status to the CK_ACTV output pin. 0 = CKIN1 active input clock 1 = CKIN2 active input clock If CK_ACTV_PIN = 0, this pin will tristate. The CK_ACTV status will always be reflected in the CK_ACTV_REG read only register bit.
G5	SCL	I	LVCMOS	I ² C Serial Clock. This pin functions as the serial clock input. This pin has a weak pull-down.
G6	SDA	I/O	LVCMOS	I ² C Serial Data. I ² C pin functions as the bi-directional serial data port.

Note: Internal register names are indicated by italics, e.g., *IRQ_PIN*. See Si5376 Register Map.

Table 10. Si5376 Pin Descriptions (Continued)

Pin #	Pin Name	I/O	Signal Level	Description
B1	CKOUT1P_A	0	Multi	Output Clock for DSPLLq.
A2	CKOUT1N_A			Differential output clocks. Output signal format is selected by
A5	CKOUT2P_A			SFOUT_REG register bits. Output is differential for LVPECL,
A4	CKOUT2N_A			LVDS, and CML compatible modes. For CMOS format, both output pins drive in phase single-ended clock outputs at the same
A9	CKOUT1P_B			frequency.
В9	CKOUT1N_B			
E9	CKOUT2P_B			
D9	CKOUT2N_B			
J9	CKOUT1P_C			
J8	CKOUT1N_C			
J5	CKOUT2P_C			
J6	CKOUT2N_C			
J1	CKOUT1P_D			
H1	CKOUT1N_D			
E1	CKOUT2P_D			
F1	CKOUT2N_D			

Note: Internal register names are indicated by italics, e.g., *IRQ_PIN*. See Si5376 Register Map.

9. Ordering Guide

Ordering Part Number	Input/Output Clocks	PLL Bandwidth Range	Package	RoHS6 Pb-Free	Temperature Range
Si5376B-A-GL	8/8	60 Hz to 8.4 kHz	10x10 mm 80-PBGA	Yes	–40 to 85 °C
Si5376B-A-BL	8/8	60 Hz to 8.4 kHz	10x10 mm 80-PBGA	No	–40 to 85 °C
Si5376-EVB			Evaluation Board		

10. Package Outline

Figure 10 illustrates the package details for the Si5376. Table 11 lists the values for the dimensions shown in the illustration. Visit https://www.skyworksinc.com/Product_Certificate.aspx for more environmental information about the package.




Figure 10. 80-Pin Plastic Ball Grid Array (PBGA)

Table 11. Package Dimensions

Symbol	Min	Nom	Max
Α	1.22	1.39	1.56
A1	0.40	0.50	0.60
A2	0.32	0.36	0.40
A3	0.46	0.53	0.60
b	0.50	0.60	0.70
D	10.00 BSC		
Е	10.00 BSC		
D1	8.00 BSC		

	Min	Nom	Max
E1	8.00 BSC		
е	1.00 BSC		
aaa	0.10		
bbb	0.10		
CCC	0.12		
ddd	0.15		
eee	0.08		

Notes:

- 1. All dimensions shown are in millimeters (mm) unless otherwise noted.
- 2. Dimensioning and Tolerancing per ANSI Y14.5M-1994.
- 3. This drawing conforms to JEDEC outline MO-192.
- **4.** Recommended card reflow profile is per the JEDEC/IPC J-STD-020 specification for Small Body Components.

63

11. Recommended PCB Layout




Figure 11. PBGA Card Layout

Table 12. Layout Dimensions

Symbol	MIN	NOM	MAX
X	0.40	0.45	0.50
C1	8.00		
C2	8.00		
E1	1.00		
E2	1.00		

Notes:

General

- 1. All dimensions shown are in millimeters (mm) unless otherwise noted.
- 2. Dimensioning and Tolerancing is per the ANSI Y14.5M-1994 specification.
- 3. This Land Pattern Design is based on the IPC-7351 guidelines.

Solder Mask Design

4. All metal pads are to be non-solder mask defined (NSMD). Clearance between the solder mask and the metal pad is to be 60 μm minimum, all the way around the pad.

Stencil Design

- A stainless steel, laser-cut and electro-polished stencil with trapezoidal walls should be used to assure good solder paste release.
- 6. The stencil thickness should be 0.125 mm (5 mils).
- 7. The ratio of stencil aperture to land pad size should be 1:1.

Card Assembly

- 8. A No-Clean, Type-3 solder paste is recommended.
- **9.** The recommended card reflow profile is per the JEDEC/IPC J-STD-020 specification for Small Body Components.

12. Top Markings


12.1. Si5376 Top Marking (PBGA, Lead-Free)



12.2. Top Marking Explanation (PBGA, Lead-Free)

Mark Method:	Laser			
Logo Size:	6.1 x 2.2 mm Center-Justified			
Font Size:	0.80 mm Right-Justified			
Line 1 Marking:	Device Part Number	Si5376B-A-GL, Pb-free		
Line 2 Marking:	YY = Year WW = Work Week	Assigned by the Assembly House. Corresponds to the year and work week of the mold date.		
	TTTTTT = Mfg Code	Manufacturing Code from the Assembly Purchase Order form.		
Line 3 Marking:	Pin 1 Identifier	Circle = 0.75 mm Diameter Lower-Left Justified		
	"e1" Lead-Free Finish Symbol (Pb-Free BGA Balls)	Circle = 1.4 mm Diameter Center-Justified		
	Country of Origin	TW		

12.3. Si5376 Top Marking (PBGA, Lead-Finish)



12.4. Top Marking Explanation (PBGA, Lead-Finish)

Mark Method:	Laser	Laser		
Logo Size:	6.1 x 2.2 mm Center-Justified			
Font Size:	0.80 mm Right-Justified	1000		
Line 1 Marking:	Device Part Number	Si5376B-A-BL, Pb finish		
Line 2 Marking:	YY = Year WW = Work Week	Assigned by the Assembly House. Corresponds to the year and work week of the mold date.		
	TTTTTT = Mfg Code	Manufacturing Code from the Assembly Purchase Order form.		
Line 3 Marking:	Pin 1 Identifier	Circle = 0.75 mm Diameter Lower-Left Justified		
	"e0" Lead Finish Symbol (SnPb BGA Balls)	Circle = 1.4 mm Diameter Center-Justified		
	Country of Origin	TW		









skyworksinc.com/CBPro



skyworksinc.com/quality



Support & Resources skyworksinc.com/support

Copyright © 2022 Skyworks Solutions, Inc. All Rights Reserved.

Information in this document is provided in connection with Skyworks Solutions, Inc. ("Skyworks") products or services. These materials, including the information contained herein, are provided by Skyworks as a service to its customers and may be used for informational purposes only by the customer. Skyworks assumes no responsibility for errors or omissions in these materials or the information contained herein. Skyworks may change its documentation, products, services, specifications or product descriptions at any time, without notice. Skyworks makes no commitment to update the materials or information and shall have no responsibility whatsoever for conflicts, incompatibilities, or other difficulties arising from any future changes.

No license, whether express, implied, by estoppel or otherwise, is granted to any intellectual property rights by this document. Skyworks assumes no liability for any materials, products or information provided hereunder, including the sale, distribution, reproduction or use of Skyworks products, information or materials, except as may be provided in Skyworks' Terms and Conditions of Sale.

THE MATERIALS, PRODUCTS AND INFORMATION ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, WHETHER EXPRESS, IMPLIED, STATUTORY, OR OTHERWISE, INCLUDING FITNESS FOR A PARTICULAR PURPOSE OR USE, MERCHANTABILITY, PERFORMANCE, QUALITY OR NON-INFRINGEMENT OF ANY INTELLECTUAL PROPERTY RIGHT; ALL SUCH WARRANTIES ARE HEREBY EXPRESSLY DISCLAIMED. SKYWORKS DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. SKYWORKS SHALL NOT BE LIABLE FOR ANY DAMAGES, INCLUDING BUT NOT LIMITED TO ANY SPECIAL, INDIRECT, INCIDENTAL, STATUTORY, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS THAT MAY RESULT FROM THE USE OF THE MATERIALS OR INFORMATION, WHETHER OR NOT THE RECIPIENT OF MATERIALS HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGE

Skyworks products are not intended for use in medical, lifesaving or life-sustaining applications, or other equipment in which the failure of the Skyworks products could lead to personal injury, death, physical or environmental damage. Skyworks customers using or selling Skyworks products for use in such applications do so at their own risk and agree to fully indemnify Skyworks for any damages resulting from such improper use or sale.

Customers are responsible for their products and applications using Skyworks products, which may deviate from published specifications as a result of design defects, errors, or operation of products outside of published parameters or design specifications. Customers should include design and operating safeguards to minimize these and other risks. Skyworks assumes no liability for applications assistance, customer product design, or damage to any equipment resulting from the use of Skyworks products outside of Skyworks' published specifications or parameters.

Skyworks, the Skyworks symbol, Sky5®, SkyOne®, SkyBlue™, Skyworks Green™, Clockbuilder®, DSPLL®, ISOmodem®, ProSLIC®, and SiPHY® are trademarks or registered trademarks of Skyworks Solutions, Inc. or its subsidiaries in the United States and other countries. Third-party brands and names are for identification purposes only and are the property of their respective owners. Additional information, including relevant terms and conditions, posted at www.skyworksinc.com, are incorporated by reference.